




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.





A

B

PRODUCT NUMBER		DIM	LENGTH FORMULAS (SEE NOTE 10)
51741-A00CCCDDEF-- NOTE ①		DIM "A"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .650 [16.51] (NOTE 10)
SEE NOTE 1		DIM "B"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .350 [8.89]
		DIM "C"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .300 [7.62]
		DIM "D"	.250 [6.35] x DD + .375 [9.53]
		DIM "F"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .680 [17.27]
		DIM "G"	.250 [6.35] x DD + .225 [5.72]

CONNECTOR NOTES	
①. PRODUCT NUMBER CODE: 51741 - A 00 CCC DD E F LF	NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE ADD THIS SUFFIX: 78u"/2.00um Sn ON PCB INTERFACE  RETENTION TO PCB (NOTE 8) TAIL OPTIONS (NOTE 7) NUMBER OF LEFT END POWER CONTACTS (NOTE 6) NUMBER OF SIGNAL CONTACTS (NOTE 5) ALWAYS '00' (ZERO, ZERO) (NOTE 4) PLATING (NOTE 3) BASE NUMBER
②. HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC. SIGNAL CONTACT MATERIAL: COPPER ALLOY POWER CONTACT MATERIAL: COPPER ALLOY	
 ③. PLATING OPTION: 1 = SEE PRINT 10064183 FOR PLATING SPEC OF 51741-100CCCDDEF; 51741-100CCCDDEFLF	
④. THIS PART NOT AVAILABLE WITH RIGHT SIDE POWER CONTACTS.	
⑤. SIGNAL CONTACTS, 004 TO 148 AVAILABLE.	
⑥. LEFT END POWER CONTACTS, 01 TO 20 AVAILABLE. MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.	
⑦. TAIL OPTIONS: A = .135±.010 [3.43±.25] SOLDER TO BOARD C = .135±.010 [3.43±.25] PRESS FIT	

SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	projection	COPY		www.fciconnect.com	
L				.XX±.01/0.XX±0.3				title	
				.XXX±.005/0.XX±0.13				VERTICAL RECEPTACLE W/ GUIDE PIN SIGNAL / POWER	
				.XXX±.0020/.XX±.051				product family	
				angles 0°±2°				PWRBLADE	
				dr D. EATON 05-25-99				code	
				enr J. BROWN 05-24-99				213	
				chr J. BROWN 05-26-99				sheet	
				appd J. BROWN 05-26-99				2	
sheet index	revision sheet								

Pro/E		3		4	
		cage code 22526			

- ⑧. RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098 + .002, -.001 [2.49 +0.05, -0.03] THRU HOLE IN PCB)
BOARD LOCK TO BE USED IN CONJUNCTION WITH AN .092 PCB OR THICKER.
C = NO RETENTION FEATURE (ALL PRESS FIT).
- ⑨. MANUFACTURE'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
- ⑩. THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART IS 8.00 [203.2].
11. PRODUCT SPECIFICATION GS-12-149.
12. REFERENCE 51698 FOR SPECIALS WORKSHEET.
- PCB NOTES:
13. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
14. ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF .004 [0.01]
15. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
16. 0.0453±.001 [1.151±.02] DRILLED HOLES PLATED WITH 0.0003 [0.007] MIN SnPb OVER 0.001 [1.03] TO .003 [0.08] PLATING TO ACHIEVE A .040 ±.003 [1.02 ±.08] HOLE.
17. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

A


B

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51741-A00CCCDDEF -- NOTE ①
SEE NOTE 1




SECTION B-B
SCALE 2:1



SECTION C-C
SCALE 2:1



SECTION A-A
SCALE 2:1



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecr no.	dr	date			linear	.XX±.01/0.X±0.3	COPY		projection		title	
L						angles	.XXX±.005/0.XX±0.13					VERTICAL RECEPTACLE W/ GUIDE PIN	
							.XXX±.0020/.XX±.051					SIGNAL / POWER	
						dr	D. EATON 05-25-99					product family	
						enr	J. BROWN 05-24-99					PWRBLADE	
						chr	J. BROWN 05-26-99					code	
						appd	J. BROWN 05-26-99					213	
sheet index		revision sheet										sheet	
												3	
												4	

Pro/E

cage code 22526