




- 1 WIRE SIZE AND AMP LOGO APPEAR ON OUTSIDE OF WIRE BARREL.
- 2 RETENTION CLIP: PHOSPHOR BRONZE PER QQ-B-750.
PIN CONTACT: COPPER PER QQ-C-576.
- 3 PIN CONTACT: 0.76µm [0.000030] MIN GOLD PER MIL-G-45204 ON CONTACT MATING END, GOLD FLASH ON REMAINDER , ALL OVER 1.27µm [0.000050] MIN NICKEL PER QQ-N-390.
RETENTION CLIP: 2.54µm [0.000100] MIN NICKEL PER QQ-N-290.
- 4 PIN CONTACT: 5.08µm [0.000200] MIN SILVER PER QQ-S-365 ON CONTACT MATING END, 1.27µm [0.000050] MIN SILVER ON REMAINDER, ALL OVER 1.27µm [0.000050] MIN NICKEL PER QQ-N-290.
RETENTION CLIP: 2.54µm [0.000100] MIN NICKEL PER QQ-N-290.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
FT	13		0	RLSE PER NPR 5498 WAS 95-5019-9	21 MAR 96	-	-
			A	ADDED -1,-3,-5,-7 PER EC	21 MAR 97	CO	AF
			B	REV PER EC 0320-399-97	22 JAN 98	MB	RW

	12.32 [.485]	-	28.52 [1.123]	DETAIL X	213841-8
	12.32 [.485]	-	28.52 [1.123]	DETAIL X	213841-7
	12.32 [.485]	32.84 [1.293]	28.52 [1.123]	-	213841-6
	12.32 [.485]	32.84 [1.293]	28.52 [1.123]	-	213841-5
	10.16 [.400]	-	26.37 [1.038]	DETAIL X	213841-4
	10.16 [.400]	-	26.37 [1.038]	DETAIL X	213841-3
	10.16 [.400]	30.68 [1.208]	26.37 [1.038]	-	213841-2
	10.16 [.400]	30.68 [1.208]	26.37 [1.038]	-	213841-1
FINISH	C	B	A	LOOSE PIECE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT AND ANY IMPROVEMENTS IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHALL BE CONTACTED FOR THE LATEST NOTATION.		DMN C. OBERMAN 21 MAR 96	AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm (INCHES)		CHK R. STONE 25 MAR 96	NAME G. STEINHAUER		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. STEINHAUER 26 MAR 96	PRODUCT SPEC		
0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.01 4 PLC ±.01		APPLICATION SPEC	SIZE A1		
NATERIAL		WEIGHT	CAGE CODE 00779		
FINISH		CUSTOMER DRAWING	DRAWING NO C-213841		
SEE TABLE		SCALE	10:1		
		SHEET	1 OF 1		
		REV	B		