


PIN RECEPTACLES

FOR .048" - .064" DIAMETER PINS (#13 CONTACT)
FOR .045" - .065" DIAMETER PINS (#23 CONTACT)

0364

0364-0-15-XX-13-XX-10-0


Solder mount in .100 min. mounting hole
 Also available on 16mm wide carrier tape:
 1,300 parts per 13" reel
 Order as: 0364-0-57-XX-13-XX-10-0



0363

0363-0-15-XX-23-XX-10-0


Solder mount in .102 min. mounting hole



0365

0365-0-15-XX-23-XX-10-0


Hex press-fit in .105 plated through-hole
 Also available on 16mm wide carrier tape:
 1,200 parts per 13" reel
 Order as: 0365-0-57-XX-23-XX-10-0



0366

0366-0-15-XX-13-XX-10-0


Press-fit in .109 mounting hole



0372

0372-0-15-XX-13-XX-10-0


Solder mount in .102 min. mounting hole
 Also available on 24mm wide carrier tape:
 950 parts per 13" reel
 Order as: 0372-0-57-XX-13-XX-10-0



0362

0362-0-15-XX-13-XX-10-0


Solder mount in .102 min. mounting hole



0367

0367-0-15-XX-23-XX-10-0


Square press-fit in .040 plated through-hole



9324

9324-0-15-XX-23-XX-04-0


Press-fit in .106 mounting hole



0492

0492-0-15-XX-13-XX-04-0


Press-fit in .106 mounting hole



0381

0381-0-15-XX-23-XX-10-0


Press-fit in .104 mounting hole



4034

4034-0-15-XX-23-XX-04-0


Press-fit in .109 mounting hole



3044

3044-0-15-XX-23-XX-04-0

Solder mount in .104 min. mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **15** 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **27** 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#13 or #23 CONTACT (DATA ON PAGE 260)

(For alternate contact choices, see group G on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com