


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
J	REVISED PER ECD-12-021161	04DEC12	G.WELLS
K	REVISED PER ECD-14-002312	13FEB15	H.SMITH



CODE 54
STRAIGHT ADAPTER


NOTES:

1. THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR.
2. SEE CH00-0250-008 FOR ORDERING INFORMATION, MODIFICATIONS AND ADDITIONAL DIMENSIONS.
3. SEE DRAWING "TR" FOR DETAIL ON TINEL-LOCK RING. RINGS ARE DESIGNED TO BE HEATED ELECTRICALLY. ALL RINGS ARE MARKED WITH THERMOCHROMIC PAINT WHICH CHANGES COLOR WHEN INSTALLATION TEMPERATURE IS REACHED.
4. ADAPTER TO BE PERMANENTLY MARKED WITH CODE IDENT. NO. AND PART NO. LESS RING DESIGNATOR (E.G.: 06090-TXR54AB00-1206). RINGS SHALL BEAR NO MARKING.
5. FOR LARGER ENTRY SIZES, A 2 PIECE ADAPTER (TYPE II) IS SUPPLIED.
6. ADAPTER MATES TO MIL-C-81703, SERIES III, MS3424, MS3446, MS3464, MS3467, MS3468, CLASS E & L.
7. ADAPTER MATES TO MIL-C-5015G, MS3400 SERIES, CLASS D, E, K, L, U & W: MS3400, MS3401, MS3404, MS3406, MS3450, MS3451, MS3454, MS3456, MS3470, MS3471, MS3472, MS3474, MS3475, MS3476. MIL-C-83723, SERIES II, CLASS A & L. MIL-C-83723, SERIES I & III, CLASS A, G, K, R & S: M83723/1, /2, /3, /4, /5, /6, /7, /8, /13, /14, /36, /37, /38, /39, /40, /41, /42, /43, /48, /49, /65, /66, /67, /68, /69, /70, /71, /72, /73, /74, /75, /76, /77, /78, /82, /83, /84, /85, /86, /87, /91, /92, /95, /97, /98, (MS3155 CONTROLLED INTERFACE).
8. THESE DIMENSIONS APPLY IF A SELF-LOCKING COUPLING NUT IS USED. (MOD. CODE "S")
9. THESE DIMENSIONS APPLY IF AN ADAPTER MATERIAL IS STAINLESS STEEL.


If this document is printed it becomes uncontrolled. Check for the latest revision

© 2015 TYCO ELECTRONICS. ALL RIGHTS RESERVED


Raychem Adapters
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS.	DRAWN R. RAMIREZ	DATE 03-18-93	TE Connectivity			
	CHECKED	DATE				
	APPROVED	DATE				
	REVISED N. NAGAR	DATE 13-02-15	TITLE TINEL-LOCKTM ADAPTER			
DECIMALS .XXX ± 0.005 [0.13 mm] .XX ± 0.01 [0.25 mm] .X ± 0.1 [0.50 mm]	CAD NAME txr54_1_k_cd					
ANGLES .X ± 1 DEG.	THIRD ANGLE PROJECTION 		SIZE A	CODE IDENT. NO. 06090	DWG. NO. TXR54	
DO NOT SCALE THIS DWG			SHEET 1 OF 3			


SEE SHEET 1 FOR REVISION




STRAIGHT ADAPTER-TYPE I




45° ADAPTER-TYPE I




90° ADAPTER
TYPE I



STRAIGHT ADAPTER-TYPE II



45° ADAPTER-TYPE II



90° ADAPTER
TYPE II

Raychem Adapters
CUSTOMER DRAWING

SIZE	CODE IDENT. NO.	DWG. NO.	REV
A	06090	TXR54	K
DO NOT SCALE THIS DWG		CAD NAME	txr54_2_k_cd
		SHEET 2 OF 3	

TABLE I

ORDER NO.	SHELL SIZE		MAX ENTRY SIZE TYPE I	A THREAD CLASS 2B	B DIA MAX	B DIA MAX	C MAX	D MAX	E MAX	M DIA MAX	W MAX	W MAX
	6	7										
03	3		04	.562-24 UNEF	.669 [17.00]	.940 [23.88]	.75 [19.1]	1.083 [27.5]	1.13 [28.7]	.695 [17.65]	1.06 [26.9]	1.05 [26.8]
08		8 & 8S	04	.500-20 UNF	.617 [15.67]	.890 [22.61]	.75 [19.1]	1.075 [27.3]	1.10 [27.9]	.630 [16.00]	.98 [25.0]	.90 [22.9]
10		10, 10S & 10SL	06	.625-24 UNEF	.734 [18.64]	1.010 [25.65]	.77 [19.6]	1.102 [28.0]	1.16 [29.5]	.757 [19.23]	1.06 [27.0]	1.00 [25.5]
12	7	12 & 12S	08	.750-20 UNEF	.858 [21.79]	1.140 [28.96]	.80 [20.3]	1.122 [28.5]	1.22 [31.0]	.882 [22.40]	1.16 [29.5]	1.13 [28.8]
14	12	14 & 14S	08	.875-20 UNEF	.984 [24.99]	1.260 [32.00]	.82 [20.8]	1.161 [29.5]	1.28 [32.5]	1.007 [25.58]	1.22 [31.0]	1.21 [30.9]
16	19	16 & 16S	10	1.000-20 UNEF	1.112 [28.24]	1.390 [35.31]	.84 [21.3]	1.190 [30.2]	1.35 [34.3]	1.132 [28.75]	1.36 [34.5]	1.34 [34.0]
18	27	18	12	1.062-18 UNEF	1.218 [30.94]	1.510 [38.35]	.86 [21.8]	1.220 [31.0]	1.40 [35.6]	1.218 [30.94]	1.48 [37.5]	1.41 [36.0]
20	37	20	14	1.188-18 UNEF	1.345 [34.16]	1.640 [41.66]	.88 [22.4]	1.236 [31.4]	1.46 [37.1]	1.345 [34.16]	1.67 [42.5]	1.54 [39.3]
22		22	16	1.312-18 UNEF	1.468 [37.30]	1.760 [44.70]	.91 [23.1]	1.244 [31.6]	1.53 [38.9]	1.468 [37.30]	1.75 [44.5]	1.67 [42.4]
24		24	18	1.438-18 UNEF	1.593 [40.46]	1.890 [48.00]	.93 [23.6]	1.283 [32.6]	1.59 [40.4]	1.593 [40.46]	1.80 [45.5]	1.78 [45.3]
28		28	22	1.750-18 UNS	1.969 [50.01]	2.140 [54.36]	.98 [24.9]	1.300 [33.0]	1.78 [45.2]	1.969 [50.01]	2.15 [54.7]	2.01 [51.2]
32		32	24	2.000-18 UNS	2.219 [56.36]	2.400 [60.96]	1.03 [26.2]	1.19 [30.2]	1.90 [48.3]	2.219 [56.36]	2.41 [61.4]	2.38 [60.5]
36		36	24	2.250-16 UN	2.469 [62.71]	2.640 [67.06]	1.08 [27.4]	1.23 [31.2]	2.03 [51.6]	2.469 [62.71]	2.67 [67.7]	2.60 [66.0]
40		40	24	2.500-16 UN	2.719 [69.06]	2.890 [73.41]	1.15 [29.1]	1.28 [32.5]	2.15 [54.6]	-- [---]	2.90 [73.7]	2.85 [72.5]
44		44	24	2.750-16 UN	2.969 [75.41]	3.140 [79.76]	1.20 [30.6]	1.355 [34.2]	2.28 [57.9]	-- [---]	3.15 [80.0]	2.99 [76.0]
48		48	24	3.000-16 UN	3.219 [81.76]	3.390 [86.11]	1.25 [31.8]	1.394 [35.4]	2.40 [61.0]	-- [---]	3.40 [86.3]	3.16 [80.3]
61	61		18	1.500-18 UNEF	1.653 [42.00]	1.880 [47.75]	.94 [23.9]	1.09 [27.7]	1.62 [41.1]	1.653 [42.00]	1.90 [48.3]	1.92 [48.8]

TABLE II

ENTRY SIZE	Z +.010 -.020	S DIA	Y ±.015 [±0.38]	F MAX	G MAX	H MAX	H MAX 8	J MAX	K MAX	K MAX 8
04	.250 [6.35]	.376 [9.56] .370 [9.39]	.550 [13.97]	N/A	N/A	N/A	N/A	N/A	N/A	N/A
05	.312 [7.92]	.438 [11.13] .432 [10.97]	.612 [15.54]	.77 [19.6]	1.10 [28.0]	1.19 [30.2]	1.19 [30.2]	1.16 [29.5]	.83 [21.0]	.97 [24.6]
06	.375 [9.53]	.501 [12.73] .495 [12.57]	.675 [17.14]	.77 [19.6]	1.10 [28.0]	1.19 [30.2]	1.19 [30.2]	1.16 [29.5]	.83 [21.0]	.97 [24.6]
07	.437 [11.09]	.563 [14.31] .556 [14.12]	.737 [18.71]	.80 [20.3]	1.10 [28.0]	1.38 [35.1]	1.38 [35.1]	1.22 [31.0]	.92 [23.4]	.97 [24.6]
08	.500 [12.70]	.626 [15.91] .619 [15.72]	.800 [20.32]	.80 [20.3]	1.12 [28.5]	1.38 [35.1]	1.38 [35.1]	1.22 [31.0]	.96 [24.5]	1.11 [28.3]
10	.625 [15.87]	.752 [19.11] .742 [18.84]	.925 [23.49]	.84 [21.3]	1.16 [29.5]	1.51 [38.4]	1.51 [38.4]	1.35 [34.3]	1.18 [30.0]	1.28 [32.4]
12	.750 [19.05]	.877 [22.28] .867 [22.02]	1.050 [26.67]	.88 [22.4]	1.19 [30.2]	1.63 [41.4]	1.63 [41.4]	1.40 [35.6]	1.35 [34.3]	1.40 [35.6]
14	.875 [22.23]	1.002 [25.46] .991 [25.17]	1.175 [29.84]	.88 [22.4]	1.22 [31.0]	1.78 [45.2]	1.78 [45.2]	1.46 [37.1]	1.41 [35.8]	1.51 [38.5]
16	1.000 [25.40]	1.127 [28.63] 1.116 [28.34]	1.300 [33.02]	.93 [23.6]	1.24 [31.4]	1.88 [47.8]	1.88 [47.8]	1.53 [38.9]	1.60 [40.6]	1.64 [41.7]
18	1.125 [28.57]	1.252 [31.81] 1.241 [31.52]	1.425 [36.19]	.93 [23.6]	1.25 [31.6]	2.01 [51.1]	2.01 [51.1]	1.59 [40.4]	1.66 [42.2]	1.73 [43.9]
20	1.250 [31.75]	1.377 [34.98] 1.366 [34.69]	1.550 [39.37]	.98 [24.9]	1.28 [32.6]	2.13 [54.1]	2.13 [54.1]	1.78 [45.2]	2.04 [51.8]	2.04 [51.8]
22	1.375 [34.93]	1.502 [38.15] 1.488 [37.79]	1.675 [42.55]	1.03 [26.2]	1.41 [35.8]	2.29 [58.2]	2.29 [58.2]	1.85 [47.0]	2.23 [56.6]	2.23 [56.6]
24	1.500 [38.10]	1.627 [41.33] 1.613 [40.97]	1.800 [45.72]	1.08 [27.4]	1.52 [38.6]	2.42 [61.5]	2.42 [61.5]	1.92 [48.8]	2.23 [56.6]	2.23 [56.6]
28	1.750 [44.45]	1.873 [47.58] 1.867 [47.42]	2.050 [52.00]	1.08 [27.4]	1.76 [44.9]	2.60 [66.0]	2.40 [60.8]	2.03 [51.6]	2.30 [58.5]	2.40 [61.0]

Raychem Adapters
CUSTOMER DRAWING

SIZE A	CODE IDENT. NO. 06090	DWG. NO. TXR54	REV K
DO NOT SCALE THIS DWG		CAD NAME txr54_3_k_cd	SHEET 3 OF 3