





JKL LAMP NUMBER	VOLTS RATED	WATTS	INITIAL MSCP	INITIAL LUMENS	AVERAGE LIFE HRS.	FILAMENT TYPE
6S6-12V	12	6	3.58	45.0	1,500	C-2V
6S6-30V	30	6	3.98	50.0	1,500	C-2V
6S6-120V	120	6	3.18	40.0	1,500	C-7A
6S6-145V	145	6	3.18	40.0	1,500	C-7A
6S6-155V	155	6	3.18	40.0	1,500	C-7A
10S6-230V	230	10	5.97	75.0	1,500	C-1
10S6-250V	250	10	5.97	75.0	1,500	C-1

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
DRAWN BY		APPVD BY DATE		SIZE	FSCM NO.	DRAWING NO.	
L. WENGSTROM		Q.C. 3/1/01		A	55335	SCREW BASE CANDELABRA S-6	
- CAD DRAWING -				SCALE	RELEASED DATE	REVISION DATE	
MANUAL REVISIONS NOT PERMITTED				NONE	3/1/01		
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE			REV. NO.	SHEET	
						1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[6S6-120V](#) [6S6-145V](#) [6S6-155V](#) [10S6-230V](#) [6S6-12V](#) [6S6-30V](#)