

**Part Number: 87203-7364**

D-Subminiature Shielded I/O PCB Male Plug, Right Angle, Through Hole, 25 Circuits, M2.6 Inner Thread Screws Assembled, Gold (Au) Flash

Image not available

Status:	OBsolete
Replacement:	NONE
Series:	87203
Category:	I/O Connectors

Series image - Reference only

Mates With Part(s):
[87204](#)

Product Environmental Compliance

[EU RoHS](#): Not RoHS Compliant

[China RoHS](#):

[REACH SVHC](#):

[Low-Halogen Status](#): Not Reviewed

Part Detail**General**

Status	Obsolete
Category	I/O Connectors
Series	87203
Application	Wire-to-Board
Comments	Shell: Steel
Component Type	Plug
Obsolete Date	2006/07/01
Product Name	D-Sub
Type	N/A

Physical

Circuits (Loaded)	25
Circuits (maximum)	25
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.77mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	300V

Agency Certification

CSA	LR19980
UL	E29179

Solder Process Data

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

Material Info

UPC	800754319133
-----	--------------

Application Tooling

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)