



586 Series BASED LED T 3 1/4 MINIATURE SCREW (E10)




FEATURES / BENEFITS

- ▲ Easy installation
- ▲ Super bright single chip design
- ▲ AlInGaP and InGaN technology
- ▲ Polarized and non polarized configurations available
- ▲ High brightness with low current draw - uses up to 90% less energy than an incandescent
- ▲ Long life - typically 100K hours
- ▲ No heat generated
- ▲ Resistant to shock and vibration
- ▲ Integral resistor
- ▲ Colors include red, green, amber, blue and white

Dialight's line of based LED lamps is designed to directly replace many popular subminiature and miniature incandescent lamps. The benefits of LED technology over incandescent are significant: They offer long life, are shock resistant, withstand vibration and provide energy conservation.

SPECIFICATIONS



Measurements are typical
Dimensions are inches [mm]

- ▲ Operating voltages - 6, 14 and 28 VDC
- ▲ Non-polarized
- ▲ Operating temperature: -30°C to 85°C
- ▲ Storage temperature: -40°C to 100°C
- ▲ Replaces incandescent lamp numbers:
40, 46, 1481, 1487, 1821*

* May replace other incandescent lamps.

CONSIDERATIONS

- ▲ Although these lamps can be operated at a lower voltage, which will increase the life, the intensity will be reduced.
- ▲ Operation of the based LED at a higher voltage should not exceed 10% above the recommended voltage.
- ▲ Dialight does not recommend the based LED lamps be used in neon lamp sockets.
- ▲ Since lens caps act as filters for the light emitted from the based LED, it is important to match the color of the wavelength of the LED. Dialight recommends using transparent lenses, which will optimize light output.

Dialight reserves the right to make changes at any time
in order to supply the best product possible.



ISO 9001

Dialight Corporation

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732.919.3119 • Fax: (1) 732.751.5778 • www.dialight.com



a Roxboro Group Company

MDEL586F001_A

T 3 1/4 MINIATURE SCREW (E10)

Part Number	Color	Polarity	Peak Wavelength nm	Nominal Voltage	Forward Current (TYP. - mA)	Intensity (TYP. - mcd)
586-2701-201	Red	Non-Polarized	630	6	15	1050
586-2702-201	Green	Non-Polarized	525	6	15	1650
586-2703-201	Yellow	Non-Polarized	592	6	15	1275
586-2705-201	Blue	Non-Polarized	470	6	15	487
586-2706-201	White	Non-Polarized	*	6	15	825
586-2701-203	Red	Non-Polarized	630	14	15	1050
586-2702-203	Green	Non-Polarized	525	14	15	1650
586-2703-203	Yellow	Non-Polarized	592	14	15	1275
586-2705-203	Blue	Non-Polarized	470	14	15	487
586-2706-203	White	Non-Polarized	*	14	15	825
586-2701-205	Red	Non-Polarized	630	28	7.5	525
586-2702-205	Green	Non-Polarized	525	28	7.5	825
586-2703-205	Yellow	Non-Polarized	592	28	7.5	637
586-2705-205	Blue	Non-Polarized	470	28	7.5	243
586-2706-205	White	Non-Polarized	*	28	7.5	412

* Color Coordinates: x = 0.330, y = 0.365

Based LEDs SELECTION

With the technological advancements in Light Emitting Diodes (LEDs) brightness can now rival the incandescent lamp when used in similar packages. These advancements have created a new type of product called the based LED - an LED with the functionality of an incandescent bulb.


The following styles are currently available in red, green, amber, blue and white:

- ▲ T 1 3/4 Midget Flange
- ▲ T 1 3/4 Bi-Pin
- ▲ T 2 Telephone Slide
- ▲ T 3 1/4 Miniature Bayonet (BA9s)
- ▲ T 3 1/4 Miniature Screw (E10)
- ▲ 15MM SC Bayonet (BA15S)

Dialight's line of based LEDs continues to grow.

Please visit our website for more information.

www.dialight.com



586 Series Based LED



A4703



ISO 9001

Dialight Corporation

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732.919.3119 • Fax: (1) 732.751.5778 • www.dialight.com



a Roxboro Group Company