



Inductive
Sensors



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
30 mm - Nonembeddable, Potted-In Cable 	Ni15-G30K-AN6X	T4671700	Short Barrel	15	3-Wire DC NPN
	Ni15-G30K-AP6X	T4670700	Short Barrel	15	3-Wire DC PNP
	Ni15-G30-Y0	T1006300		15	2-Wire DC NAMUR
	Ni15-G30-Y0X	T4020100		15	
30 mm - Nonembeddable, Potted-In Cable 	Ni15-G30-AN6X	T4647700		15	3-Wire DC NPN
	Ni15-G30-AN7X	T1714900		15	
	Ni15-G30-AP6X	T4647600		15	3-Wire DC PNP
	Ni20-G30-ADZ30X2	T4205404		20	2-Wire AC/DC Short-Circuit Protected
	Ni15-G30-AZ3X	T1306000		15	2-Wire AC/DC


Voltage	Switching Freq. (Hz)	Operating Current (mA) AC/DC	Operating Temp. (°C)	Protection	Housing	Face	End Cap	Power LED	Output LED	Cable Length/ Cable Mat.	Wiring Diagram #	Wiring Diagrams
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	1	Diagram 1
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	2	Diagram 2
5-30 VDC	200	Remote	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	N/A	2M/PVC	3	Diagram 3
	200	Remote	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	3	
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	1	Diagram 4
	500	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	1	
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	2	Diagram 3
20-250 VAC 10-300 VDC	20	≤400/300	-25 to +70	IP 67	CPB	PA 12	EPTR	GN	RD	2M/PVC	4	Diagram 4
20-250 VAC 10-300 VDC	20	≤400/300	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	RD	2M/PVC	4	Diagram 4

WIRING DIAGRAM




OUTPUT: Y0

LOCKNUT LN-M30



SPECIFICATIONS

OPERATING VOLTAGE	5-15 VDC
HYSTERESIS (DIFFERENTIAL TRAVEL)	1-10% (5% TYPICAL)
NOMINAL VOLTAGE	8.2 VDC
OUTPUT FUNCTION	RESISTANCE CHANGE, REQUIRES REMOTE AMPLIFIER
RESISTANCE CHANGE FROM NONACTIVATED TO ACTIVATED CONDITION	1.0 kΩ to >8.0 kΩ
RESULTING CURRENT CHANGE	≤ 2.2 mA to ≤ 1.0 mA
RECOMMENDED SWITCHING POINT FOR REMOTE AMPLIFIER	1.55 mA
TIME DELAY BEFORE AVAILABILITY	≤ 5 ms
POWER-ON EFFECT PROTECTION	REALIZED IN AMPLIFIER
POLARITY INVERSION PROTECTION	INCORPORATED
WIRE BREAK PROTECTION	REALIZED IN AMPLIFIER
PROTECTION AGAINST TRANSIENTS	REALIZED IN AMPLIFIER
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)
ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67
SHOCK	30 g, 11 ms
VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)
LED FUNCTION	RED: OUTPUT ENERGIZED
SENSING RANGE	15 mm = .591" (NOMINAL)
SWITCHING FREQUENCY	200 Hz
REPEATABILITY	≤ 2% of NOMINAL SENSING RANGE
SHIELDED	NO



RELATED DOCUMENTS

- 1.
- 2.
- 3.
- 4.

MATERIAL
BRASS BARRELFINISH
COPPER/NICKEL/
CHROME PLATING3RD ANGLE
PROJECTIONTOLERANCES UNLESS
OTHERWISE SPECIFIED.X ±0.02
.XX ±0.01
.XXX ±0.005
ANGLES ±1°ALL MILLIMETER
DIMENSIONS ARE
REFERENCE ONLYTHIS DRAWING IS
PROPERTY OF
TURCK INC. USE OF
THIS DOCUMENT
WITHOUT WRITTEN
PERMISSION IS
PROHIBITED.CRAFT RJP
CSCR

UNIT OF MEASUREMENT

INCH [MILLIMETER]

DO NOT SCALE THIS DRAWING

TURCK INC
High Technology Sensors and Automation Controls

DATE 1/27/93

SCALE NONE

DESCRIPTION

Ni15-G30-Y0X

IDENTIFICATION NO.

T4020100

REV

B

FILE: T4020100

SHEET 1 OF 1

B	UPDATE TO CURRENT TITLE BLOCK	RDS	01/21/93	10154
REV	DESCRIPTION	BY	DATE	EDD NO.