

## MM74HC154 4-to-16 Line Decoder

### General Description

The MM74HC154 decoder utilizes advanced silicon-gate CMOS technology, and is well suited to memory address decoding or data routing applications. It possesses high noise immunity, and low power consumption of CMOS with speeds similar to low power Schottky TTL circuits.

The MM74HC154 have 4 binary select inputs (A, B, C, and D). If the device is enabled these inputs determine which one of the 16 normally HIGH outputs will go LOW. Two active LOW enables (G1 and G2) are provided to ease cascading of decoders with little or no external logic.

Each output can drive 10 low power Schottky TTL equivalent loads, and is functionally and pin equivalent to the 74LS154. All inputs are protected from damage due to static discharge by diodes to  $V_{CC}$  and ground.

### Features

- Typical propagation delay: 21 ns
- Power supply quiescent current: 80  $\mu$ A
- Wide power supply voltage range: 2–6V
- Low input current: 1  $\mu$ A maximum


### Ordering Code:

| Order Number | Package Number | Package Description                                                         |
|--------------|----------------|-----------------------------------------------------------------------------|
| MM74HC154WM  | M24B           | 24-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| MM74HC154MTC | MTC24          | 24-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| MM74HC154N   | N24C           | 24-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide      |

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

### Connection Diagram

Pin Assignments for DIP, SOIC and TSSOP




### Truth Table

| Inputs          |                 | Outputs |   |   |   | Low Output (Note 1) |
|-----------------|-----------------|---------|---|---|---|---------------------|
| $\overline{G1}$ | $\overline{G2}$ | D       | C | B | A |                     |
| L               | L               | L       | L | L | L | 0                   |
| L               | L               | L       | L | L | H | 1                   |
| L               | L               | L       | L | H | L | 2                   |
| L               | L               | L       | L | H | H | 3                   |
| L               | L               | L       | H | L | L | 4                   |
| L               | L               | L       | H | L | H | 5                   |
| L               | L               | L       | H | H | L | 6                   |
| L               | L               | L       | H | H | H | 7                   |
| L               | L               | H       | L | L | L | 8                   |
| L               | L               | H       | L | L | H | 9                   |
| L               | L               | H       | L | H | L | 10                  |
| L               | L               | H       | L | H | H | 11                  |
| L               | L               | H       | H | L | L | 12                  |
| L               | L               | H       | H | L | H | 13                  |
| L               | L               | H       | H | H | L | 14                  |
| L               | L               | H       | H | H | H | 15                  |
| L               | H               | X       | X | X | X | —                   |
| H               | L               | X       | X | X | X | —                   |
| H               | H               | X       | X | X | X | —                   |

Note 1: All others HIGH

## Logic Diagram



**Absolute Maximum Ratings**(Note 2)

(Note 3)

|                                                  |                         |
|--------------------------------------------------|-------------------------|
| Supply Voltage ( $V_{CC}$ )                      | -0.5 to +7.0V           |
| DC Input Voltage ( $V_{IN}$ )                    | -1.5 to $V_{CC} + 1.5V$ |
| DC Output Voltage ( $V_{OUT}$ )                  | -0.5 to $V_{CC} + 0.5V$ |
| Clamp Diode Current ( $I_{IK}, I_{OK}$ )         | $\pm 20$ mA             |
| DC Output Current, per pin ( $I_{OUT}$ )         | $\pm 25$ mA             |
| DC $V_{CC}$ or GND Current, per pin ( $I_{CC}$ ) | $\pm 50$ mA             |
| Storage Temperature Range ( $T_{STG}$ )          | -65°C to +150°C         |
| Power Dissipation ( $P_D$ )                      |                         |
| (Note 4)                                         | 600 mW                  |
| S.O. Package only                                | 500 mW                  |
| Lead Temperature ( $T_L$ )                       |                         |
| (Soldering 10 seconds)                           | 260°C                   |

**Recommended Operating Conditions**

|                                                  | Min | Max      | Units |
|--------------------------------------------------|-----|----------|-------|
| Supply Voltage ( $V_{CC}$ )                      | 2   | 6        | V     |
| DC Input or Output Voltage ( $V_{IN}, V_{OUT}$ ) | 0   | $V_{CC}$ | V     |
| Operating Temperature Range ( $T_A$ )            | -40 | +85      | °C    |
| Input Rise or Fall Times                         |     |          |       |
| ( $t_r, t_f$ ) $V_{CC} = 2.0V$                   |     | 1000     | ns    |
| $V_{CC} = 4.5V$                                  |     | 500      | ns    |
| $V_{CC} = 6.0V$                                  |     | 400      | ns    |

**Note 2:** Absolute Maximum Ratings are those values beyond which damage to the device may occur.**Note 3:** Unless otherwise specified all voltages are referenced to ground.**Note 4:** Power Dissipation temperature derating — plastic "N" package: -12 mW/°C from 65°C to 85°C.**DC Electrical Characteristics** (Note 5)

| Symbol          | Parameter                         | Conditions                                                                                                           | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = −40 to 85°C |    | Units |
|-----------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------|-----------------|-----------------------|-------------------|------------------------------|----|-------|
|                 |                                   |                                                                                                                      |                 | Typ                   | Guaranteed Limits |                              |    |       |
| V <sub>IH</sub> | Minimum HIGH Level Input Voltage  |                                                                                                                      | 2.0V            |                       | 1.5               | 1.5                          | V  |       |
|                 |                                   |                                                                                                                      | 4.5V            |                       | 3.15              | 3.15                         |    |       |
|                 |                                   |                                                                                                                      | 6.0V            |                       | 4.2               | 4.2                          |    |       |
| V <sub>IL</sub> | Maximum LOW Level Input Voltage   |                                                                                                                      | 2.0V            |                       | 0.5               | 0.5                          | V  |       |
|                 |                                   |                                                                                                                      | 4.5V            |                       | 1.35              | 1.35                         |    |       |
|                 |                                   |                                                                                                                      | 6.0V            |                       | 1.8               | 1.8                          |    |       |
| V <sub>OH</sub> | Minimum HIGH Level Output Voltage | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 2.0                   | 1.9               | 1.9                          | V  |       |
|                 |                                   |                                                                                                                      | 4.5V            | 4.5                   | 4.4               | 4.4                          |    |       |
|                 |                                   |                                                                                                                      | 6.0V            | 6.0                   | 5.9               | 5.9                          |    |       |
|                 |                                   | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4.0 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA | 4.5V            | 4.2                   | 3.98              | 3.84                         | V  |       |
|                 |                                   |                                                                                                                      | 6.0V            | 5.7                   | 5.48              | 5.34                         |    |       |
|                 |                                   |                                                                                                                      |                 |                       |                   |                              |    |       |
| V <sub>OL</sub> | Maximum LOW Level Output Voltage  | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 0                     | 0.1               | 0.1                          | V  |       |
|                 |                                   |                                                                                                                      | 4.5V            | 0                     | 0.1               | 0.1                          |    |       |
|                 |                                   |                                                                                                                      | 6.0V            | 0                     | 0.1               | 0.1                          |    |       |
|                 |                                   | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4.0 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA | 4.5V            | 0.2                   | 0.26              | 0.33                         | V  |       |
|                 |                                   |                                                                                                                      | 6.0V            | 0.2                   | 0.26              | 0.33                         |    |       |
|                 |                                   |                                                                                                                      |                 |                       |                   |                              |    |       |
| I <sub>IN</sub> | Maximum Input Current             | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                             | 6.0V            |                       | ±0.1              | ±1.0                         | μA |       |
| I <sub>CC</sub> | Maximum Quiescent Supply Current  | V <sub>IN</sub> = V <sub>CC</sub> or GND<br>I <sub>OUT</sub> = 0 μA                                                  | 6.0V            |                       | 8.0               | 80                           | μA |       |

**Note 5:** For a power supply of 5V  $\pm 10\%$  the worst case output voltages ( $V_{OH}$ , and  $V_{OL}$ ) occur for HC at 4.5V. Thus the 4.5V values should be used when designing with this supply. Worst case  $V_{IH}$  and  $V_{IL}$  occur at  $V_{CC} = 5.5V$  and 4.5V respectively. (The  $V_{IH}$  value at 5.5V is 3.85V.) The worst case leakage current ( $I_{IN}$ ,  $I_{CC}$ , and  $I_{OZ}$ ) occur for CMOS at the higher voltage and so the 6.0V values should be used.


**AC Electrical Characteristics**
 $V_{CC} = 5V$ ,  $T_A = 25^\circ C$ ,  $C_L = 15 \text{ pF}$ ,  $t_r = t_f = 6 \text{ ns}$ 

| Symbol                | Parameter                                                                  | Conditions | Typ | Guaranteed Limit | Units |
|-----------------------|----------------------------------------------------------------------------|------------|-----|------------------|-------|
| $t_{PHL}$ , $t_{PLH}$ | Maximum Propagation Delay, $\overline{G1}$ , $\overline{G2}$ or A, B, C, D |            | 21  | 32               | ns    |

**AC Electrical Characteristics**
 $V_{CC} = 2.0V$  to  $6.0V$ ,  $C_L = 50 \text{ pF}$ ,  $t_r = t_f = 6 \text{ ns}$  (unless otherwise specified)


| Symbol                              | Parameter                                                                   | Conditions | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = −40 to 85°C | Units |
|-------------------------------------|-----------------------------------------------------------------------------|------------|-----------------|-----------------------|-------------------|------------------------------|-------|
|                                     |                                                                             |            |                 | Typ                   | Guaranteed Limits |                              |       |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, $\overline{G1}$ or $\overline{G2}$ or A, B, C, D |            | 2.0V            | 63                    | 160               | 190                          | ns    |
|                                     |                                                                             |            | 4.5V            | 24                    | 36                | 42                           |       |
|                                     |                                                                             |            | 6.0V            | 20                    | 30                | 35                           |       |
| t <sub>TLH</sub> , t <sub>THL</sub> | Maximum Output Rise and Fall Time                                           |            | 2.0V            | 25                    | 75                | 95                           | ns    |
|                                     |                                                                             |            | 4.5V            | 7                     | 15                | 19                           |       |
|                                     |                                                                             |            | 6.0V            | 6                     | 13                | 16                           |       |
| C <sub>PD</sub>                     | Power Dissipation Capacitance (Note 6)                                      |            |                 | 90                    |                   |                              | pF    |
| C <sub>IN</sub>                     | Maximum Input Capacitance                                                   |            |                 | 5                     | 10                | 10                           | pF    |

**Note 6:**  $C_{PD}$  determines the no load dynamic power consumption,  $P_D = C_{PD} V_{CC}^2 f + I_{CC} V_{CC}$ , and the no load dynamic current consumption,  $I_S = C_{PD} V_{CC} f + I_{CC}$ .




**24-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  
Package Number M24B**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



24-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  
Package Number MTC24

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



N24C (REV F)

24-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide  
Package Number N24C

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)