


LOC	D1ST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
GP	00				H	REV PER 0U1D-0274-00	22 OCT 01	JR
					J	REV PER EC 0UE0-0002-01	10 JAN 02	JR



1. PARTS PACKAGED UNASSEMBLED.
2. PARTS PACKAGED AS A UNIT KIT.
3. PARTS INDIVIDUALLY BULK PACKAGED & SHIPPED AS A UNIT PACKAGE.
4. ZINC PLATED PER ASTM B633, TYPE III, CLASS SC1, CLEAR CHROMATE.
5. ZINC PLATED PER ASTM B633, TYPE II, CLASS SC1, YELLOW CHROMATE.
6. THIS KIT CAN BE USED WITH TWO-PIECE STRAIGHT/90° EXIT CABLE CLAMPS, RF1/EMI CABLE CLAMPS OR UNIVERSAL CABLE CLAMPS.
7. THIS KIT CAN BE USED WITH STRAIGHT/45° EXIT ONE-PIECE CABLE CLAMPS, STRAIGHT/90° EXIT ONE-PIECE CABLE CLAMPS, OR ON CONNECTORS WITHOUT CABLE CLAMPS.

7	SUPERSEDED BY 745578-3	.415	5	#4-40	3	745578-4
		.415	5	#4-40	2	745578-3
6	OBSOLETE	.547	4	#2-56	3	745578-2
6	OBSOLETE	.547	4	#2-56	2	745578-1

		A	HARDWARE FINISH	THREAD TYPE	PACKAGING	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .010 ANGLES ± -	DR 8-12-88 L SIPE	AMP AMP INCORPORATED Harrisburg, Pa. 17105 KIT, SLIDE LATCH, SIZE 5, 50 POSITION, AMPLIMITE®				
	CHK 8-12-88 W LENKER					
	APPD 8-15-88 R WHYNE					
	APPD 8-16-88 J SHOWERS					
MATERIAL	PRODUCT SPEC					
SLIDE LATCH: STAINLESS STEEL HARDWARE: STEEL PER ASTM A108	-					
FINISH	APPLICATION SPEC	SIZE	FSCM NO	DRAWING NO		
HARDWARE: SEE TABLE	-	C	00779	745578		
	WEIGHT -	SCALE	4:1	SHEET 1 OF 1		