


$B \pm .01 (.25)$ 

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE ^{lbs.} (N)	CROSS SECTION	WEIGHT ^{lbs.} /100 pcs. (g)
	MIN. ⁱⁿ (mm)	MAX. ⁱⁿ (mm)									
BT2LH	.188 (4.8)	2.00 (51)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	8.7 (221)	120 (534)	LIGHT HEAVY	.59 (267)
BT3LH	.188 (4.8)	3.00 (76)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	11.8 (300)	120 (534)	LIGHT HEAVY	.79 (358)
BT4LH	.188 (4.8)	4.00 (102)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	14.9 (378)	120 (534)	LIGHT HEAVY	.99 (449)
BT5LH	.188 (4.8)	5.00 (127)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	18.1 (460)	120 (534)	LIGHT HEAVY	1.19 (540)
BT6LH	.188 (4.8)	6.00 (152)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	21.2 (538)	120 (534)	LIGHT HEAVY	1.39 (631)
BT7LH	.188 (4.8)	7.00 (178)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	24.4 (620)	120 (534)	LIGHT HEAVY	1.59 (722)
BT8LH	.188 (4.8)	8.00 (203)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	27.5 (699)	120 (534)	LIGHT HEAVY	1.79 (813)
BT9LH	.188 (4.8)	9.00 (229)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	30.7 (780)	120 (534)	LIGHT HEAVY	1.99 (904)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm .10$ (.5) (XXX) $\pm .020$ (.5)
(.XX) $\pm .02$ (.5) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
PMH

MAT'L:

SCALE

NONE

DATE
6-24-93

NYLON 6.6

DRAWING NO.

BT-0037

SHT. 3 OF 3

DWG
A
SIZE

6	5/2/06	JABO		REMOVED CURVED TIP REFERENCE & TIP STYLE COLUMN	BT-0037	6			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		