


LOC	DIST	REVISIONS					
CM	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			T2	REVISED PER ECR-15-006687	26OCT2015	NK	NL



- 2 CONTACTS ACCEPT 22 AWG WIRE WITH 2.41[.095] MAX INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 1.14±0.03[.045±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.

5 DIMENSIONS IN BRACKETS ARE IN INCHES.

 NOTE DELETED.

9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

		TIN	95.10 [3.744]	24	5-641150-4
			91.14 [3.588]	23	5-641150-3
			87.17 [3.432]	22	5-641150-2
			83.21 [3.276]	21	5-641150-1
			79.25 [3.120]	20	5-641150-0
			75.29 [2.964]	19	4-641150-9
			71.32 [2.808]	18	4-641150-8
			67.36 [2.652]	17	4-641150-7
			63.40 [2.496]	16	4-641150-6
			59.44 [2.340]	15	4-641150-5
			55.47 [2.184]	14	4-641150-4
			51.51 [2.028]	13	4-641150-3
			47.55 [1.872]	12	4-641150-2
			43.59 [1.716]	11	4-641150-1
			39.62 [1.560]	10	4-641150-0
			35.66 [1.404]	9	3-641150-9
			31.70 [1.248]	8	3-641150-8
			27.74 [1.092]	7	3-641150-7
			23.77 [.936]	6	3-641150-6
			19.81 [.780]	5	3-641150-5
			15.85 [.624]	4	3-641150-4
			11.89 [.468]	3	3-641150-3
			7.92 [.312]	2	3-641150-2
SUPERSEDED 	TIN-LEAD		95.10 [3.744]	24	2-641150-4
			91.14 [3.588]	23	2-641150-3
			87.17 [3.432]	22	2-641150-2
			83.21 [3.276]	21	2-641150-1
			79.25 [3.120]	20	2-641150-0
			75.29 [2.964]	19	1-641150-9
			71.32 [2.808]	18	1-641150-8
			67.36 [2.652]	17	1-641150-7
			63.40 [2.496]	16	1-641150-6
			59.44 [2.340]	15	1-641150-5
			55.47 [2.184]	14	1-641150-4
			51.51 [2.028]	13	1-641150-3
			47.55 [1.872]	12	1-641150-2
OBSOLETE	TIN		43.59 [1.716]	11	1-641150-1
SUPERSEDED 	TIN-LEAD		39.62 [1.560]	10	1-641150-0
			35.66 [1.404]	9	641150-9
			31.70 [1.248]	8	641150-8
			27.74 [1.092]	7	641150-7
OBSOLETE	TIN		23.77 [.936]	6	641150-6
OBSOLETE			19.81 [.780]	5	641150-5
OBSOLETE			15.85 [.624]	4	641150-4
OBSOLETE			11.89 [.468]	3	641150-3
OBSOLETE			7.92 [.312]	2	641150-2
	CONTACT FINISH	DIM A	NO. OF CIRCUITS	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		FINISH D. LEWIS 2-12-91		 TE Connectivity	
		CHK R. SWING 2-12-91			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-156 CONNECTOR ASSEMBLY, 22 AWG, STANDARD —	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13 [.005] 4 PLC ± — ANGLES ± —			
MATERIAL 		FINISH —			
		APVD — PRODUCT SPEC 108-1051 APPLICATION SPEC 114-1020		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-641150	
				RESTRICTED TO —	
				SCALE 4:1 SHEET 1 OF 1 REV T2	