

PA847C04 (40A)

(45V / 40A)

Schottky barrier diode

Major characteristics

Characteristics	PA847C04	Units	Condition
V_{RRM}	45	V	
V_F	0.38	V	$T_j=125^{\circ}\text{C}$, typ
I_o	40	A	

Features

- Low V_F
- Optimized for 3.3V
- 5V output application
- Center tap connection

Applications

- High frequency operation
- DC-DC converters
- AC adapter

Maximum ratings and characteristics

- Absolute maximum ratings

Item	Symbol	Conditions	Rating	Unit
Repetitive peak surge reverse voltage	V_{RSM}	$t_w=500\text{ns}$, $\text{duty}=1/40$	45	V
Repetitive peak reverse voltage	V_{RRM}		45	V
Average output current	I_o	Square wave, $\text{duty}=1/2$ $T_c=102^{\circ}\text{C}$	40 *	A
Non-repetitive surge current	I_{FSM}	Sine wave 10ms, 1shot	250	A
Operating junction temperature	T_j		+150	$^{\circ}\text{C}$
Storage temperature	T_{stg}		-40 to +150	$^{\circ}\text{C}$

* Average output current at centertap full wave connection


- Electrical characteristics ($T_c=25^{\circ}\text{C}$ Unless otherwise specified)

Item	Symbol	Conditions	Max.	Unit
Forward voltage drop	V_F	$I_{FM}=16\text{A}$	0.55	V
Reverse current	I_R	$V_R=V_{RRM}$	8.0	mA


- Electrical characteristics ($T_c=25^{\circ}\text{C}$ Unless otherwise specified)

Item	Symbol	Condition	Max.	Unit
Thermal resistance	$R_{th(j-c)}$	Junction to case	1.2	$^{\circ}\text{C/W}$

Outline drawings, mm




Connection diagram




Characteristics


Forward Characteristic (typ.)





Reverse Characteristic (typ.)



Forward Power Dissipation



Reverse Power Dissipation

Current Derating (I_o - T_c)

λ : Conduction angle of forward current for each rectifier element
 I_o : Output current of center-tap full wave connection

Junction Capacitance Characteristic (typ.)

