

	10	9	8	7	6	5	4	3	2	19016
	MATERIAL NUMBER	ENGINEERING NUMBER	TAPE MATERIAL NUMBER	TAPE ENGINEERING NUMBER	WIRE RANGE AWG MM ²	FITS MALE TAB SIZE	"L" MAX.	"B" ±.01/(±0.3)	"H" ±.01/(±0.3)	
F	190160112	M-1133	190160097	M-1133T	26-24 0.1 -0.3	.110x.032 (2.80 X 0.81)	.53 (13.5)	.16 (4.1)	.08 (2.0)	
	190160037	BB-1135	190160038	BB-1135T	16-14 1.0-2.6	.110x.032 (2.80 X 0.81)	.57 (14.5)	.20 (5.1)	.08 (2.0)	
	190160075	M-1130	190160076	M-1130T	26-24 0.1 -0.3	.110x.020 (2.80 X 0.51)	.53 (13.5)	.16 (4.1)	.07 (1.8)	
	190160035	BB-1132	190160036	BB-1132T	16-14 1.0-2.6	.110x.020 (2.80 X 0.51)	.57 (14.5)	.20 (5.1)	.07 (1.8)	



E

D

C

B

A



PARTS ON TAPE

NOTES:

- MATERIAL: BRASS .012 (.30) THK.
FINISH: ELECTRO-TIN PLATING

WAS: CD-1903 EC NO: ETC2005-0016 DRWN: BENDERLE 2004/07/29 CHKD: BENDERLE 2004/07/29 APPR: RDEROSS 2004/07/29	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE NONE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		REVISE ON CAD ONLY		
		 = 0	mm	INCH	DIMENSION STYLE IN/MM		TITLE KRIMPTITE QUICK DISCONNECTS				
			4 PLACES	± ---	± ---	DRAWN BY DATE BENDERLE 2004/07/26					
			3 PLACES	± ---	± ---	CHECKED BY DATE R DEROSS 2004/07/26					
			2 PLACES	± ---	± ---	APPROVED BY DATE R DEROSS 2004/07/26					
	REV	 = 0	1 PLACE	± ---	± ---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19016-001	SHEET NO. 1 OF 1		
			ANGULAR ± --- °				MOLEX INCORPORATED				
			DRAFT WHERE APPLICABLE				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
			MUST REMAIN WITHIN DIMENSIONS				B				

F

E

D

C

B

A

B