

12 W BTL OR 2 × 6 WATT STEREO CAR RADIO POWER AMPLIFIER

GENERAL DESCRIPTION

The TDA1519B is an integrated class-B dual output amplifier in a 9-lead single in-line (SIL) plastic medium power package. The device is primarily developed for car radio applications.

Features

- Requires very few external components for Bridge Tied Load (BTL)
- Stereo or BTL application
- High output power
- Low offset voltage at output (important for BTL)
- Fixed gain
- Good ripple rejection
- Mute/stand-by switch
- Load dump protection
- AC and DC short-circuit-safe to ground and V_p
- Thermally protected
- Reverse polarity safe
- Capability to handle high energy on outputs ($V_p = 0$ V)
- No switch-on/switch-off pop
- Protected against electrostatic discharge
- Identical inputs (inverting and non-inverting)
- Compatible with TDA1519A (except output power)

QUICK REFERENCE DATA

parameter	conditions	symbol	min.	typ.	max.	unit
Supply voltage range						
operating		V_p	6.0	14.4	18.0	V
non-operating		V_p	—	—	30	V
load dump protected		V_p	—	—	45	V
Repetitive peak output current		I_{ORM}	—	—	2.5	A
Total quiescent current		I_{tot}	—	40	80	mA
Stand-by current		I_{sb}	—	0.1	100	μ A
Switch-on current		I_{sw}	—	—	40	μ A
Input impedance						
BTL		$ Z_I $	25	—	—	k Ω
stereo		$ Z_I $	50	—	—	k Ω
Stereo application						
Output power	THD = 5%; 4 Ω THD = 10%; 4 Ω	P_o	—	5	—	W
Channel separation		P_o	—	6	—	W
Noise output voltage		α	40	—	—	dB
BTL application		$V_{no(rms)}$	—	150	—	μ V
Output power	THD = 10%; 8 Ω	P_o	—	12	—	W
Supply voltage ripple rejection	$R_S = 0$ Ω $f = 100$ Hz $f = 1$ kHz to 10 kHz	RR	34	—	—	dB
DC output offset voltage		RR	48	—	—	dB
Crystal temperature		$ \Delta V_O $	—	—	250	mV
		T_c	—	—	150	$^{\circ}$ C

PACKAGE OUTLINE

9-lead SIL; plastic (SOT110B).

PINNING

- | | | |
|---|----------------|---------------------------------|
| 1 | NINV | non-inverting input |
| 2 | GND1 | ground (signal) |
| 3 | RR | supply voltage ripple rejection |
| 4 | OUT1 | output 1 |
| 5 | GND2 | ground (substrate) |
| 6 | OUT2 | output 2 |
| 7 | V _P | positive supply voltage |
| 8 | M/SS | mute/stand-by switch |
| 9 | INV | inverting input |




Fig.1 Block diagram.

FUNCTIONAL DESCRIPTION

The TDA1519B contains two identical amplifiers with differential input stages. The gain of each amplifier is fixed at 40 dB. A special feature of this device is the mute/stand-by switch which has the following features:

- Low stand-by current ($< 100 \mu\text{A}$)
- Low mute/stand-by switching current (low cost supply switch)
- Mute condition

RATINGS

Limiting values in accordance with the Absolute Maximum System (IEC 134)

parameter	conditions	symbol	min.	max.	unit
Supply voltage					
operating		V_P	—	18	V
non-operating		V_P	—	30	V
load dump protected	during 50 ms; $t_r \geq 2.5 \text{ ms}$	V_P	—	45	V
AC and DC short-circuit-safe voltage		V_{PSC}	—	18	V
Reverse polarity		V_{PR}	—	6	V
Energy handling capability at outputs	$V_P = 0 \text{ V}$		—	200	mJ
Non-repetitive peak output current		I_{OSM}	—	4	A
Repetitive peak output current		I_{ORM}	—	2.5	A
Total power dissipation	see Fig.2	P_{tot}	—	15	W
Crystal temperature		T_c	—	150	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-55	+150	$^{\circ}\text{C}$




Fig.2 Power derating curve.

DC CHARACTERISTICS

$V_p = 14.4 \text{ V}$; $T_{amb} = 25 \text{ }^\circ\text{C}$; measurements taken using Fig.3; unless otherwise specified

parameter	conditions	symbol	min.	typ.	max.	unit
Supply						
Supply voltage range	note 1	V _P	6.0	14.4	18.0	V
Total quiescent current		I _{tot}	—	40	80	mA
DC output voltage	note 2	V _O	—	6.95	—	V
DC output offset voltage		ΔV ₄₋₆	—	—	250	mV
Mute/stand-by switch						
Switch-on voltage level		V _{ON}	8.5	—	—	V
Mute condition						
Output signal in mute position	V _I = 1 V (max.); f = 20 Hz to 15 kHz	V _{mute}	3.3	—	6.4	V
		V _O	—	—	20	mV
DC output offset voltage		ΔV ₄₋₆	—	—	250	mV
		V _{sb}	0	—	2	V
Stand-by condition						
DC current in stand-by condition		I _{sb}	—	—	100	μA
Switch-on current		I _{sw}	—	12	40	μA

AC CHARACTERISTICS

$V_p = 14.4 \text{ V}$; $R_L = 4 \Omega$; $f = 1 \text{ kHz}$; $T_{amb} = 25 \text{ }^\circ\text{C}$; measurements taken using Fig.3; unless otherwise specified

parameter	conditions	symbol	min.	typ.	max.	unit
Stereo application						
Output power	note 3					
	THD = 0.5%	P_O	4	5	—	W
	THD = 10%	P_O	5.5	6.0	—	W
Output power at $V_p = 13.2 \text{ V}$	note 3					
	THD = 0.5%	P_O	—	3.5	—	W
	THD = 10%	P_O	—	4.8	—	W
Total harmonic distortion	$P_O = 1 \text{ W}$	THD	—	0.1	—	%
Low frequency roll-off	note 4					
	-3 dB	f_L	—	45	—	Hz
High frequency roll-off	-1 dB	f_H	20	—	—	kHz
Closed loop voltage gain		G_v	39	40	41	dB
Supply voltage ripple rejection						
ON	notes 5 and 6	RR	40	—	—	dB
ON	notes 5 and 7	RR	45	—	—	dB
mute	notes 5, 6 and 7	RR	45	—	—	dB
stand-by	notes 5, 6 and 7	RR	80	—	—	dB
Input impedance		$ Z_i $	50	60	75	$k\Omega$
Noise output voltage (RMS value)	note 8					
ON	$R_S = 0 \Omega$	$V_{no(rms)}$	—	150	—	μV
ON	$R_S = 10 \text{ k}\Omega$	$V_{no(rms)}$	—	250	500	μV
mute	note 9	$V_{no(rms)}$	—	120	—	μV
Channel separation	$R_S = 10 \text{ k}\Omega$	α	40	—	—	dB
Channel unbalance		$ \Delta G_v $	—	0.1	1	dB

AC CHARACTERISTICS

$V_p = 14.4 \text{ V}$; $R_L = 8 \Omega$; $f = 1 \text{ kHz}$; $T_{amb} = 25^\circ \text{C}$; measurements taken using Fig.4; unless otherwise specified

parameter	conditions	symbol	min.	typ.	max.	unit
BTL application						
Output power	note 3					
	THD = 0.5%	P_o	8	10	—	W
	THD = 10%	P_o	11	12	—	W
Output power at $V_p = 13.2 \text{ V}$	note 3					
	THD = 0.5%	P_o	—	7.5	—	W
	THD = 10%	P_o	—	10	—	W
Total harmonic distortion	$P_o = 1 \text{ W}$	THD	—	0.1	—	%
Power bandwidth	THD = 0.5%;					
	$P_o = -1 \text{ dB}$; w.r.t. 15 W	B_w	—	35 to 15 000	—	Hz
Low frequency roll-off	note 4					
	-1 dB	f_L	—	45	—	Hz
High frequency roll-off	-1 dB	f_H	20	—	—	kHz
Closed loop voltage gain		G_v	45	46	47	dB
Supply voltage ripple rejection	notes 5 and 6	RR	34	—	—	dB
	ON	RR	48	—	—	dB
	mute	RR	48	—	—	dB
	stand-by	RR	80	—	—	dB
	notes 5, 6 and 7	RR	80	—	—	dB
Input impedance		$ Z_i $	25	30	38	$k\Omega$
Noise output voltage (RMS value)	note 8					
	$R_S = 0 \Omega$	$V_{no(rms)}$	—	200	—	μV
	$R_S = 10 k\Omega$	$V_{no(rms)}$	—	350	700	μV
	note 9	$V_{no(rms)}$	—	180	—	μV
	mute					

Notes to the characteristics

1. The circuit is DC adjusted at $V_p = 6\text{ V}$ to 18 V and AC operating at $V_p = 8.5\text{ V}$ to 18 V .
2. At $18\text{ V} < V_p < 30\text{ V}$ the DC output voltage $\leq V_p/2$.
3. Output power is measured directly at the output pins of the IC.
4. Frequency response externally fixed.
5. Ripple rejection measured at the output with a source impedance of $0\ \Omega$ (maximum ripple amplitude of 2 V).
6. Frequency $f = 100\text{ Hz}$.
7. Frequency between 1 kHz and 10 kHz .
8. Noise voltage measured in a bandwidth of 20 Hz to 20 kHz .
9. Noise output voltage independent of R_S ($V_I = 0\text{ V}$).

APPLICATION INFORMATION




Fig.3 Stereo application circuit diagram.




Fig.4 BTL application circuit diagram.




Fig.5 Total quiescent current (I_{tot}) as a function of supply voltage (V_P).




Fig.6 Output power (P_O) as a function of supply voltage (V_P) for stereo application at $R_L = 4 \Omega$, $f = 1$ kHz.




Fig.7 Total harmonic distortion (THD) as a function of output power (P_O) for stereo application at $R_L = 4 \Omega$, $f = 1$ kHz.




Fig.8 Total harmonic distortion (THD) as a function of operating frequency (f) for stereo application at $R_L = 4 \Omega$, $P_O = 1$ W.