





-
- 9.8±0.2
- GROUND CONTACT
15 PLC
- 4.80
- GROUND CONTACT,
CONTACT AREA
TYP
- 3.70
- COMPLIANT PIN AREA
TYP
- 1.80
- COMPLIANT PIN AREA
TYP
- 17.00
- 12.50
- GROUND
CONTACT
QTY: 15
- 1.50
TYP
- 7.00
TYP
- 3.50
TYP
- 2.00
TYP
- 3.0^{+0.2}₀
- 11.80±0.18

4805 (3/11)