



IR Emitter and Detector Product Data Sheet

LTR-546AB

Spec No.: DS-50-98-0010

Effective Date: 05/18/2010

Revision: B

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics


No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.

Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660

<http://www.liteon.com/opto>

FEATURES

- * HIGH PHOTO SENSITIVITY
- * SUITABLE FOR INFRARED RADIATION
- * LOW JUNCTION CAPACITANCE
- * HIGH CUT-OFF FREQUENCY
- * FAST SWITCHING TIME
- * THE LTR-546AB IS A SPECIAL DARK BLUE PLASTIC PACKAGE THAT CUT THE VISIBLE LIGHT AND SUITABLE FOR THE DETECTORS OF INFRARED APPLICATIONS

PACKAGE DIMENSIONS**NOTES:**

1. All dimensions are in millimeters (inches).
2. Tolerance is ± 0.25 mm (.010") unless otherwise noted.
3. Protruded resin under flange is 1.5 mm (.059") max.
4. Lead spacing is measured where the leads emerge from the package.
5. Specifications are subject to change without notice.



LITE-ON TECHNOLOGY CORPORATION.

Property of Lite-On Only

ABSOLUTE MAXIMUM RATINGS AT TA=25°C

PARAMETER	MAXIMUM RATING	UNIT
Power Dissipation	150	mW
Reverse Voltage	30	V
Operating Temperature Range	-40°C to + 85°C	
Storage Temperature Range	-55°C to + 100°C	
Lead Soldering Temperature [1.6mm(.063") From Body]	260°C for 5 Seconds	

ELECTRICAL OPTICAL CHARACTERISTICS AT TA=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Reverse Break Down Voltage	$V_{(BR)R}$	30			V	$I_R = 100 \mu A$ $E_e = 0mW/cm^2$
Reverse Dark Current Voltage	$ID(R)$			30	nA	$V_R = 10V$ $E_e = 0mW/cm^2$
Open Circuit Voltage	V_{OC}		350		mV	$\lambda = 940nm$ $E_e = 0.5mW/cm^2$
Rise Time	T_r		50		nsec	$V_R = 10V$ $\lambda = 940nm$ $R_L = 1K\Omega$
Fall Time	T_f		50		nsec	
Short Circuit Current	I_s	1.7	2		μA	$V_R = 5V$ $\lambda = 940nm$ $E_e = 0.1mW/cm^2$
Total Capacitance	C_T		25		pF	$V_R = 3V$ $f = 1MHz$ $E_e = 0mW/cm^2$
Wavelength of the Max Sensitivity	λ_{SMAX}		900		nm	

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 DARK CURRENT VS.
REVERSE VOLTAGE
TA=25° C, Ee=0 mW/cm²




Fig.2 CAPACITANCE VS.
REVERSE VOLTAGE
F=1MHZ; Ee=0mW/cm²




Fig.3 PHOTOCURRENT VS.
AMBIENT TEMPERATURE




Fig.4 DARK CURRENT
AMBIENT TEMPERATURE
VR=10, Ee=0mW/cm²

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.5 RELATIVE SPECTRAL SENSITIVITY VS WAVELENGTH




Fig.6 PHOTOCURRENT VS IRRADIANCE $\lambda = 940 \text{ nm}$




Fig.7 SENSITIVITY DIAGRAM




Fig.8 TOTAL POWER DISSIPATION VS AMBIENT TEMPERATURE