



LOC	DIST	REVISIONS			
AD	00	P	LTR	DESCRIPTION	DATE
					DWN
					APVD
		K1		REVISED ECO-09-024927	06NOV09
					KK
					AEG





SECTION X-X



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).
- 2 TOLERANCE NON-CUMULATIVE.
- 3 THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED BOARD MOUNTING
(RECOMMENDED BOARD THICKNESS: .055-.070)



OBSOLETE 4	3.120	2.964	20	-2-87986-0-
	2.964	2.808	19	-1-87986-9-
	2.808	2.652	18	-1-87986-8-
	2.652	2.496	17	-1-87986-7-
	2.496	2.340	16	-1-87986-6-
	2.340	2.184	15	-1-87986-5-
	2.184	2.028	14	1-87986-4
4 OBSOLETE	2.028	1.872	13	-1-87986-3-
	1.872	1.716	12	1-87986-2
4 OBSOLETE	1.716	1.560	11	-1-87986-1-
	1.560	1.404	10	1-87986-0
OBSOLETE 4	1.404	1.248	9	-87986-9-
	1.248	1.092	8	-87986-8-
	1.092	.936	7	87986-7
	.936	.780	6	87986-6
	.780	.624	5	87986-5
	.624	.468	4	87986-4
4 OBSOLETE	.468	.312	3	-87986-3-
	.312	.156	2	87986-2
	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17MAR86	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		L D RINGLEY	18MAR86		
		P deJONG	18MAR86		
		P deJONG	18MAR86		
		APVD	18MAR86	NAME	
		PRODUCT SPEC		ASSY, MOD I, BOARD MOUNT RECP, .156 CL, STD PRESSURE, TYPE B, FOR ROUND HOLE MOUNTING	
		108-25,016			
		APPLICATION SPEC			
		114-25,004			
		WEIGHT	114-25,004		
		CUSTOMER DRAWING			
		SCALE	5:1		
		SHEET	1		
		OF	1		
		REV	K1		