


IEC Interconnection Cord with IEC Connector C13, V-Lock, straight

new



Description

1 Function:

- Interconnection Cord,
- Protection class I, Pin temperature 70 °C,
- with V-Lock interlocking system

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data

Ratings IEC	10A / 250VAC; 50 Hz
Dielectric Strength	> 2 kVDC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	moulded
Material: Housing	PVC, black

Connector	C13 acc. to IEC 60320 IEC 60320-1 UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I
-----------	--

All Variants

Connector cable						Plug					Order Number
Type	V-Lock	Cord Type	Conductor cross section	Length [m]	Color	Type	Country	Standard	Style	Index	
C13	●	H05VV-F3G0.75	3 x 0.75 mm²	0.6	black	Interconnection	INT	IEC 60320-2-2	straight	-	6051.2037

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 150 Pcs

Mating Outlets/Connectors

Category / Description



[Appliance Outlet Overview complete](#)

IEC Appliance Outlet F, Screw-on Mounting, Front Side, Solder or Quick-connect Terminal	6600-3
IEC Appliance Outlet F, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	6600-4
IEC Appliance Outlet H, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	6602-4
IEC Appliance Outlet F, Snap-in Mounting, Front Side, IDC Terminal	6610

[Appliance Outlet further types to VAC13KS](#)

Mating Inlets/Plugs shuttered

Appliance Inlet Overview complete



IEC Appliance Inlet C14, Snap-in Mounting, Solder, Quick-connect, Screw or PCB Terminal	6010
IEC Appliance Inlet C14, Screw-on Mounting, Front or Rear Side, Solder or Quick-connect or Screw-on Terminal	6048
IEC Appliance Inlet C14, Screw-on Mounting, Front Side, Solder or Quick-connect, Screw Terminal	6061
IEC Appliance Inlet C14 or C18, Screw-on Mounting, Rear Side, PCB terminals	GSP1
IEC Appliance Inlet C14 or C18, sandwich Mounting, PCB- or Solder Terminal	GSP2

[Appliance Inlet further types to VAC13KS](#)

Power Entry Module Overview complete



IEC Appliance Inlet C14 or C18 with Fuseholder 1- or 2-pole	4707
IEC Appliance Inlet C14 with Circuit Breaker TA35 2-pole	6135
IEC Appliance Inlet C14 or C18 with Circuit Breaker TA45	6145
IEC Appliance Inlet C14, with Line Switch 2-pole, Voltage Selector and Fuseholder 1or 2-pole	6766
IEC Appliance Inlet C14 or C18 with Line Switch 1- or 2-pole	DC11

[Power Entry Module further types to VAC13KS](#)

...

Power Entry Module with line filter Overview complete



IEC Appliance Inlet C14 or C18 with Filter, ECO design, Front- or Rear Side Mounting	5120
IEC Appliance Inlet C14 or C18 with Filter, high attenuation, ECO design, Front- or Rear Side Mounting	5123
IEC Appliance Inlet C20 with Filter, ECO design, front or rear side Mounting	5130
IEC Appliance Inlet C14 with Filter, Circuit Breaker TA45	5145
IEC Appliance Inlet C14 with High Frequency Filter, X2Y Technology, ECO design, Front- or Rear Side Mounting	5150

[Power Entry Module with line filter further types to VAC13KS](#)

...