



## NYLON RETAINING SPACERS

Similar to our standard spacers, but with a specially configured I.D. designed to grip the outside of the screw shank. The spacer slides on the screw easily, but is retained on the screw. For use in applications requiring pre-assembly of the screw and spacer, to reduce final assembly cost.




| CAT. NO. | .156 (3.9) Clear Hole for #4 Screw |            |            |
|----------|------------------------------------|------------|------------|
| LENGTH   | O.D.                               | I.D.       |            |
| 2341     | .125 (3.2)                         |            |            |
| 2342     | .250 (6.4)                         |            |            |
| 2343     | .375 (9.5)                         |            |            |
| 2344     | .500 (12.7)                        | .250 (6.4) | .102 (2.6) |
| 2345     | .625 (15.9)                        |            |            |
| 2346     | .750 (19.1)                        |            |            |
| 2347     | .875 (22.2)                        |            |            |
| 2348     | 1.00 (25.4)                        |            |            |

| CAT. NO. | .198 (5.0) Clear Hole for #6 Screw |            |            |
|----------|------------------------------------|------------|------------|
| LENGTH   | O.D.                               | I.D.       |            |
| 2361     | .125 (3.2)                         |            |            |
| 2362     | .250 (6.4)                         |            |            |
| 2363     | .375 (9.5)                         |            |            |
| 2364     | .500 (12.7)                        | .312 (7.9) | .128 (3.3) |
| 2365     | .625 (15.9)                        |            |            |
| 2366     | .750 (19.1)                        |            |            |
| 2367     | .875 (22.2)                        |            |            |
| 2368     | 1.00 (25.4)                        |            |            |

| CAT. NO. | .240 (6.1) Clear Hole for #8 Screw |            |            |
|----------|------------------------------------|------------|------------|
| LENGTH   | O.D.                               | I.D.       |            |
| 2381     | .125 (3.2)                         |            |            |
| 2382     | .250 (6.4)                         |            |            |
| 2383     | .375 (9.5)                         |            |            |
| 2384     | .500 (12.7)                        | .375 (9.5) | .152 (3.8) |
| 2385     | .625 (15.9)                        |            |            |
| 2386     | .750 (19.1)                        |            |            |
| 2387     | .875 (22.2)                        |            |            |
| 2388     | 1.00 (25.4)                        |            |            |

| CAT. NO. | .277 (7.0) Clear Hole for #10 Screw |             |            |
|----------|-------------------------------------|-------------|------------|
| LENGTH   | O.D.                                | I.D.        |            |
| 2391     | .125 (3.2)                          |             |            |
| 2392     | .250 (6.4)                          |             |            |
| 2393     | .375 (9.5)                          |             |            |
| 2394     | .500 (12.7)                         | .500 (12.7) | .177 (4.5) |
| 2395     | .625 (15.9)                         |             |            |
| 2396     | .750 (19.1)                         |             |            |
| 2397     | .875 (22.2)                         |             |            |
| 2398     | 1.00 (25.4)                         |             |            |

## HINGED STANDOFFS



- Applications unlimited
- Time saving
- Space saving
- Interconnect circuits or services without danger of shorting

### MATERIAL:


Brass, ASTM-B16. Zinc Plate and Yellow Chromate



### FEMALE/FEMALE




| CAT. NO. | L LENGTH     | U          | P           | D DIAMETER | T THREAD |
|----------|--------------|------------|-------------|------------|----------|
| 351      | .750 (19.1)  | .172 (4.4) | .375 (9.5)  | .187 (4.7) | 4-40     |
| 352      | 1.000 (25.4) | .250 (6.4) | .625 (15.9) |            |          |
| 330      | 1.250 (31.8) | .250 (6.4) | .625 (15.9) |            |          |
| 353      | .750 (19.1)  | .172 (4.4) | .375 (9.5)  |            |          |
| 354      | 1.000 (25.4) | .250 (6.4) | .625 (15.9) | .250 (6.4) | 6-32     |
| 331      | 1.250 (31.8) | .250 (6.4) | .625 (15.9) |            |          |
| 355      | .750 (19.1)  | .172 (4.4) | .375 (9.5)  |            |          |
| 356      | 1.000 (25.4) | .250 (6.4) | .625 (15.9) | .250 (6.4) | 8-32     |
| 332      | 1.250 (31.8) | .250 (6.4) | .625 (15.9) |            |          |



### MALE/FEMALE



| CAT. NO. | L LENGTH    | S          | U          | D DIAMETER | T THREAD |
|----------|-------------|------------|------------|------------|----------|
| 333      | .625 (15.9) | .250 (6.4) | .172 (4.4) | .187 (4.7) | 4-40     |
| 334      | .875 (22.2) | .250 (6.4) | .250 (6.4) |            |          |
| 335      | .625 (15.9) | .312 (7.9) | .172 (4.4) |            |          |
| 336      | .875 (22.2) | .312 (7.9) | .250 (6.4) | .250 (6.4) | 6-32     |
| 337      | .625 (15.9) | .312 (7.9) | .172 (4.4) |            |          |
| 338      | .875 (22.2) | .312 (7.9) | .250 (6.4) | .250 (6.4) | 8-32     |



### MALE/MALE



| CAT. NO. | L LENGTH    | S          | P          | D DIAMETER | T THREAD |
|----------|-------------|------------|------------|------------|----------|
| 357      | .500 (12.2) | .250 (6.4) | .250 (6.4) | .187 (4.7) | 4-40     |
| 358      | .500 (12.2) | .312 (7.9) | .250 (6.4) | .250 (6.4) | 6-32     |
| 359      | .500 (12.2) | .312 (7.9) | .250 (6.4) | .250 (6.4) | 8-32     |

