


DO NOT SCALE

DIMENSIONS IN mm



METRIC

THIRD ANGLE
PROJECTION




NOTES:

- △1 FOR USE ON STANDARD APPLICATORS.(RIGHT-LEFT FEED)
- △2 FOR USE ON MINIATURE APPLICATORS.(LEFT-RIGHT FEED)
- △3 FOR USE ON MINIATURE APPLICATORS,
AMP O-MATOR APPLICATION.(LEFT-RIGHT FEED)
- △4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI





SECTION B-B



SECTION A-A

WIRE RANGE :
0,5-1,0mm ² AWG
INSULATION RANGE :
1,8-3,3mm DIA.



△4 OBSOLETE	△2	SEL. GOLD	BRASS	-8=163300=1
OBSOLETE	△3	PRE-TINPLATED	BRASS	1=163300=5
	△2	PRE-TINPLATED	PHOSPHOR BR.	163300=8
	△2	UNPLATED	PHOSPHOR BR.	163300=7
	△2	PRE-TINPLATED	BRASS	163300=6
	△2	UNPLATED	BRASS	163300=5
△4 OBSOLETE	△1	PRE-TINPLATED	PHOSPHOR BR.	163300=4
	△1	UNPLATED	PHOSPHOR BR.	163300=3
	△1	PRE-TINPLATED	BRASS	163300=2
	△1	UNPLATED	BRASS	163300=1
		PLATING	PLATING	MATERIAL
				PARTNUMBER

—	—	—	—	—	CUSTOMER DRAWING					FOR REFERENCE ONLY WILL NOT BE UPDATED		
—	—	—	—	—	 AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.					NAME SOCKET MATE-N-LOK.		
—	—	—	—	—								
—	—	—	—	—								
—	—	—	—	—								
J1	ECO-10-002990	KK	HMR	11-02-10	© COPYRIGHT 19 — BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION —,19 —							
J	H-9701	JvdH	AB	13-04-92								
LTR.	REVISION RECORD		DR.	CHK.	DATE							
DR.: J.V.D.HEIJDEN.		CHK.: A.BIJNEN.		APP.: L.V.SOEST.		DWG.No.			REV.LTR.	SHEET	A3	
DATE: 10-04-92		DATE: —		DATE: —		163300			J1	1 OF 1		