



● PCB MOUNTING LEDs - Ø 3mm




- Ideal for auto-insertion
- Complements 3 way and 8 way models
- Housing conforms to UL94 V-O flammability ratings
- Reverse polarity options available



1 2 2 SERIES

MLQ = 150




Ordering Information & Typical Technical Characteristics (Ta = 25°C)

Mean Time Between Failure = 100,000 Hours. Low Current Models 250,000 Hours. Luminous intensity figures refer to the unmodified discrete LED.

PART NUMBER	COLOUR	LENS	VOLTAGE DC Vopr	CURRENT DC Iopr	LUMINOUS INTENSITY lv@20mA	WAVE LENGTH λp	VIEWING ANGLE	OPERATING TEMP Topr	STORAGE TEMP Tstg
STANDARD INTENSITY									
122-305-01	Red	Coloured Diffused	2.0	2	35	625	Wide	-40 ~ +80	-40 ~ +80
122-311-01	Yellow		2.1	2	20	590			
122-314-01	Green		2.2	2	20	565			
122-305-04	Red		2.0*	20	35	625			
122-311-04	Yellow		2.1*	20	20	590			
122-314-04	Green		2.2*	20	20	565			
122-330-04	Red/Green	White Diffused	2.0/2.2*	20	25/25	625/565			
UNITS			Vdc	mA	mcd	nm		°C	°C

* = Voltage DC for 20mA product is Vf@20mA, not Vopr

Please contact our Sales office for multi-colour array part numbers.



● SAMPLES AVAILABLE