


KL3N14

OUTLINE DIMENSIONS



RATINGS


●Absolute Maximum Ratings

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~125	°C
Junction Temperature	T _j		125	°C
Maximum Off-State Voltage	V _{DRM}		120	V
Surge On-State Current	I _{TSM}	10/1000 μ s, Non-repetitive	30	A
		8/20 μ s, Non-repetitive	100	


●Electrical Characteristics (Tl=25°C)

Item	Symbol	Conditions	Ratings	Unit
Breakover Voltage	V _{BO}	Pulse measurement (Peak hold)	Min 130	V
Off-State Current	I _{DRM}	V _D = V _{DRM}	Max 10	μ A
Holding Current	I _H	Pulse measurement	Min 100(180)	mA
On-State Voltage	V _T	I _T = 2A	TYP 1.8	V
Junction Capacitance	C _j	f = 1kHz OSC = 1V, V _D = 50V	Max 50	pF
Clamping Voltage	V _{CL}	dv/dt = 100V/ μ s	Max 195	V


KL3N14 On-State Voltage - On-State Current




KL3N14 Breakover Voltage - Junction Temperature




KL3N14 Holding Current - Junction Temperature



KL3N14 Junction Capacitance



KL3N14 Junction Capacitance



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Shindengen:

[KL3N14-5103](#) [KL3N14-4073](#) [KL3N14-4063](#) [KL3N14-5063](#) [KL3N14-5073](#) [KL3N14-4103](#)