



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

.25 [6.3] DIA
THRU



AISI #5 EDGES ROLLED
TO ELIMINATE SHARPNESS



PANDUIT PART NUMBER	MATERIAL	PACKAGE QUANTITY	LENGTH = "L" ± .02
MT172-C	304 SS	100	1.72 [43]
MT172-C316	316 SS	100	1.72 [43]
MT350-C	304 SS	100	3.50 [89]
MT350-C316	316 SS	100	3.50 [89]

NOTES:

- BRACKETS [] DENOTES DIMENSIONS IN MILLIMETERS
- CUSTOM PERMANENT MARKING AVAILABLE
CONSULT FACTORY
- TOLERANCES:
 .XXX = ±.010 [.25]
 .XX = ±.02 [.5]
 .X = ±.03 [.8]
 ANGLES = ±2°

							TITLE							
							METAL TAGS - 1 HOLE							
							CUSTOMER DRAWING							
							ITEM REVISION NAME				N41064BS/03		PANDUIT	
							DATASET FILE NAME				N41064BS_DC/03A			
03A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW PANDUIT GLOBAL TITLE BLOCK WITH PANDUIT LOGO	SSECN01031	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° - THIRD ANGLE PROJECTION					MATERIAL: STAINLESS STEEL		
02	5/02	JAMB	JAC	JAC	MATERIAL FOR PART NUMBER MT172-C & MT350-C WAS 302 SS	09145								
01	1/01	KMD	JAC	JAC	MT172-C316 WAS MT172-316C, MT350-C316 WAS MT-316C. CAD FILE SPEC WAS NPC-S41084_00	09062								
00	11/91	SM	JAC	LA	RELEASED	00679						DRAWING NUMBER: N41064BS_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
							SAM	11/11/91	JAC	1:1			A	