



LOC	DIST	P	F	ZONE	LTR	REVISIONS	
						DESCRIPTION	DATE
CM	53					O RELEASED PER PR CM 90-28	2-26-90
						A REVISED PER CM-3286	2-7-91
						B REV PER EC 0730-3607-91	1-7-94
						C REV PER EC 0730-0156-94	8-24-94






1 0.00076 - 0.00091 [.000030 - .000036] GOLD PLATE IN LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] NICKEL UNDERPLATE ALL OVER. 0.00013 - 0.00020 [.000005 - .000008] GOLD FLASH ON REMAINDER OF CONTACT.

2. DIMENSIONS IN BRACKETS ARE IN INCHES.

3. WIRE RANGE: 0.05-0.15 mm²
[30-26 AWG]
INSULATION RANGE: 0.81-1.45 DIA.
[.032 - .057]



METRIC



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON
2 PL DEC ±
3 PL DEC ±0.13 [.005]
ANGLES ±

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DR P. Collins 2-26-90
CHK R. Juring 3-2-90
APPD M. Tull 3-2-90

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

FINISH	PRE-TIN	0.30 [.012] PH BRZ	770672 -6
		0.30 [.012] BRASS	770672 -1
		MATERIAL	PART NO

AMP AMP INCORPORATED
Harrisburg, Pa. 17105

PIN, UNIVERSAL MATE-N-LOKTM,
LOOSE PIECE

SIZE	FSCM NO	DRAWING NO
C	00779	770672
SCALE	10:1	SHEET 1 OF 1

CUSTOMER DRAWING