





"SIMM" P.C. BOARD LAYOUT



NOTES:

1. CARD SLOT ACCEPTS P.C. BOARDS $\frac{.050 \pm .004}{(1.27 \pm 0.10)}$ THICK,
MEASURED OVER CONTACT PADS.
2. PRODUCT SPEC PS-78954 APPLIES.
3. LOCATION OF LOWER CORNER OF MODULE BOARD.
4. CENTER PEG IS AN INTERFERENCE FIT TO RECOMMENDED P.C. BOARD HOLE.

MATERIALS:


HOUSING: LCP, GLASS FILLED, 94V-0. COLOR: BLACK.

LATCH: STAINLESS STEEL.


TERMINAL: PHOSPHOR BRONZE, POST PLATED

30 $\mu\text{IN.}/(7.6 \mu\text{m})$ MIN. GOLD IN CONTACT AREA AND 150 $\mu\text{IN.}/(3.81 \mu\text{m})$ MIN. TIN IN TAIL AREA OVER 75 $\mu\text{IN.}/(1.91 \mu\text{m})$ MIN. NICKEL OVERALL.

- THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.



RECOMMENDED SOCKET
P.C. BOARD HOLE PATTERN



L	LEAD FEED UCP 2004-1582 RWWHITE 04/02/25
K	REVISED PER ECR #U051394 GMY 7-24-95
J	REVISED PCP LENGTH PER ECR #U3151 MJS 6-8-93
I	REMOVED TRACKING TOES PER ECR #U20914 PDB 06-17-92
H	REVISED NOTES PER ECR #U1064 PDB 10-03-91
G	CORRECT HOLE PATTERN PER ECR #U0925-1 PDB 09-25-91
F	REVISED MASTER PER ECR #U1020 PDB 09-04-91
E	ISO WAS 120 PER ECR #U122-91 PDB 11-22-91
D	REVISED PER ECR #U00846 PDB 10-25-90
C	REVISED PER ECR #U0620 PDB 08-24-90
B	REVISED PER ECR #U0635 PDB 08-20-90
A	RELEASE TO MFG. PER ECR #U3023 PDR 08-07-90

DIMENSIONS SHOWN (METRIC) INCH		MFG. SH. REV. LTR.	REVISIONS
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR = 1/2°		REVISIONS	
INCH METRIC		REVISIONS	
3 PLACE ±	0.10 ---	REVISIONS	
2 PLACE ±	0.14 ± 0.25	REVISIONS	
1 PLACE ---	0.35	REVISIONS	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		REVISIONS	
DRAW. BY: PDB		REVISIONS	
CHK'D. BY:		REVISIONS	
APP'D. BY: SCALE 2:		REVISIONS	