



Extruded Cable Ties made of Acetal provide an excellent solution for outdoor applications requiring strength and durability.

- Excellent solution for outdoor applications requiring strength and durability
- Ideal for securing cables in vertical ladder racks and outdoor messenger strand applications
- Weather Resistant Acetal strap body and head
- Double stainless steel, Type 302, locking barbs
- High tensile strength and high impact resistance
- Excellent chemical and moisture resistance
- 250 lb. minimum loop tensile strength
- Meets Telcordia TR-TSY-000789
- May be used with Stackable Aerial Cable Spacers SACS50-T100

Part Number:	DT8EH-Q0
Product Family:	<i>Dura-Ty™</i> Cable Tie
Product Line:	Dura-Ty Extruded Cable Ties

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Cable Tie, 27.0", Extra-Heavy cross section
-------------------	---

Product Type:	Cable Ties
---------------	------------

Material:	Weather Resistant Acetal
-----------	--------------------------

Color:	Black
--------	-------

CSA Certified:	No
----------------	----

UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No
Length (In.):	27.0
Length (mm):	686
Width (In.):	.500
Width (mm):	12.7
CE Compliant:	Yes
Cross Section:	Extra-Heavy
Head Height (In.):	.490
Head Height (mm):	12.4
Head Width (In.):	.718
Head Width (mm):	18.2
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	8.00
Max. Bundle Diameter (mm):	203
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	250
Min. Loop Tensile Strength (N):	1112

Std. Pkg. UOM:	PK
Thickness (In.):	.059
Thickness (mm):	1.5
Tool:	GTH, GS4EH, ST3EH
UOM:	PC
Std. Pkg. Qty.:	25
Min. Order Qty.:	25