




222A121-100-0 Product Details

[Share](#) | [Print](#) | [Email](#)

222A121-100-0

TE Internal Number: 353081-000

Active

Molded Parts


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Molded Part Type = Molded Boot
- Family Name = 222A1
- 90°
- Marine Application, Military Application, Rail Application
- Connector Accessory Outside Diameter (Min-Max) = 10.20 - 24.00 mm

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Boot, 90 deg., Thin Wall](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Molded Boot
- Angle = 90°
- Size = 21
- Material = Low Fire Hazard Material

Body Features:

- Connector Accessory Outside Diameter (Min-Max) (mm [in]) = 10.20 - 24.00 [0.402 - 0.945]
- Cable Diameter Range (mm [in]) = 5.30 - 18.00 [0.209 - 0.709]

Contact Features:

- [Family Name](#) = 222A1

Housing Features:

- [Material Systems Code](#) = 100
- Adhesive Pre-Coating = Without
- Adhesive Description = Adhesive Purchased Separately.

Configuration Features:

- Material Code = 100
- Adhesive Code = S1006, S1030, S1125

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -30 - +105

Operation/Application:

- Application = Marine, Military, Rail

Other:

- Brand = Raychem
- Comment = Contact Raychem for additional adhesive and/or cut off boot length information

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

 Enter your email address
