

HBL2326 -- Twist-Lock Flanged Receptacle



2P3W, 20A 250V, L6-20R, White Nylon

Product Specifications

Product Type		
Product Item	Flanged Receptacle	
Wiring Scheme	2 Pole, 3 Wire Grounding	
Amperage	20A	
Voltage	250V AC	
NEMA Configuration	L6-20R	
Item Style	Standard	
Device Color	White	
Horsepower	2	
Terminal Retainer Material	Clear polycarbonate	
Terminal Clamp Material	.08" (2) steel-nickel plated	
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive	

Ground Screw Material	#10-32 Brass (green finish) Multi-drive
Body Holding Screw Material	Steel, zinc plated Multi-drive
Body Contact Carrier Material	Natural White Nylon
Contact Spring Material	Brass
Spring Binding Plate Material	Brass
Flanged Casing Material	Natural White Nylon
Mounting Screw Material	Nickel-plated Brass Round head screws
Ground Contact Material	.031" (.8) Brass
Ratings	Molded into face.
Catalog No.	Ink marked on nylon casing.
Dielectric Voltage Withstand	2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	20A #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Listings	FED SPEC UL/CSA
Feature Info	Nylon casing, back wired.
Catalog Page	Click here for catalog page B22
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358503787
Weight in LBs	0.25



NEMA L6-20R
20A 250V
UL/CSA

NEMA
Configuration

Hubbell Incorporated (Delaware)

185 Plains Road

Milford, CT 06460-2420

Ph: (203) 882-4800

Fax: (800) 255-1031



Wiring Device-Kellems