

PRODUCT NUMBER
75160-YXX-XXLF

RoHS COMPLIANT & COMPATIBLE, SEE NOTE 8

TOTAL NB OF POSITIONS 02 TO 36

PIN STYLE SEE SHEET 2

PLATING:

1 = 0.76µm FULL GOLD/GXT

3 = 2µm MIN MATTE TIN FULL PLATED

8 = 0.38µm FULL GOLD/GXT

1.27µm MIN NICKEL UNDERPLATING

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC
FLAME RETARDANT PER UL94-VO, COLOR BLACK.

2. PIN MATERIAL : PHOSPHOR BRONZE.

3. DIM 1.27^{+0.03}_{-0.13} FOR MOULDED SIDE(S)
ONLY. IF SIDE(S) ARE BROKEN, DIM 1.02
TO 1.7 MAX APPLIES.

4. PIN PUSH OUT FORCE : 12N MIN.

5. PRODUCT PACKAGED IN POLY BAGS.

6. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS N x 2.54 = 20.32mm

7. FOR STANDARD SELECTIVE GOLD PLATED
PRODUCTS, SEE DRAWING 77311.

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - "LF" MEANS THE PRODUCT IS LEAD-FREE





b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004




mat'l. code				surface		tolerance		projection	product family	
SEE NOTES				ISO 1302 ✓		ISO 406 ISO 1101			BERGSTIK	
ltr	ecr	no	dr	date	tolerances unless otherwise specified				title	
BR	F20607	LMU		03.12.03	angles	linear	.x ±0.3		HEADER SR,STR 2.54mm PITCH	
BS	F03079	LMU		03.04.04			.xx ±0.15			
BT	F05-0186	JCO		05.04.29			xxx ±0.05			
BU	F06-0196	LMU		06.06.20	dr	D LEGRAND	02.01.15		dwg no	
BV	F08-0148	JCO		08.05.27	enr	JMC	02.01.15		sheet 1 of 2	
BW	B-19264	LMU		14.10.31	chr	COMPAGNON	02.01.15		75160	
					appd	JMC	02.01.15		A3	
sheet index		revision		BW	BK				type	
		sheet		2					CUSTOMER Drawing	

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
01		5.72	2.54	10.8
02		5.84	3.43	11.81
03		5.72	5.09	13.34
04		5.72	7.62	15.88
05		5.72	10.16	18.42
06		5.72	12.7	20.96
07		5.72	15.24	23.5
08		5.72	17.78	26.04
09		5.72	20.32	28.58
10		5.72	22.86	31.12
11		5.72	5.97	14.22
12		5.72	8.51	16.76
13		5.72	11.05	19.3
14		5.72	16.13	24.38
15		8.51	2.54	13.59
16		8.51	5.51	16.56
17		8.51	10.59	21.64
18		5.72	3.05	11.3
19		12.83	3.05	18.42
20		15.37	3.05	20.96
21		20.45	3.05	26.04
22		7.75	3.05	13.34
23		5.84	4.95	13.34
24		7.21	3.05	12.8
25		8.51	3.18	14.22
26		15.57	2.84	20.96

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
27		6.6	2.67	11.81
28		6.6	4.19	13.34
29		17.53	3.43	23.5
30		22.61	3.43	28.58
31		8.2	2.84	13.59
32		10.29	3.05	15.88
35		25.21	3.37	31.12
38		5.84	3.81	12.19
39		11.17	3.05	16.76
41		4.99	2.8	10.33
43		6.98	4.8	14.32
44		12.27	3.35	18.16
46		8.08	2.72	13.34
48		5.84	2.42	10.8
50		5.84	3.12	11.5
56		5.72	3.05	11.3
61		16.61	3.2	22.35
62		13.5	3.05	19.09
70		6.54	3.5	12.57
73		28.4	3.18	34.12
75		16.47	10.3	29.31
79		3.3	3.3	9.14
80		8.07	2.2	12.81
90		1.9	3.56	8
95		15.96	4	22.5
96		5.84	3.43	11.81

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
97		7.75	3.05	13.34
98		10.29	3.05	15.88



mat'l. code SEE P/N				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
BH	F05-0186	JCO	05.04.29	angles	.x ±0.3	mm	HEADER STR,SR. 2.54mm PITCH
BJ	F06-0196	LMU	06.06.20	linear	.xx ±0.15		
BK	B-19264	LMU	14.10.31		xxx ±0.05	scale 5:1	dwg no
	F20301	LMU	02.04.23	dr	MULIN.L	99.04.07	sheet 2 of - size
				enfr	JMC	99.04.07	75160 A3
BF	F20607	LM	03.12.03	chr			type
BG	F03079	LMU	03.04.04	appd	JMC	99.04.07	CUSTOMER Drawing
sheet index	revision sheet						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[75160-101-02LF](#) [75160-101-03LF](#) [75160-101-04LF](#) [75160-101-07LF](#) [75160-101-08LF](#) [75160-101-20LF](#) [75160-101-36LF](#) [75160-102-02LF](#) [75160-102-03LF](#) [75160-102-08LF](#) [75160-102-10LF](#) [75160-102-36LF](#) [75160-102R03LF](#) [75160-102R06LF](#) [75160-103-36LF](#) [75160-104-02LF](#) [75160-104-36LF](#) [75160-105-08LF](#) [75160-105-36LF](#) [75160-106-36LF](#) [75160-107-36LF](#) [75160-108-36LF](#) [75160-110-36LF](#) [75160-111-36LF](#) [75160-114-10LF](#) [75160-115-14LF](#) [75160-115-36LF](#) [75160-116-36LF](#) [75160-118-02LF](#) [75160-118-03LF](#) [75160-118-08LF](#) [75160-118-09LF](#) [75160-118-11LF](#) [75160-118-20LF](#) [75160-118-25LF](#) [75160-118-36LF](#) [75160-119-09LF](#) [75160-119-12LF](#) [75160-119-36LF](#) [75160-120-36LF](#) [75160-122-13LF](#) [75160-122-36LF](#) [75160-124-36LF](#) [75160-125-36LF](#) [75160-126-08LF](#) [75160-126-36LF](#) [75160-127-03LF](#) [75160-128-09LF](#) [75160-128-36LF](#) [75160-132-09LF](#) [75160-132-11LF](#) [75160-132-36LF](#) [75160-135-36LF](#) [75160-138-08LF](#) [75160-139-36LF](#) [75160-148-36LF](#) [75160-150-04LF](#) [75160-150-05LF](#) [75160-150-06LF](#) [75160-150-08LF](#) [75160-150-20LF](#) [75160-150-36LF](#) [75160-156-02LF](#) [75160-156-03LF](#) [75160-156-04LF](#) [75160-156-20LF](#) [75160-156-36LF](#) [75160-175-20LF](#) [75160-301-03LF](#) [75160-301-06LF](#) [75160-301-36LF](#) [75160-302-02LF](#) [75160-302-03LF](#) [75160-302-05LF](#) [75160-302-08LF](#) [75160-302-10LF](#) [75160-302-17LF](#) [75160-302-28LF](#) [75160-302-36LF](#) [75160-303-36LF](#) [75160-311-36LF](#) [75160-313-19LF](#) [75160-315-36LF](#) [75160-316-03LF](#) [75160-318-02LF](#) [75160-318-03LF](#) [75160-318-36LF](#) [75160-319-03LF](#) [75160-322-20LF](#) [75160-322-36LF](#) [75160-325-08LF](#) [75160-326-06LF](#) [75160-327-02LF](#) [75160-327-04LF](#) [75160-327-05LF](#) [75160-327-06LF](#) [75160-327-10LF](#) [75160-327-24LF](#) [75160-327-36LF](#) [75160-329-36LF](#)