

## High Intensity SMD LED


Color	Type	Technology	Angle of Half Intensity $\pm\varphi$
Yellow	TLME310.	AlInGaP on GaAs	60°

### Description

This device has been designed to meet the increasing demand for AlInGaP technology.

The package of the TLME310. is the P-LCC-2 (equivalent to a size B tantalum capacitor).

It consists of a lead frame which is embedded in a white thermoplast. The reflector inside this package is filled up with clear epoxy.



94 8553

### Features

- SMD LED with exceptional brightness
- Luminous intensity categorized
- Compatible with automatic placement equipment
- EIA and ICE standard package
- Compatible with infrared, vapor phase and wave solder processes according to CECC
- Available in 8 mm tape
- Low profile package
- Non-diffused lens: excellent for coupling to light pipes and backlighting
- Low power consumption
- Luminous intensity ratio in one packaging unit  $I_{V_{max}}/I_{V_{min}} \leq 2.0$ , optional  $\leq 1.6$

### Applications

- Automotive: backlighting in dashboards and switches
- Telecommunication: indicator and backlighting in telephone and fax
- Indicator and backlight for audio and video equipment
- Indicator and backlight in office equipment
- Flat backlight for LCDs, switches and symbols
- General use

### Absolute Maximum Ratings

$T_{amb} = 25^\circ\text{C}$ , unless otherwise specified

**TLME310.**, , , ,

Parameter	Test Conditions	Symbol	Value	Unit
Reverse voltage		$V_R$	5	V
DC forward current	$T_{amb} \leq 60^\circ\text{C}$	$I_F$	30	mA
Surge forward current	$t_p \leq 10 \mu\text{s}$	$I_{FSM}$	0.1	A
Power dissipation	$T_{amb} \leq 60^\circ\text{C}$	$P_V$	80	mW
Junction temperature		$T_j$	125	$^\circ\text{C}$
Operating temperature range		$T_{amb}$	-40 to +100	$^\circ\text{C}$
Storage temperature range		$T_{stg}$	-55 to +100	$^\circ\text{C}$
Soldering temperature	$t \leq 5 \text{ s}$	$T_{sd}$	260	$^\circ\text{C}$
Thermal resistance junction/ambient	mounted on PC board (pad size $> 16 \text{ mm}^2$ )	$R_{thJA}$	400	K/W

## Optical and Electrical Characteristics

$T_{amb} = 25^\circ C$ , unless otherwise specified


### Yellow (TLME310.)

Parameter	Test Conditions	Type	Symbol	Min.	Typ.	Max.	Unit
Luminous intensity <sup>2)</sup>	$I_F = 10 \text{ mA}$	TLME3100	$I_V$	25	50		mcd
Luminous intensity <sup>1)</sup>		TLME3101	$I_V$	32		100	mcd
		TLME3102	$I_V$	20		64	mcd
		TLME3105	$I_V$	50		160	mcd
Dominant wavelength	$I_F = 10 \text{ mA}$		$\lambda_d$	581	588	594	nm
Peak wavelength	$I_F = 10 \text{ mA}$		$\lambda_p$		590		nm
Angle of half intensity	$I_F = 10 \text{ mA}$		$\phi$		$\pm 60$		deg
Forward voltage	$I_F = 20 \text{ mA}$		$V_F$		2	2.6	V
Reverse voltage	$I_R = 10 \mu\text{A}$		$V_R$	5			V
Junction capacitance	$V_R = 0, f = 1 \text{ MHz}$		$C_j$		15		pF

<sup>1)</sup> in one Packing Unit  $I_V$ Min./  $I_V$ Max.  $\leq 1.6$


<sup>2)</sup> in one Packing Unit  $I_V$ Min./  $I_V$ Max.  $\leq 2$

## Typical Characteristics ( $T_{amb} = 25^\circ C$ , unless otherwise specified)




16614       $T_{amb}$  – Ambient Temperature ( °C )

Figure 1. Power Dissipation vs. Ambient Temperature




16615       $T_{amb}$  – Ambient Temperature ( °C )

Figure 2. Forward Current vs. Ambient Temperature




95 10319

Figure 3. Rel. Luminous Intensity vs. Angular Displacement



95 10878

Figure 4. Forward Current vs. Forward Voltage



95 10880

Figure 5. Rel. Luminous Intensity vs. Ambient Temperature



 96 11589 1 0.5 0.2 0.1 0.05 0.02  $T_p/T$ 

Figure 6. Rel. Lumin. Intensity vs. Forw. Current/Duty Cycle



 96 11588 1 10 100  $I_F$  – Forward Current ( mA )

Figure 7. Relative Luminous Intensity vs. Forward Current





 95 10881 550 560 570 580 590 600 610 620 630 640 650  $\lambda$  – Wavelength ( nm )

Figure 8. Relative Luminous Intensity vs. Wavelength






16616

T<sub>amb</sub> – Ambient Temperature ( °C )

16621


t<sub>p</sub> – Pulse Length ( ms )

**Dimensions in mm**



technical drawings  
according to DIN  
specifications

**Dimensions in mm**



Dimensions: IR and Vaporphase  
( Wave Soldering )

95 10966

## Ozone Depleting Substances Policy Statement

It is the policy of **Vishay Semiconductor GmbH** to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

**Vishay Semiconductor GmbH** has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

**Vishay Semiconductor GmbH** can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

**We reserve the right to make changes to improve technical design and may do so without further notice.**

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Telefunken products for any unintended or unauthorized application, the buyer shall indemnify Vishay Telefunken against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany  
Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423