



REV.	DATE	DESCRIPTION
NC	07/13/04	INITIAL RELEASE
A	01/20/08	REMOVE NOTES, REVISE INSULATOR TO DELRIN.



RECOMMENDED CABLE STRIPPING DIMS



8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
7	CONTACT PIN	BRASS	NOTE 2		1	DRAWN	G.R.S.	01/20/08						
6	HEX NUT	BRASS	NICKEL		1	CHECKED			PART DESCRIPTION TNC CLAMP PLUG (FOR RG-58C/U, 58/U, 142A/U, 223/U CABLE)					
5	WASHER	BRASS	NICKEL		1	ISSUED								
4	GASKET	SILICONE	RED		1	SHEET	1 OF 1		PART NO. 122274					
3	BRAID CLAMP	BRASS	NICKEL		1									
2	INSULATOR	DELTRIN	NATURAL		1				DWG. NO. 122274.DWG REV. A SIZE A SCALE NA					
1	BODY	BRASS	NICKEL		1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/122/122274.DWG								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122274](#)