



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	7.5	± 1.0
T:	4.0	± 1.0
Lead Diameter	0.5	± .1
S:	5.0	± 1.0
L:	38.0	± 9
Coating Lead Run Down (straight Leads)		±
B:	4.00	± 2
C:	1.50	± .5



Electrical Specifications

Resistance:	10.0 Ω	± 20 %
Max Steady State Current upto 65°C:	3.20	A
Max Rec. Energy Rating:	9	J
Actual Failure Instantaneous Energy:	18	J
Maximum Capacitance @ 120 VAC:	630	μ f
Maximum Capacitance @ 240 VAC:	160	μ f
Resistance @ 100% Max Current:		Ω
Resistance @ 50% Max Current:		Ω
Body Temperature at 100% Max Current:	158.00	°c
Dissipation Constant:	9.0	mw/°c
Thermal Time Constant:	27	Sec.
Material Type (for Beta and Curve):	B	

SL08 10003

Date: 08/23/2012	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: A