

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19203-0390](#)
Status: **Active**
Overview: Quick-Disconnect Terminals
Description: Krimptite™ Quick Disconnect, Female Steel 900 Degree F/383 Degree C, 14-16 AWG, Tab 6.35mm

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Quick Disconnects
Series [19203](#)
Crimp Quality Equipment Yes
Insulated No
Overview [Quick-Disconnect Terminals](#)
Product Name Krimptite™
Type Quick Disconnect
UPC 822348428175

Physical
Barrel Type Closed
Gender Male
Glow-Wire Compliant No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Steel
Material - Plating Mating Nickel
Material - Plating Termination Nickel
Net Weight 0.601/g
Orientation Straight
Packaging Type Bag
Tab Thickness 0.80mm
Tab Width 7.70mm
Temperature Range - Operating -65°C to +105°C
Wire Size AWG 14, 16

Electrical
Voltage - Maximum N/A

Material Info

Reference - Drawing Numbers
Product Specification PS-19902-011, PS-19902-013
Sales Drawing SD-19203-025




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19203Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640031100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640071100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0390](#)