



P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	C1	CHANGE SPEC CODE	ECO-06-028026	01-DEC-06	Y.X	N.F
	D	CHANGE TE LOGO&DATE CODE	ECO-08-020482	11-SEP-08	YS.H	BH.Y



NOTES:

1.TERMINAL DIMENSIONS BEFORE SOLDER DIP

2.LAST SUFFIX
NON : WASHABLE TYPE

④ 3.LOT NO. SYSTEM AS FOLLOWING:


WEEK

YEAR


Diagram dimension	Tolerance
0.99mm max.	$\pm$ 0.1mm
1 - 2.99mm	$\pm$ 0.2mm
3mm min.	$\pm$ 0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN H.SASAKI	Tyco Electronics Tyco Electronics Corporation Shenzhen,China			
		CHK N.FUNAYAMA				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A.NAGAI	NAME PCH SPEC,000 CUSTOMER DRAWING ④			
		PRODUCT SPEC —				
	0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$	APPLICATION SPEC —	SIZE A3		CAGE CODE 00779	DRAWING NO 1461410
		WEIGHT —	RESTRICTED TO —			
MATERIAL —	FINISH —	CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV D	

DRILLING DIAGRAM (BOTTOM VIEW)



CONNECTION DIAGRAM (BOTTOM VIEW)



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

HB

DIST

REVISIONS

變更

P

LTR

DESCRIPTION

ECN

DATE

DWN

APVD

1461410-4	PCH-148D2H	48V	PCH-148D2H	n	Ⓒ1
9-1440003-5	PCH-124D2H	24V	PCH-124D2H	m	Ⓒ1
1461410-3	PCH-118D2H	18V	PCH-118D2H	l	Ⓒ1
9-1440003-3	PCH-112D2H	12V	PCH-112D2H	k	Ⓒ1
9-1440003-2	PCH-109D2H	9V	PCH-109D2H	j	Ⓒ1
9-1440003-1	PCH-106D2H	6V	PCH-106D2H	i	Ⓒ1
9-1440003-0	PCH-105D2H	5V	PCH-105D2H	h	Ⓒ1
1461410-2	PCH-148D2	48V	PCH-148D2	g	Ⓒ1
1440004-1	PCH-124D2	24V	PCH-124D2	f	Ⓒ1
1461410-1	PCH-118D2	18V	PCH-118D2	e	Ⓒ1
1440004	PCH-112D2	12V	PCH-112D2	d	Ⓒ1
9-1440003-9	PCH-109D2	9V	PCH-109D2	c	Ⓒ1
9-1440003-8	PCH-106D2	6V	PCH-106D2	b	Ⓒ1
9-1440003-7	PCH-105D2	5V	PCH-105D2	a	Ⓒ1
TE PART NO	TE TYPE NAME	PART B	PART A	TYPE	

RELAY TYPE

		UV RESIN	UV SEAL	17
		EPOXY RESIN	SEAL	16
		UEW	COIL WIRE	15
	SOLDER DIP	HCP WIRE	COIL TERMINAL	14
		Ag ALLOY	STATIONARY CONTACT	13
		Ag ALLOY	MOVBLE CONTACT	12
		Cu ALLOY	HINGE SPRING	11
	SOLDER DIP	Cu ALLOY	NC TERMINAL	10
	SOLDER DIP	Cu ALLOY	NC TERMINAL	9
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	8
UL94 V-0		PBT	CARD	7
UL94 V-0		PBT	CASE	6
UL94 HB		PA66	BOBBIN	5
UL94 V-0		PBT	BASE	4
	Ni PLATED	STEEL	CORE	3
	Ni PLATED	STEEL	ARMATURE	2
	Ni PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shenzhen,China

NAME

PCH SPEC,000 CUSTOMER DRAWING Ⓒ1

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

1461410

—

SCALE

NTS

SHEET

2

OF

2

REV

D