

A

A

B

B

C

C

D


D

E




E

F



F




K-K (10:1)



RECOMMENDED PATTERN



MATED



MATED HEIGHT (h) (mm)

RECEPTACLE NO.	HEADER NO.	
DF15#(0.8)-*DS-0.65V(56)	DF15(3.2)-*DP-0.65V(56)	4
DF15#(1.8)-*DS-0.65V(56)		5

NOTES 1. LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 mm MAX.

PART NO.	CODE NO.	CONTACT	A	B	C	D	E	F	G	H	J
DF15(3.2)-20DP-0.65V(56)	CL677-0082-0-56	20	9.85	7.45	5.85	9.65	8.45	7.05	8.65	7.85	10.25
DF15(3.2)-30DP-0.65V(56)	CL677-0083-2-56	30	13.1	10.7	9.1	12.9	11.7	10.3	11.9	11.1	13.5
DF15(3.2)-40DP-0.65V(56)	CL677-0084-5-56	40	16.35	13.95	12.35	16.15	14.95	13.55	15.15	14.35	16.75
DF15(3.2)-50DP-0.65V(56)	CL677-0085-8-56	50	19.6	17.2	15.6	19.4	18.2	16.8	18.4	17.6	20.0

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
1	PHOSPHOR BRONZE	CONTACT AREA: GOLD PLATED 0.1μm min LEAD AREA: TIN PLATED 1μm min UNDER PLATING: NICKEL PLATED 1μm min	6	PS	BLACK (PLASTIC REEL)
2	POLYAMIDE (PA6T)	NATURAL (BEIGE), UL94V-0	5	POLYESTER	CLEAR (COVER TAPE)
			4	PS	CLEAR (EMBOSSED CARRIER TAPE)
			3	BRASS	TIN PLATED 1μm min UNDER PLATING: NICKEL PLATED 1μm min

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	A. Murakami	J. Michida	T. Miyagaki	L. Ikeda	
	05-11-10	05-11-10	05-11-10	05-11-11	

DRAWING NO.	PART NO.
EDC3-302773-05	DF15(3.2)-*DP-0.65V(56)

SCALE	UNITS	mm	CODE NO.
5 : 1	mm		CL677

