

# 74LVC4066-Q100

## Quad bilateral switch

Rev. 4 — 22 February 2024

Product data sheet

## 1. General description

The 74LVC4066-Q100 is a high-speed Si-gate CMOS device.

The 74LVC4066-Q100 provides four single pole, single-throw analog switch functions. Each switch has two input/output terminals (nY and nZ) and an active HIGH enable input (nE). When nE is LOW, the analog switch is turned off.

Schmitt-trigger action at the enable inputs makes the circuit tolerant of slower input rise and fall times across the entire  $V_{CC}$  range from 1.65 V to 5.5 V.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

## 2. Features and benefits


- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
  - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Wide supply voltage range from 1.65 V to 5.5 V
- Very low ON resistance:
  - 7.5  $\Omega$  (typical) at  $V_{CC} = 2.7$  V
  - 6.5  $\Omega$  (typical) at  $V_{CC} = 3.3$  V
  - 6  $\Omega$  (typical) at  $V_{CC} = 5$  V
- Switch current capability of 32 mA
- High noise immunity
- CMOS low-power consumption
- Direct interface TTL-levels
- Latch-up performance exceeds 250 mA
- Enable inputs accept voltages up to 5 V
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Multiple package options
- DHVQFN package with Side-Wettable Flanks enabling Automatic Optical Inspection (AOI) of solder joints

3. Ordering information

Table 1. Ordering information


| Type number                      | Package           |          |                                                                                                                                    |                          |
|----------------------------------|-------------------|----------|------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
|                                  | Temperature range | Name     | Description                                                                                                                        | Version                  |
| <a href="#">74LVC4066D-Q100</a>  | -40 °C to +125 °C | SO14     | plastic small outline package; 14 leads;<br>body width 3.9 mm                                                                      | <a href="#">SOT108-1</a> |
| <a href="#">74LVC4066PW-Q100</a> | -40 °C to +125 °C | TSSOP14  | plastic thin shrink small outline package;<br>14 leads; body width 4.4 mm                                                          | <a href="#">SOT402-1</a> |
| <a href="#">74LVC4066BQ-Q100</a> | -40 °C to +125 °C | DHVQFN14 | plastic dual in-line compatible thermal<br>enhanced very thin quad flat package; no leads;<br>14 terminals; body 2.5 × 3 × 0.85 mm | <a href="#">SOT762-1</a> |

4. Functional diagram



5. Pinning information

5.1. Pinning



5.2. Pin description

Table 2. Pin description

| Symbol          | Pin          | Description                |
|-----------------|--------------|----------------------------|
| 1Y, 2Y, 3Y, 4Y  | 1, 4, 8, 11  | independent input/output   |
| 1Z, 2Z, 3Z, 4Z  | 2, 3, 9, 10  | independent output/input   |
| 1E, 2E, 3E, 4E  | 13, 5, 6, 12 | enable input (active HIGH) |
| GND             | 7            | ground (0 V)               |
| V <sub>CC</sub> | 14           | supply voltage             |

6. Functional description

Table 3. Function table

H = HIGH voltage level; L = LOW voltage level.

| Input nE | Switch |
|----------|--------|
| L        | OFF    |
| H        | ON     |

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol           | Parameter               | Conditions                                                          | Min  | Max  | Unit |
|------------------|-------------------------|---------------------------------------------------------------------|------|------|------|
| V <sub>CC</sub>  | supply voltage          |                                                                     | -0.5 | +6.5 | V    |
| V <sub>I</sub>   | input voltage           | [1]                                                                 | -0.5 | +6.5 | V    |
| I <sub>IK</sub>  | input clamping current  | V <sub>I</sub> < -0.5 V or V <sub>I</sub> < V <sub>CC</sub> + 0.5 V | -50  | -    | mA   |
| I <sub>SK</sub>  | switch clamping current | V <sub>I</sub> < -0.5 V or V <sub>I</sub> < V <sub>CC</sub> + 0.5 V | -    | ±50  | mA   |
| V <sub>SW</sub>  | switch voltage          | enable and disable mode [2]                                         | -0.5 | +6.5 | V    |
| I <sub>SW</sub>  | switch current          | -0.5 < V <sub>SW</sub> < V <sub>CC</sub> + 0.5 V                    | -    | ±50  | mA   |
| I <sub>CC</sub>  | supply current          |                                                                     | -    | 100  | mA   |
| I <sub>GND</sub> | ground current          |                                                                     | -100 | -    | mA   |
| T <sub>stg</sub> | storage temperature     |                                                                     | -65  | +150 | °C   |
| P <sub>tot</sub> | total power dissipation | T <sub>amb</sub> = -40 °C to +125 °C [3]                            | -    | 500  | mW   |

- [1] The minimum input voltage rating may be exceeded if the input current rating is observed.  
[2] The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed.  
[3] For SOT108-1 (SO14) package: P<sub>tot</sub> derates linearly with 10.1 mW/K above 100 °C.  
For SOT402-1 (TSSOP14) package: P<sub>tot</sub> derates linearly with 7.3 mW/K above 81 °C.  
For SOT762-1 (DHVQFN14) package: P<sub>tot</sub> derates linearly with 9.6 mW/K above 98 °C.

8. Recommended operating conditions

Table 5. Recommended operating conditions

| Symbol           | Parameter                           | Conditions                            | Min  | Typ | Max             | Unit |
|------------------|-------------------------------------|---------------------------------------|------|-----|-----------------|------|
| V <sub>CC</sub>  | supply voltage                      |                                       | 1.65 | -   | 5.5             | V    |
| V <sub>I</sub>   | input voltage                       |                                       | 0    | -   | 5.5             | V    |
| V <sub>SW</sub>  | switch voltage                      | [1]                                   | 0    | -   | V <sub>CC</sub> | V    |
| T <sub>amb</sub> | ambient temperature                 |                                       | -40  | -   | +125            | °C   |
| Δt/ΔV            | input transition rise and fall rate | V <sub>CC</sub> = 1.65 V to 2.7 V [2] | -    | -   | 20              | ns/V |
|                  |                                     | V <sub>CC</sub> = 2.7 V to 5.5 V [2]  | -    | -   | 10              | ns/V |

- [1] To avoid sinking GND current from terminal nZ when switch current flows in terminal nY, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal nZ, no GND current will flow from terminal nY. In this case, there is no limit for the voltage drop across the switch.  
[2] Applies to control signal levels.

9. Static characteristics


Table 6. Static characteristics

At recommended operating conditions voltages are referenced to GND (ground = 0 V).

| Symbol              | Parameter                 | Conditions                                                                                                              | -40 °C to +85 °C    |         |                     | -40 °C to +125 °C   |                     | Unit |
|---------------------|---------------------------|-------------------------------------------------------------------------------------------------------------------------|---------------------|---------|---------------------|---------------------|---------------------|------|
|                     |                           |                                                                                                                         | Min                 | Typ [1] | Max                 | Min                 | Max                 |      |
| V <sub>IH</sub>     | HIGH-level input voltage  | V <sub>CC</sub> = 1.65 V to 1.95 V                                                                                      | 0.65V <sub>CC</sub> | -       | -                   | 0.65V <sub>CC</sub> | -                   | V    |
|                     |                           | V <sub>CC</sub> = 2.3 V to 2.7 V                                                                                        | 1.7                 | -       | -                   | 1.7                 | -                   | V    |
|                     |                           | V <sub>CC</sub> = 2.7 V to 3.6 V                                                                                        | 2.0                 | -       | -                   | 2.0                 | -                   | V    |
|                     |                           | V <sub>CC</sub> = 4.5 V to 5.5 V                                                                                        | 0.7V <sub>CC</sub>  | -       | -                   | 0.7V <sub>CC</sub>  | -                   | V    |
| V <sub>IL</sub>     | LOW-level input voltage   | V <sub>CC</sub> = 1.65 V to 1.95 V                                                                                      | -                   | -       | 0.35V <sub>CC</sub> | -                   | 0.35V <sub>CC</sub> | V    |
|                     |                           | V <sub>CC</sub> = 2.3 V to 2.7 V                                                                                        | -                   | -       | 0.7                 | -                   | 0.7                 | V    |
|                     |                           | V <sub>CC</sub> = 2.7 V to 3.6 V                                                                                        | -                   | -       | 0.8                 | -                   | 0.8                 | V    |
|                     |                           | V <sub>CC</sub> = 4.5 V to 5.5 V                                                                                        | -                   | -       | 0.3V <sub>CC</sub>  | -                   | 0.3V <sub>CC</sub>  | V    |
| I <sub>I</sub>      | input leakage current     | pin nE; V <sub>CC</sub> = 5.5 V; V <sub>I</sub> = 5.5 V or GND [2]                                                      | -                   | ±0.1    | ±5                  | -                   | ±20                 | µA   |
| I <sub>S(OFF)</sub> | OFF-state leakage current | V <sub>SW</sub>   = V <sub>CC</sub> - GND; V <sub>CC</sub> = 5.5 V; see Fig. 6 [2]                                      | -                   | ±0.1    | ±5                  | -                   | ±20                 | µA   |
| I <sub>S(ON)</sub>  | ON-state leakage current  | V <sub>SW</sub>   = V <sub>CC</sub> - GND; V <sub>CC</sub> = 5.5 V; see Fig. 7 [2]                                      | -                   | ±0.1    | ±5                  | -                   | ±20                 | µA   |
| I <sub>CC</sub>     | supply current            | V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>SW</sub> = GND or V <sub>CC</sub> ; V <sub>CC</sub> = 5.5 V [2]         | -                   | 0.1     | 10                  | -                   | 40                  | µA   |
| ΔI <sub>CC</sub>    | additional supply current | pin nE; V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; V <sub>CC</sub> = 5.5 V; V <sub>SW</sub> = GND or V <sub>CC</sub> [2] | -                   | 5       | 500                 | -                   | 5000                | µA   |
| C <sub>I</sub>      | input capacitance         |                                                                                                                         | -                   | 12.5    | -                   | -                   | -                   | pF   |
| C <sub>S(OFF)</sub> | OFF-state capacitance     |                                                                                                                         | -                   | 8.0     | -                   | -                   | -                   | pF   |
| C <sub>S(ON)</sub>  | ON-state capacitance      |                                                                                                                         | -                   | 14.0    | -                   | -                   | -                   | pF   |


- [1] All typical values are measured at T<sub>amb</sub> = 25 °C.  
[2] These typical values are measured at V<sub>CC</sub> = 3.3 V.

9.1. Test circuits



V<sub>I</sub> = V<sub>CC</sub> or GND and V<sub>O</sub> = GND or V<sub>CC</sub>.

**Fig. 6. Test circuit for measuring OFF-state leakage current**



V<sub>I</sub> = V<sub>CC</sub> or GND and V<sub>O</sub> = open circuit.

**Fig. 7. Test circuit for measuring ON-state leakage current**

9.2. ON resistance



Table 7. ON resistance

At recommended operating conditions; voltages are referenced to GND (ground 0 V); for graphs see Fig. 9 to Fig. 14.

| Symbol                | Parameter                | Conditions                                                 | -40 °C to +85 °C |         |     | -40 °C to +125 °C |     | Unit |
|-----------------------|--------------------------|------------------------------------------------------------|------------------|---------|-----|-------------------|-----|------|
|                       |                          |                                                            | Min              | Typ [1] | Max | Min               | Max |      |
| R <sub>ON(peak)</sub> | ON resistance (peak)     | V <sub>I</sub> = GND to V <sub>CC</sub> ; see Fig. 8       |                  |         |     |                   |     |      |
|                       |                          | I <sub>SW</sub> = 4 mA; V <sub>CC</sub> = 1.65 V to 1.95 V | -                | 34.0    | 130 | -                 | 195 | Ω    |
|                       |                          | I <sub>SW</sub> = 8 mA; V <sub>CC</sub> = 2.3 V to 2.7 V   | -                | 12.0    | 30  | -                 | 45  | Ω    |
|                       |                          | I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V           | -                | 10.4    | 25  | -                 | 38  | Ω    |
|                       |                          | I <sub>SW</sub> = 24 mA; V <sub>CC</sub> = 3 V to 3.6 V    | -                | 7.8     | 20  | -                 | 30  | Ω    |
|                       |                          | I <sub>SW</sub> = 32 mA; V <sub>CC</sub> = 4.5 V to 5.5 V  | -                | 6.2     | 15  | -                 | 23  | Ω    |
| R <sub>ON(rail)</sub> | ON resistance (rail)     | V <sub>I</sub> = GND; see Fig. 8                           |                  |         |     |                   |     |      |
|                       |                          | I <sub>SW</sub> = 4 mA; V <sub>CC</sub> = 1.65 V to 1.95 V | -                | 8.2     | 18  | -                 | 27  | Ω    |
|                       |                          | I <sub>SW</sub> = 8 mA; V <sub>CC</sub> = 2.3 V to 2.7 V   | -                | 7.1     | 16  | -                 | 24  | Ω    |
|                       |                          | I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V           | -                | 6.9     | 14  | -                 | 21  | Ω    |
|                       |                          | I <sub>SW</sub> = 24 mA; V <sub>CC</sub> = 3 V to 3.6 V    | -                | 6.5     | 12  | -                 | 18  | Ω    |
|                       |                          | I <sub>SW</sub> = 32 mA; V <sub>CC</sub> = 4.5 V to 5.5 V  | -                | 5.8     | 10  | -                 | 15  | Ω    |
|                       |                          | V <sub>I</sub> = V <sub>CC</sub> ; see Fig. 8              |                  |         |     |                   |     |      |
|                       |                          | I <sub>SW</sub> = 4 mA; V <sub>CC</sub> = 1.65 V to 1.95 V | -                | 10.4    | 30  | -                 | 45  | Ω    |
|                       |                          | I <sub>SW</sub> = 8 mA; V <sub>CC</sub> = 2.3 V to 2.7 V   | -                | 7.6     | 20  | -                 | 30  | Ω    |
|                       |                          | I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V           | -                | 7.0     | 18  | -                 | 27  | Ω    |
|                       |                          | I <sub>SW</sub> = 24 mA; V <sub>CC</sub> = 3 V to 3.6 V    | -                | 6.1     | 15  | -                 | 23  | Ω    |
|                       |                          | I <sub>SW</sub> = 32 mA; V <sub>CC</sub> = 4.5 V to 5.5 V  | -                | 4.9     | 10  | -                 | 15  | Ω    |
|                       |                          |                                                            |                  |         |     |                   |     |      |
| R <sub>ON(flat)</sub> | ON resistance (flatness) | V <sub>I</sub> = GND to V <sub>CC</sub> [2]                |                  |         |     |                   |     |      |
|                       |                          | I <sub>SW</sub> = 4 mA; V <sub>CC</sub> = 1.65 V to 1.95 V | -                | 26.0    | -   | -                 | -   | Ω    |
|                       |                          | I <sub>SW</sub> = 8 mA; V <sub>CC</sub> = 2.3 V to 2.7 V   | -                | 5.0     | -   | -                 | -   | Ω    |
|                       |                          | I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V           | -                | 3.5     | -   | -                 | -   | Ω    |
|                       |                          | I <sub>SW</sub> = 24 mA; V <sub>CC</sub> = 3 V to 3.6 V    | -                | 2.0     | -   | -                 | -   | Ω    |
|                       |                          | I <sub>SW</sub> = 32 mA; V <sub>CC</sub> = 4.5 V to 5.5 V  | -                | 1.5     | -   | -                 | -   | Ω    |

[1] Typical values are measured at T<sub>amb</sub> = 25 °C and nominal V<sub>CC</sub>.  
[2] Flatness is defined as the difference between the maximum and minimum value of ON resistance measured at identical V<sub>CC</sub> and temperature.

9.3. ON resistance test circuit and graphs






Fig. 12. ON resistance as a function of input voltage;  $V_{CC} = 2.7$  V




Fig. 13. ON resistance as a function of input voltage;  $V_{CC} = 3.3$  V




Fig. 14. ON resistance as a function of input voltage;  $V_{CC} = 5.0$  V



## 10. Dynamic characteristics

**Table 8. Dynamic characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 17.

| Symbol    | Parameter                     | Conditions                                                                         | -40 °C to +85 °C |         |     | -40 °C to +125 °C |      | Unit |
|-----------|-------------------------------|------------------------------------------------------------------------------------|------------------|---------|-----|-------------------|------|------|
|           |                               |                                                                                    | Min              | Typ [1] | Max | Min               | Max  |      |
| $t_{pd}$  | propagation delay             | nY to nZ or nZ to nY; see Fig. 15 [2] [3]                                          |                  |         |     |                   |      |      |
|           |                               | $V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$                                       | -                | 0.8     | 2.0 | -                 | 3.0  | ns   |
|           |                               | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$                                         | -                | 0.4     | 1.2 | -                 | 2.0  | ns   |
|           |                               | $V_{CC} = 2.7 \text{ V}$                                                           | -                | 0.4     | 1.0 | -                 | 1.5  | ns   |
|           |                               | $V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$                                         | -                | 0.3     | 0.8 | -                 | 1.5  | ns   |
|           |                               | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$                                         | -                | 0.2     | 0.6 | -                 | 1.0  | ns   |
| $t_{en}$  | enable time                   | nE to nY or nZ; see Fig. 16 [4]                                                    |                  |         |     |                   |      |      |
|           |                               | $V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$                                       | 1.0              | 5.3     | 10  | 1.0               | 12.5 | ns   |
|           |                               | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$                                         | 1.0              | 3.0     | 5.6 | 1.0               | 7.0  | ns   |
|           |                               | $V_{CC} = 2.7 \text{ V}$                                                           | 1.0              | 2.6     | 5.0 | 1.0               | 6.5  | ns   |
|           |                               | $V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$                                         | 1.0              | 2.5     | 4.4 | 1.0               | 5.5  | ns   |
|           |                               | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$                                         | 1.0              | 1.9     | 3.9 | 1.0               | 5.0  | ns   |
| $t_{dis}$ | disable time                  | nE to nY or nZ; see Fig. 16 [5]                                                    |                  |         |     |                   |      |      |
|           |                               | $V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$                                       | 1.0              | 4.2     | 9.0 | 1.0               | 11.5 | ns   |
|           |                               | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$                                         | 1.0              | 2.4     | 5.5 | 1.0               | 7.0  | ns   |
|           |                               | $V_{CC} = 2.7 \text{ V}$                                                           | 1.0              | 3.6     | 6.5 | 1.0               | 8.5  | ns   |
|           |                               | $V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$                                         | 1.0              | 3.4     | 6.0 | 1.0               | 7.5  | ns   |
|           |                               | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$                                         | 1.0              | 2.5     | 5.0 | 1.0               | 6.5  | ns   |
| $C_{PD}$  | power dissipation capacitance | $C_L = 50 \text{ pF}$ ; $f_i = 10 \text{ MHz}$ ; $V_I = \text{GND to } V_{CC}$ [6] |                  |         |     |                   |      |      |
|           |                               | $V_{CC} = 2.5 \text{ V}$                                                           | -                | 11.0    | -   | -                 | -    | pF   |
|           |                               | $V_{CC} = 3.3 \text{ V}$                                                           | -                | 12.5    | -   | -                 | -    | pF   |
|           |                               | $V_{CC} = 5.0 \text{ V}$                                                           | -                | 15.6    | -   | -                 | -    | pF   |

[1] Typical values are measured at  $T_{amb} = 25 \text{ °C}$  and nominal  $V_{CC}$ .

[2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .

[3] Propagation delay is the calculated RC time constant of the typical ON resistance of the switch and the specified capacitance when driven by an ideal voltage source (zero output impedance).

[4]  $t_{en}$  is the same as  $t_{PZH}$  and  $t_{PZL}$ .

[5]  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

[6]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu\text{W}$ ).

$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma\{(C_L + C_{S(ON)}) \times V_{CC}^2 \times f_o\}$  where:

$f_i$  = input frequency in MHz;

$f_o$  = output frequency in MHz;

$C_L$  = output load capacitance in pF;

$C_{S(ON)}$  = maximum ON-state switch capacitance in pF;

$V_{CC}$  = supply voltage in V;

$N$  = number of inputs switching;

$\Sigma\{(C_L + C_{S(ON)}) \times V_{CC}^2 \times f_o\}$  = sum of the outputs.

10.1. Waveforms and test circuit






Table 9. Measurement points

| Supply voltage   | Input       | Output       |                   |                   |
|------------------|-------------|--------------|-------------------|-------------------|
| $V_{CC}$         | $V_M$       | $V_M$        | $V_X$             | $V_Y$             |
| 1.65 V to 1.95 V | $0.5V_{CC}$ | $0.5 V_{CC}$ | $V_{OL} + 0.15 V$ | $V_{OH} - 0.15 V$ |
| 2.3 V to 2.7 V   | $0.5V_{CC}$ | $0.5V_{CC}$  | $V_{OL} + 0.15 V$ | $V_{OH} - 0.15 V$ |
| 2.7 V            | 1.5 V       | 1.5 V        | $V_{OL} + 0.3 V$  | $V_{OH} - 0.3 V$  |
| 3.0 V to 3.6 V   | 1.5 V       | 1.5 V        | $V_{OL} + 0.3 V$  | $V_{OH} - 0.3 V$  |
| 4.5 V to 5.5 V   | $0.5V_{CC}$ | $0.5V_{CC}$  | $V_{OL} + 0.3 V$  | $V_{OH} - 0.3 V$  |



Test data is given in [Table 10](#).  
Definitions test circuit:  
 $R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator.  
 $C_L$  = Load capacitance including jig and probe capacitance.  
 $R_L$  = Load resistance.  
 $V_{EXT}$  = External voltage for measuring switching times.

Fig. 17. Test circuit for measuring switching times

Table 10. Test data

| Supply voltage   | Input    |               | Load  |              | $V_{EXT}$          |                    |                    |
|------------------|----------|---------------|-------|--------------|--------------------|--------------------|--------------------|
| $V_{CC}$         | $V_I$    | $t_r, t_f$    | $C_L$ | $R_L$        | $t_{PLH}, t_{PHL}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ |
| 1.65 V to 1.95 V | $V_{CC}$ | $\leq 2.0$ ns | 30 pF | 1 k $\Omega$ | open               | GND                | $2V_{CC}$          |
| 2.3 V to 2.7 V   | $V_{CC}$ | $\leq 2.0$ ns | 30 pF | 500 $\Omega$ | open               | GND                | $2V_{CC}$          |
| 2.7 V            | 2.7 V    | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | 6 V                |
| 3.0 V to 3.6 V   | 2.7 V    | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | 6 V                |
| 4.5 V to 5.5 V   | $V_{CC}$ | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2V_{CC}$          |

10.2. Additional dynamic characteristics


Table 11. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V);  $T_{amb} = 25$  °C.

| Symbol | Parameter                 | Conditions                                                                         | Min | Typ   | Max | Unit |
|--------|---------------------------|------------------------------------------------------------------------------------|-----|-------|-----|------|
| THD    | total harmonic distortion | $R_L = 10$ k $\Omega$ ; $C_L = 50$ pF; $f_i = 1$ kHz; see <a href="#">Fig. 18</a>  |     |       |     |      |
|        |                           | $V_{CC} = 1.65$ V                                                                  | -   | 0.032 | -   | %    |
|        |                           | $V_{CC} = 2.3$ V                                                                   | -   | 0.008 | -   | %    |
|        |                           | $V_{CC} = 3$ V                                                                     | -   | 0.006 | -   | %    |
|        |                           | $V_{CC} = 4.5$ V                                                                   | -   | 0.005 | -   | %    |
|        |                           | $R_L = 10$ k $\Omega$ ; $C_L = 50$ pF; $f_i = 10$ kHz; see <a href="#">Fig. 18</a> |     |       |     |      |
|        |                           | $V_{CC} = 1.65$ V                                                                  | -   | 0.068 | -   | %    |
|        |                           | $V_{CC} = 2.3$ V                                                                   | -   | 0.009 | -   | %    |
|        |                           | $V_{CC} = 3$ V                                                                     | -   | 0.008 | -   | %    |
|        |                           | $V_{CC} = 4.5$ V                                                                   | -   | 0.006 | -   | %    |

| Symbol         | Parameter                | Conditions                                                                                                                                                        | Min | Typ   | Max | Unit |
|----------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-------|-----|------|
| $f_{(-3dB)}$   | -3 dB frequency response | $R_L = 600\ \Omega$ ; $C_L = 50\ \text{pF}$ ; see <a href="#">Fig. 19</a>                                                                                         |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | 170   | -   | MHz  |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | 210   | -   | MHz  |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | 212   | -   | MHz  |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | 215   | -   | MHz  |
|                |                          | $R_L = 50\ \Omega$ ; $C_L = 5\ \text{pF}$ ; see <a href="#">Fig. 19</a>                                                                                           |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | > 500 | -   | MHz  |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | > 500 | -   | MHz  |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | > 500 | -   | MHz  |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | > 500 | -   | MHz  |
| $\alpha_{iso}$ | isolation (OFF-state)    | $R_L = 600\ \Omega$ ; $C_L = 50\ \text{pF}$ ; $f_i = 1\ \text{MHz}$ ; see <a href="#">Fig. 20</a>                                                                 |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | -46   | -   | dB   |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | -46   | -   | dB   |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | -46   | -   | dB   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | -46   | -   | dB   |
|                |                          | $R_L = 50\ \Omega$ ; $C_L = 5\ \text{pF}$ ; $f_i = 1\ \text{MHz}$ ; see <a href="#">Fig. 20</a>                                                                   |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | -42   | -   | dB   |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | -42   | -   | dB   |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | -42   | -   | dB   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | -42   | -   | dB   |
| $V_{ct}$       | crosstalk voltage        | between digital inputs and switch; $R_L = 600\ \Omega$ ; $C_L = 50\ \text{pF}$ ; $f_i = 1\ \text{MHz}$ ; $t_r = t_f = 2\ \text{ns}$ ; see <a href="#">Fig. 21</a> |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | 69    | -   | mV   |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | 87    | -   | mV   |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | 156   | -   | mV   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | 302   | -   | mV   |
| Xtalk          | crosstalk                | between switches; $R_L = 600\ \Omega$ ; $C_L = 50\ \text{pF}$ ; $f_i = 1\ \text{MHz}$ ; see <a href="#">Fig. 22</a>                                               |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | -58   | -   | dB   |
|                |                          | between switches; $R_L = 50\ \Omega$ ; $C_L = 5\ \text{pF}$ ; $f_i = 1\ \text{MHz}$ ; see <a href="#">Fig. 22</a>                                                 |     |       |     |      |
|                |                          | $V_{CC} = 1.65\ \text{V}$                                                                                                                                         | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 2.3\ \text{V}$                                                                                                                                          | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 3\ \text{V}$                                                                                                                                            | -   | -58   | -   | dB   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | -58   | -   | dB   |
| $Q_{inj}$      | charge injection         | $C_L = 0.1\ \text{nF}$ ; $V_{gen} = 0\ \text{V}$ ; $R_{gen} = 0\ \Omega$ ; $f_i = 1\ \text{MHz}$ ; $R_L = 1\ \text{M}\Omega$ ; see <a href="#">Fig. 23</a>        |     |       |     |      |
|                |                          | $V_{CC} = 1.8\ \text{V}$                                                                                                                                          | -   | 3.3   | -   | pC   |
|                |                          | $V_{CC} = 2.5\ \text{V}$                                                                                                                                          | -   | 4.1   | -   | pC   |
|                |                          | $V_{CC} = 3.3\ \text{V}$                                                                                                                                          | -   | 5.0   | -   | pC   |
|                |                          | $V_{CC} = 4.5\ \text{V}$                                                                                                                                          | -   | 6.4   | -   | pC   |
|                |                          | $V_{CC} = 5.5\ \text{V}$                                                                                                                                          | -   | 7.5   | -   | pC   |


### 10.3. Test circuits



Test conditions:


$$V_{CC} = 1.65 \text{ V}; V_i = 1.4 \text{ V (p-p)}.$$
 $V_{CC} = 2.3 \text{ V}; V_i = 2 \text{ V (p-p)}.$  $V_{CC} = 3 \text{ V}; V_i = 2.5 \text{ V (p-p)}.$ 
$$V_{CC} = 4.5 \text{ V}; V_i = 4 \text{ V (p-p)}.$$

**Fig. 18. Test circuit for measuring total harmonic distortion**




Adjust  $f_i$  voltage to obtain 0 dBm level at output. Increase  $f_i$  frequency until dB meter reads -3 dB.

**Fig. 19. Test circuit for measuring the frequency response when switch is in ON-state**




Adjust  $f_i$  voltage to obtain 0 dBm level at input.

**Fig. 20. Test circuit for measuring isolation (OFF-state)**




**Fig. 21. Test circuit for measuring crosstalk voltage (between digital inputs and switch)**



$$20 \log_{10} (V_{O2} / V_{O1}) \text{ or } 20 \log_{10} (V_{O1} / V_{O2}).$$

**Fig. 22. Test circuit for measuring crosstalk between switches**



$$Q_{inj} = \Delta V_O \times C_L.$$

$\Delta V_O$  = output voltage variation.

$R_{gen}$  = generator resistance.

$V_{gen}$  = generator voltage.

**Fig. 23. Test circuit for measuring charge injection**

11. Package outline

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1




Fig. 24. Package outline SOT108-1 (SO14)

TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm

SOT402-1




Fig. 25. Package outline SOT402-1 (TSSOP14)



**DHVQFN14: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 14 terminals; body 2.5 x 3 x 0.85 mm**

SOT762-1




Fig. 26. Package outline SOT762-1 (DHVQFN14)

12. Abbreviations

Table 12. Abbreviations

| Acronym | Description                             |
|---------|-----------------------------------------|
| CMOS    | Complementary Metal Oxide Semiconductor |
| DUT     | Device Under Test                       |
| ESD     | ElectroStatic Discharge                 |
| HBM     | Human Body Model                        |
| TTL     | Transistor-Transistor Logic             |

13. Revision history

Table 13. Revision history

| Document ID        | Release date                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Data sheet status  | Change notice | Supersedes         |
|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|---------------|--------------------|
| 74LVC4066_Q100 v.4 | 20240222                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Product data sheet | -             | 74LVC4066_Q100 v.3 |
| Modifications:     | <ul style="list-style-type: none"><li><a href="#">Fig. 24</a>, <a href="#">Fig. 25</a>: Aligned SO and TSSOP package outline drawings to JEDEC MS-012 and MO-153.</li></ul>                                                                                                                                                                                                                                                                                                   |                    |               |                    |
| 74LVC4066_Q100 v.3 | 20230824                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Product data sheet | -             | 74LVC4066_Q100 v.2 |
| Modifications:     | <ul style="list-style-type: none"><li><a href="#">Section 2</a>: ESD specification updated according to the latest JEDEC standard.</li></ul>                                                                                                                                                                                                                                                                                                                                  |                    |               |                    |
| 74LVC4066_Q100 v.2 | 20200326                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Product data sheet | -             | 74LVC4066_Q100 v.1 |
| Modifications:     | <ul style="list-style-type: none"><li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li><li>Legal texts have been adapted to the new company name where appropriate.</li><li><a href="#">Section 2</a> updated.</li><li><a href="#">Table 4</a>: Derating values for P<sub>tot</sub> total power dissipation updated.</li><li><a href="#">Fig. 26</a>: Package outline drawing SOT762-1 (DHVQFN14) updated.</li></ul> |                    |               |                    |
| 74LVC4066_Q100 v.1 | 20120807                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Product data sheet | -             | -                  |

## 14. Legal information

### Data sheet status

| Document status [1][2]         | Product status [3] | Definition                                                                            |
|--------------------------------|--------------------|---------------------------------------------------------------------------------------|
| Objective [short] data sheet   | Development        | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification      | This document contains data from the preliminary specification.                       |
| Product [short] data sheet     | Production         | This document contains the product specification.                                     |

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <https://www.nexperia.com>.

### Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use in automotive applications** — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

**Terms and conditions of commercial sale** — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description..... 1

2. Features and benefits..... 1

3. Ordering information.....2

4. Functional diagram.....2

5. Pinning information.....3

5.1. Pinning.....3

5.2. Pin description.....3

6. Functional description..... 3

7. Limiting values..... 4

8. Recommended operating conditions.....4

9. Static characteristics.....5

9.1. Test circuits.....5

9.2. ON resistance.....6

9.3. ON resistance test circuit and graphs.....7

10. Dynamic characteristics..... 9

10.1. Waveforms and test circuit..... 10

10.2. Additional dynamic characteristics..... 11

10.3. Test circuits..... 13

11. Package outline..... 15

12. Abbreviations..... 18

13. Revision history..... 18

14. Legal information.....19

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: [salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)

Date of release: 22 February 2024