





$\frac{7}{16}$ - 28 UNEF-2B THREAD

STAMP: KINGS KA-59-69

NOTES:

1. FOR USE WITH RG-174, 179, 187 & 188/U CABLES.
2. FOR CABLE TRIMMING USE KTJ-30.
3. FOR CRIMPING USE DIE SIZE 32.
4. FOR CABLING INSTRUCTIONS SEE CP-406.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES:
FRACTIONS & .010 DECIMALS $\pm .004$ ANGLES $\pm 0^\circ 30'$
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS, BREAK SHARP EDGES .003 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

ITEM	REQ'D	DESCRIPTION	DWG. NO.
9	1	INSULATOR	
8	1	TNC CAPTIVE CONTACT M-F	
7	1	COUPLING NUT	
6	1	GASKET	
5	1	CRIMP CONTACT	C-59-95-2-M07
4	1	C-RING	
3	1	INSULATOR	
2	1	BODY ASSEMBLY	
1	1	K-GRIP SLEEVE	S-89-67-2-M07

REVISIONS

NO.	CHANGES
1	CN 6350 A 19 AUG 68 ANE
2	CN 11107 A J.G.L. 25 APR 72
3	CN 25062 C JEP 1 SEPT 83

KA-59-69

REF:

FINISH

SPEC. KER 10004

MATL.

SPEC.

TNC PLUG

DRAWN A.T. DATE 8 FEB 66

APPR. L.I. DATE 9 FEB 66

KINGS ELECTRONICS
40 MARBLEDALE ROAD
TUCKAHOE, N. Y.

KA-59-69

S-D