



VIEW B ROTATED 180°	
POST-FEED 40 mm STROKE	POST-FEED 30 mm STROKE
	
LOC A DIST 66 LEADMAKER OR BENCH G	K TERMINATOR BENCH MACHINE



		-77-71 -1		PART NO		DESCRIPTION		ITEM NO	
				← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)					
QTY REQD PER ASSY				PARTS LIST					
		DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ±- 2 PLC DEC ±- 3 PLC DEC ±- ANGLES ±- SURF TEXTURE: ✓		MAIL - HT TR - FIN		 AMP Tyco Electronics Horseshoe Rd #7105-3608 Middletown, NJ 07105-3608			
		DR 145EP041APP 145EP04 F.BACHURST							
		L.O.FHOUSE							
		CHK - REL							
		NAME							
		END FEED HD-I APPLICATOR		MACHINE REF HD-I APPL					
		SCALE -		D		DWG NO 133075		SHEET 1 OF 1	
MC OCT04 APP DATE		REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX						REV A	
		CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING					
								RESTRICTED TO -	

P04 APP		B5EEN		Type Electronics	
F BACKHURST		AMP		Harrisburg, PA 17105-8688	
REL 21-10-04		WGLFFORD			
FEED HD-I APPLICATOR		MACHINE REEL		HD-I APPL	
DWG NO. 138875		SHEET 1 OF 1		REV A	