

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PROBORT, ILLINOIS

FED. MFR. CODE 91929

ASSEMBLY- PUSHBUTTON SWITCH

CATALOG LISTING

82PB22-T2

82PB22-T2

PAGE 1 OF 1

M

DRAWING
NUMBER

8

ISSUE

REPLACES

RELEASE NO. SR 8722

09APR08

ASD

CHECK

29 OCT 98

29 OCT 98

J A F

CHECK

15 APR 99

SV

PK

09APR08

CHECK


06 JAN 60

OMW

6 JAN 60

RASTER

FO-50378



NOTES

- 1 -UNIT INCLUDES CAT.LIST.311SM TYPE BASIC SWITCH (2)
- 2 -TERMINALS ARE PLATED FOR SOLDERING
- 3 -SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 4 -ALTERNATE ACTION MECHANISM (PUSH-ON, PUSH-OFF ACTUATION)
- 5 -MOUNTING HARWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ---- 35 OZ APPROX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (2)

250 VAC ---- 5 AMP
30 VOLTS DC RATING
INDUCTIVE ---- SEA LEVEL ---- 3 AMP
50,000 FT. ---- 2.5 AMP
RESISTIVE ---- SEA LEVEL ---- 5 AMP
50,000 FT. ---- 5 AMP
MAXIMUM INRUSH ---- 24 AMP

SCALE

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT