






SINGLE CONTACT DIMENSIONS



SINGLE CONTACT AFTER BENDING




DELIVERY STATUS
Anlieferzustand PPN 0-2141016-2



APPLICATION SKETCH

Einbausituation



LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	OWN	APV
		A2	DIM	21.1	10 JUN2010	TS	BF
		A3	PCN	E-10-022148	270C 12010	HS	BF

NOTE:
Bemerkung:

- | | |
|----|---|
| 1 | PART ACCORDING TE- SPECIFICATION 108-90800
Teile nach TE- Spezifikation 108-90800 |
| 71 | 2 MATERIAL: CuSn6
Material: CuSn6 |
| 69 | 3 PLATING: 0.3-1.8 μm Sn OVER 0.7-1.5 μm Ni
Oberflaeche: 0.3-1.8 μm Sn ueber 0.7-1.5 μm Ni |
| 81 | 4 PACKAGING: 50.000 CONTACTS/REEL (PAPERBOARD REEL)
Verpackung: 50.000 Kontakte/Spule (Pappspule) |
| 75 | 5 MAX SPLICINGS PER REEL: 3 SPLICES/REEL
Maximale Anzahl an Reel-Verbindungen: 3 Verbindungen pro Spule |
| 76 | 6 MEASURING POINT FOR DIMENSION OF MATERIAL THICKNESS
Messpunkt für Dickenmessung |

"THIS DRAWING IS A CONTROLLED DOCUMENT FOR IDENTIFICATION AND TRACKING PURPOSES. ANY REVISIONS OR CHANGES TO THIS DOCUMENT SHOULD BE CONTACTED FOR THE LATEST VERSION."		DWN 05FEB2010 T.Starke CEN 05FEB2010 C.F.Bienertling		 Tyco Electronics AMP GmbH 64625 Bensheim (Germany)	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 0.63 MQS MULTISPIN PIN CONTACT ON REEL	
		0 PLC ±0.25 1 PLC ±0.15 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC APPLICATION SPEC	
MATERIAL -		FINISH -		SIZE CASE CODE DRAWING NO A1 00779 C-2141016	
		WEIGHT 0.1g		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1 SHEET 1 OF 1 REV A	