





Date	SYM	REVISION RECORD	AUTH	DR.	CK.
5/27/06	A	REDRAWN, ADDED "ROHS COMPLIANT". UPDATED NOTES	T.B.	B.S.	
03/22/13	B	UPDATED TO "ROHS 2 COMPLIANT"	T.B.	B.S.	
06/14/13	C	UPDATED TITLE	T.B.	B.S.	



PCB LAYOUT

NOTES:

1. MATERIAL:

HOUSING : HIGH IMPACT NYLON 66, HALOGEN AND PHOSPHOR FREE, UL94V-0, UL FILE NO. E48285

RIVETS: BRASS, NICKLE PLATED.

SPRING: 302 STAINLESS STEEL, NICKLE PLATED.

CROSSOVER WIRE: 24AWG, UL1007, CSA, TR64

PC PINS: 302 STAINLESS STEEL, NICKEL PLATED.

TEMPERATURE RANGE: -40°C TO +140°C

RESISTANT TO SOLVENTS, COMMON OILS AND REFRIGERANTS

ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT. ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title FOUR "AAA" CELL HOLDER WITH PC PINS		
Angular ± 3°	Date 06/14/13	Drawing Number BH4AAAPC	