

# Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

**BELDEN**  
SENDING ALL THE RIGHT SIGNALS

## 9728 Multi-Conductor - Multi-Pair Snake Cable

For more Information  
please call

1-800-Belden1



### General Description:

24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs, individually Beldfoil® shielded (100% coverage) each with 24 AWG stranded tinned copper drain wire, overall PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
4	24	7x32	TC - Tinned Copper	.024

Total Number of Conductors: 8

#### Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Datalene®	FPE - Foam Polyethylene	0.019

#### Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.048

#### Overall Cable

Overall Nominal Diameter: 0.363 in.

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 60°C (UL AWM Style 2493)

Bulk Cable Weight: 51 lbs/1000 ft.

Max. Recommended Pulling Tension: 65 lbs.

Min. Bend Radius/Minor Axis: 3.750 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

AWM Specification: UL Style 2493 (300 V 60°C)

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 9728 Multi-Conductor - Multi-Pair Snake Cable

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89728

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)
100

#### Nom. Inductance:

Inductance (μH/ft)
0.23

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
12.5

#### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
23.2

#### Nominal Velocity of Propagation:

VP (%)
76

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
24

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 15 Ohm/1000 ft

#### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
.384	0.74
.7056	0.87
.768	0.88
1.024	0.94
1.4112	1.01
1.536	1.03
2.048	1.13
2.8224	1.29
3.072	1.35
4.096	1.57
5.6448	1.78
6.144	1.84
8.192	2.13
11.2896	2.45
12.288	2.57
24.576	3.57

#### Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	UL AWM Style 2493

#### Max. Recommended Current:

Current
2.5 Amps per conductor @ 25°C

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 9728 Multi-Conductor - Multi-Pair Snake Cable

### Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9728 060100	100 FT	6.000 LB	CHROME		4 FS PR #24 FHDPE PVC
9728 0601000	1,000 FT	55.000 LB	CHROME	C	4 FS PR #24 FHDPE PVC
9728 060500	500 FT	29.000 LB	CHROME		4 FS PR #24 FHDPE PVC
9728 0605000	5,000 FT	295.000 LB	CHROME		4 FS PR #24 FHDPE PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-15-2012

© 2014 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9728 060100](#) [9728 060500](#)