


LOC		DIST				REVISIONS					
				P	F	ZONE	LTR	DESCRIPTION		DATE	APPD
G		14					B	REVISED PER 0720-0719-95		18JAN96	OKS CHK




METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	E13288 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 8* APPROX AS SHOWN



										322445		
										PART NO		
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -		DR 14JUN94 DK SCHRUM		AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME TERMINAL, TAB, SOLISTRAND™			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE		CHK 05AUG94 DA PATTERSON						
				WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.50mm² [13,100-20,800] CIR MILS SOLID OR STRANDED		APPD 05AUG94 CH KULYNYCH						
				THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPD 05AUG94 JL MECKLEY						
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		COPPER PER ASTM B-152 ANNEALED		PRODUCT SPEC -		APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO C=322445
FOR ORDER ENTRY		1-800-526-5142		FINISH TIN PLATE 0.00254 [.000100] MIN THK PER MIL-T-10727		WEIGHT -		SCALE 10:1		SHEET		1 OF 1