



■ Features :

- Universal AC input / Full range
- 3 pole AC inlet IEC320-C14
- Built-in active PFC function, PF>0.95
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Fully enclosed plastic case
- Approvals: UL / CUL / PSE / TUV / BSMI / CCC / CB / FCC / CE
- Class I power (with earth pin)
- LED indicator for power on
- No load power consumption<0.5W
- ErP step2 compliant (level V)
- NRCAN compliant
- MEPS compliant
- Meet EISA 2007 (Energy Independence and Security Act)
- 2 years warranty




SPECIFICATION

ORDER NO.	GS160A12-R7B	GS160A15-R7B	GS160A20-R7B	GS160A24-R7B	GS160A48-R7B
OUTPUT	SAFETY MODEL NO.	GS160A12	GS160A15	GS160A20	GS160A24
	DC VOLTAGE	12V	15V	20V	24V
	RATED CURRENT	11.5A	9.6A	8A	6.67A
	CURRENT RANGE	0 ~ 11.5A	0 ~ 9.6A	0 ~ 8A	0 ~ 6.67A
	RATED POWER (max.)	138W	144W	160W	160W
	RIPLPE & NOISE (max.) Note.2	80mVp-p	100mVp-p	150mVp-p	180mVp-p
	VOLTAGE TOLERANCE Note.3	±5.0%	±5.0%	±4.0%	±3.0%
	LINE REGULATION Note.4	±1.0%	±1.0%	±1.0%	±1.0%
	LOAD REGULATION	±5.0%	±5.0%	±4.0%	±3.0%
	SETUP, RISE TIME Note.6	2000ms, 20ms / 230VAC	2500ms, 20ms / 115VAC	at full load	
INPUT	HOLD UP TIME (Typ.)	20ms / 230VAC	20ms / 115VAC	at full load	
	VOLTAGE RANGE Note.7	85 ~ 264VAC	120 ~ 370VDC		
	FREQUENCY RANGE	47 ~ 63Hz			
	POWER FACTOR (Typ.)	PF>0.95 / 230VAC	PF>0.98 / 115VAC	at full load	
	EFFICIENCY (Typ.)	89%	90%	92%	92.5%
	AC CURRENT	1.85A / 115VAC	1A / 230VAC		
	INRUSH CURRENT (max.)	120A / 230VAC			
PROTECTION	LEAKAGE CURRENT(max.)	0.75mA / 240VAC			
	OVERLOAD	105 ~ 135% rated output power			
		Protection type : Hiccup mode, recovers automatically after fault condition is removed			
	OVER VOLTAGE	105 ~ 135% rated output voltage			
		Protection type : Shut down o/p voltage, re-power on to recover			
ENVIRONMENT	OVER TEMPERATURE	90°C ±10°C (RTH2) detect on inside ambient temperature			
		Protection type : Shut down o/p voltage, re-power on to recover			
	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")			
	WORKING HUMIDITY	20% ~ 90% RH non-condensing			
	STORAGE TEMP., HUMIDITY	-20 ~ +85°C, 10 ~ 95% RH			
SAFETY & EMC (Note. 5)	TEMP. COEFFICIENT	±0.03% / °C (0~50°C)			
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes			
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, BSMI CNS14336, CCC GB4943, J60950-1(except for 48V) approved			
	WITHSTAND VOLTAGE	I/P-O/P: 3kVAC			
	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH			
OTHERS	EMC EMISSION	Compliance to EN55022 class B, EN61000-3-2,3, FCC PART 15 / CISPR22 class B, CNS13438 class B, GB9254, GB17625.1			
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, light industry level, criteria A			
	MTBF	290.3K hrs min. MIL-HDBK-217F(25°C)			
CONNECTOR	DIMENSION	175*72*35mm (L*W*H)			
	PACKING	0.66Kg; 20pcs / 14.2Kg / 0.85CUFT			
NOTE	PLUG	See page 2 ; Other type available by customer requested			
	CABLE	See page 2 ; Other type available by customer requested			

1. All parameters are specified at 230VAC input, rated load, 25°C 70% RH ambient.
2. Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uf & 47uf capacitor.
3. Tolerance: includes set up tolerance, line regulation, load regulation.
4. Line regulation is measured from low line to high line at rated load.
5. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives.
6. Length of set up time is measured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time.
7. Derating may be needed under low input voltage. Please check the derating curve for more details.

■ Mechanical Specification

Case No.GS160A Unit:mm




■ Plug Assignment

Standard plug : power DIN 4 pin with lock type, KYCON KPPX-4P equivalent


R7B		
	PIN NO.	OUTPUT
2	1,4	+V
1	2,3	-V

AC FG
-V connected to AC FG

■ Derating Curve



■ Static Characteristics



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mean Well:

[GS160A12-R7B](#) [GS160A15-R7B](#) [GS160A20-R7B](#) [GS160A24-R7B](#) [GS160A48-R7B](#)