




PRODUCT NUMBER
66987-0XXLF

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 5



NOTES:

- 1 - MOLDING MATERIAL: PBT 30% GLASS FILLED, COLOUR BLUE, FLAME RETARDANT, ACCORDING TO UL 94, CATEGORY V0.
- 2 - OVER DASH NUMBER -006 ONLY THE FIRST AND LAST THREE POSITIONS MUST HAVE GROOVES ON TWO SIDES
- 3 - THIS HOUSING IS INTENDED FOR USE WITH BERG TERMINAL # 76785-YXX AND BERG HEADERS # 76385-YXX OR 76383-YXX
- 4 - FOR BERG DUFLEX CLINCHER APPLICATION DATA SEE SPECIFICATION TA-333 SHEET 213-10F1
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - b - LEGAL STATEMENT: SEE GS-22-008

THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code	SEE NOTE 1	surface	ISO 1302	tolerance	ISO 406	ISO 101	projection	product family	VCC DR
Ltr	ecr no	dr	date	tolerances unless otherwise specified	angles	linear	mm	title	DUFLEX
A	F80386	DLE	98.07.10					HOUSING DOUBLE ROW	
B	F00499	PNZ	00.09.13						
C	FD4-D347	DLE	04.12.10						
D	FD5-D189	DLE	05.04.07	dr	D LEGRAND	98.07.10		dwg no	sheet 1 of 2
E	FD5-D236	DLE	05.08.24	engr	JM PHAMVAN	98.07.10		66987	A2
F	FD5-D286	DLE	05.11.07	chr	P NIZZI	98.07.10		type	CUSTOMER Drawing
G	FD6-D226	DLE	06.07.07	appd	JMP	98.07.10			
sheet index	revision	G	F						
	sheet	1	2						

The document is the property of and contains confidential and proprietary information of FCI. No part of this information may be reproduced, stored in a retrieval system, or transmitted in any form or by any means, electronic, mechanical, photocopying, recording, or by any information storage and retrieval system, without the written consent of FCI. Copyright © FCI

FCI CONFIDENTIAL



FCIconnect.com

PRODUCT NUMBER	NUMBER OF POS.	DIM"N"	DIM"P"
66987-002(LF)	2 x 02	2.54	5.00
66987-003(LF)	2 x 03	5.08	7.54
66987-004(LF)	2 x 04	7.62	10.08
66987-005(LF)	2 x 05	10.16	12.62
66987-006(LF)	2 x 06	12.70	15.16
66987-007(LF)	2 x 07	15.24	17.70
66987-008(LF)	2 x 08	17.78	20.24
66987-009(LF)	2 x 09	20.32	22.78
66987-010(LF)	2 x 10	22.86	25.32
66987-011(LF)	2 x 11	25.40	27.86
66987-012(LF)	2 x 12	27.94	30.40
66987-013(LF)	2 x 13	30.48	32.94
66987-014(LF)	2 x 14	33.02	35.48
66987-015(LF)	2 x 15	35.56	38.02
66987-016(LF)	2 x 16	38.10	40.56
66987-017(LF)	2 x 17	40.64	43.10
66987-018(LF)	2 x 18	43.18	45.64
66987-019(LF)	2 x 19	45.72	48.18
66987-020(LF)	2 x 20	48.26	50.72
66987-021(LF)	2 x 21	50.80	53.26
66987-022(LF)	2 x 22	53.34	55.80
66987-023(LF)	2 x 23	55.88	58.34
66987-024(LF)	2 x 24	58.42	60.88
66987-025(LF)	2 x 25	60.96	63.42
66987-026(LF)	2 x 26	63.50	65.96
66987-027(LF)	2 x 27	66.04	68.50
66987-028(LF)	2 x 28	68.58	71.04
66987-029(LF)	2 x 29	71.12	73.58
66987-030(LF)	2 x 30	73.66	76.12
66987-031(LF)	2 x 31	76.20	78.66
66987-032(LF)	2 x 32	78.74	81.20
66987-033(LF)	2 x 33	81.28	83.74
66987-034(LF)	2 x 34	83.82	86.28
66987-035(LF)	2 x 35	86.36	88.02
66987-036(LF)	2 x 36	88.90	91.36

mat'l. code SEE NOTES SHEET 1				surface ISO 1302	tolerance ISO 406 ISO 701	projection 1st angle	product family VCC DR			
lfr	ecn no	dr	date	tolerances unless otherwise specified			title			
E	F05-0236	DLE	05.08.24	angles	.D±x	mm	DUFLEX			
F	F06-0226	DLE	06.07.07	linear	.DD±.0x	scale N/A	HOUSING DOUBLE ROW			
				dr	D LEGRAND	98.07.13	dwg no			
				engr	P NIZZI	98.07.13	sheet 2 of 2			
				chr	D LEGRAND	98.07.13	66987			
				app	P NZ	98.07.13	type			
sheet index		revision	sheet							