


DO NOT SCALE
DIMENSIONS IN mm




METRIC

THIRD ANGLE
PROJECTION



NOTES:

- 1 SPLICE FREE FOR AMPLOMATOR.
2 REELED WITH PAPER LAYER.
3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



3 OBSOLETE

3 OBSOLETE

3 OBSOLETE

WIRE RANGE :
0,3-0,56 mm
INSULATION RANGE :
1,0-2,0 DIA.

	TIN	BRASS	2	6-160316-4
	TIN-LEAD	PHOSPHORBRONZE		6-160316-3
	TIN-LEAD	BRASS		6-160316-2
	PRE-TIN HOT DIP	PHOSPHORBRONZE		6-160316-0
	TIN	BRASS	1	5-160316-9
	NONE	BRASS	1	5-160316-8
	GOLD	PHOSPHORBRONZE		5-160316-7
	TIN	PHOSPHORBRONZE		5-160316-6
	NONE	PHOSPHORBRONZE		5-160316-5
	GOLD	BRASS		5-160316-4
	SILVER	BRASS		5-160316-3
	TIN	BRASS		5-160316-2
	NONE	BRASS		5-160316-1
	FINISH	MATERIAL	PARTNUMBER	

-	-	-	-	-	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED			
-	-	-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.			
-	-	-	-	-	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION, 19			
F2	REVISED PER ECO-09-025699	KK	AEG	16DEC09	Tyco Electronics Tyco Electronics, ITALIA S.r.l. Corso F.lli Cervi, 15 COLLEGNO (TORINO)			
F1	ET00-0045-02	HY	CT	07 MAR 02	NAME			
F	EH-0243-94	DK	PB	11-04-94	.110 SRS FASTON RECEPTACLE			
LTR.	REVISION RECORD	DR.	CHK.	DATE				
DR.:	D.KESSLER	CHK.:	P.BEIJNON	APP.:	L.V.SOEST	DWG. No.	C-160316	SHEET 1 OF 1
DATE:	11-04-94	DATE:	-	DATE:	-			REV. LTR. F2