


3216LV

Fast-acting Line-voltage Chip™ surface mount fuse

RoHS



Product features

- Surface mount fuse, fast acting, 125Vac
- Utilize thick and thin metal film technologies for superior fusing action and enhanced reliability.

Agency information

- UL Recognition Guide & File numbers: JDYX2 & E19180.
- CSA Component Acceptance: 053787 C 000 & Class No: 1422 30

Environmental data

- Operating Temperature Range: -65 °C to +125 °C, with proper derating
- Thermal Shock: MIL-STD-202, Method 107, Test Condition B (-65 °C to 125 °C), 1000 cycles, fuses soldered to FR-4 glass-epoxy circuit board
- Vibration: MIL-STD-202, Method 204, Test Condition C (55 Hz to 2000 Hz, 10 G)
- Solderability: Withstands 60 seconds above 200 °C, 260 °C maximum
- Moisture Resistance: MIL-STD-202, Method 106, 10 day cycle
- Solder Leach Resistance & Terminal Adhesion: EIA-576 (30 seconds submersion in 260 °C (tin-lead solder)

Soldering method

- Wave Immersion: 260 °C, 10 sec max.
- Infrared Reflow: 260 °C, 30 sec max.

Ordering

- Specify packaging and product code (i.e., TR/3216LV1-R)

ELECTRICAL CHARACTERISTICS	
% of Amp Rating	Opening Time
100%	4 hours minimum
250%	5 seconds maximum


SPECIFICATIONS

Part Number	Current Rating (Amps)	Voltage Rating Vac/dc	Interrupting Rating @125Vac/dc (amps)	Typical Melting Integral @ 10X Rated Current (A ² * sec)		Typ. Resistance @ ≤ 10% Rated Current (Ω)	Typ. Voltage Drop @ Rated Current (Volts)
				AC	DC		
3216LV250-R	250mA	125	50	0.00016	0.000084	4.5	1.4
3216LV375-R	375mA	125	50	0.001	0.0002	1.80	0.73
3216LV750-R	750mA	125	50	0.0033	0.00379	0.75	0.63
3216LV1-R	1	125	50	0.020	0.0084	0.52	0.63
3216LV1.25-R	1.25	125	50	0.035	0.021	0.40	0.62
3216LV1.5-R	1.5	125	50	0.038	0.024	0.26	0.49


Notes:

1. AC interrupting rating, melting integral and total clearing integral measured at 125V, unity power factor
2. DC interrupting rating, melting integral and total clearing integral measured at 125V with a battery source
3. Voltage drop measured at 23 ± 3°C ambient temperature with the device mounted on a suitable circuit board trace
4. It is recommended that fuses be mounted with ceramic (white) side facing up
5. Device designed to carry rated current for four hours minimum. An operating current of 80% or less of rated current is recommended, with further derating required at elevated ambient temperatures


Dimensions mm/(inches)
Drawing Not to Scale



Land Pattern



TIME CURRENT CURVE



PACKAGING CODE	
Packaging Code TR	Description 3000 fuses on 8mm tape-and-reel on a 7 inch (178mm) reel per EIA Standard 481

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 2541
May 2017

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.