




Home: PCB Headers >

Part Number: 26-28-2171

3.96mm (.156") Pitch KK® Header, Right Angle, Square Pin, 17 Circuits, Gold (Au) Plating



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	3246
Category:	PCB Headers
Overview:	KK® Interconnect System - Molex
Engineering/Old PN:	324617AG

[CHECK DISTRIBUTOR INVENTORY](#)[Add to My Parts](#)[Email this page](#)[Go to Part Detail ▾](#)**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active[EU RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)[▼ General](#)

Status	Obsolete
Category	PCB Headers
Series	3246
Application	Board-to-Board, Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753733152

[▼ Physical](#)

Breakaway	No
Circuits (Loaded)	17
Circuits (maximum)	17
Flammability	94V-2
Glow-Wire Compliant	No
Lock to Mating Part	None
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.96mm
PCB Locator	No
PCB Retention	None
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	0°C to +75°C

[▼ Electrical](#)

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

[▼ Agency Certification](#)

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

UL	E29179
----	--------

[▼ Material Info](#)

Engineering Number	324617AG
--------------------	----------

PRODUCTS[Antennas](#)
[Application Tooling](#)
[Cable Assemblies](#)
[Connected Lighting](#)
[Connectors](#)
[Copper Flex](#)
[Electrical Products](#)
[Industrial Automation](#)
[Membrane Switches](#)
[Optical Solutions](#)
[Printed Electronic Solutions](#)**QUICK LINKS**[Company Information](#)
[Contact Molex](#)
[Cross-Reference](#)
[Koch Industries](#)
[Industries](#)
[Investor Relations](#)
[Literature](#)
[Molex Racing](#)
[Press Room / Press Releases](#)
[Product Index](#)
[Sitemap](#)
[Terms & Conditions](#)**RESOURCES**[Supply Chain Transparency](#)
[Business Continuity](#)
[Compliance](#)
[ecocare](#)
[Feedback | Help](#)
[Jobs](#)
[Legal | Trademarks](#)
[Mobile Site](#)
[Supplier Portal](#)
[Privacy Policy](#)
[Tradeshows](#)**STAY CONNECTED**