





# Bost




73



80




85



87




91



95



96




97



99



100



101



103




104



105

PLIERS



Very high reliability  
of the unlimited use spring

## Shot-blasted finish

Transparent anticorrosion  
varnish.

## Flanged trivet

Master clearance.



## Opening return spring

Accurate gestures.  
Ideal for heavy use.

## Expert ergonomic handles

Bicolour and bimaterial.  
Very high user comfort and  
optimum handling.






## Chrome-plated multibost

- Wire cutter: max. 80kg/ mm<sup>2</sup>
- Jaws shaped to grip round, hexagon, or square parts.
- Rack joint by riveting: high resistance to torsion and transmission of a very high tightening torque.
- Dissymmetrical jaw teeth: auto-clamping pliers on tubes, no more ripping.
- Anti finger-crush stop: secure use.
- 7 adjustment positions.
- High frequency tempering of the teeth, long lifetime of the jaws (hardness: 60/62 HRC).
- Chrome-plated.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 240 | 114050 | 8 | 6 | -  | 365 |
| 240 | 114056 | 0 | 3 | C5 | 385 |



## Multibost


- Wire cutter: max. 80kg/ mm<sup>2</sup>
- Jaw shaped to grip round, hexagon, or square parts.
- Rack joint by riveting: high resistance to torsion and application of very high tightening torques.
- Dissymmetrical jaw teeth: self-locking clamp on the tubes, no more slipping.
- Anti-finger crushing stop: secure use.
- 7 adjustment positions.
- High frequency tempering of the teeth, long lifetime of the jaws (hardness: 60/62 HRC).
- Blasted, anti-corrosion transparent varnish.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 240 | 114060 | 7 | 6 | -  | 365 |
| 240 | 114066 | 9 | 3 | C5 | 385 |





| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 240 | 115490 | 1 | 10 | -  | 345 |
| 240 | 115491 | 8 | 1  | -  | 345 |
| 240 | 115496 | 3 | 3  | C5 | 345 |




### Techni2 pliers

- Automatic locking of the axis button to maintain settings.
- Self-clamping on tubes, jaw profile suited to nuts.
- 7 setting positions: flexible and precise handling.
- Jaws shaped to grip and tear round, hexagon or square parts.
- High frequency tempering of the teeth: very high resistance to wearing (hardness 60-62 HRC).
- Ergonomic handle with PVC sleeve.
- Anti-finger crush stop.
- Shot-blasted and anti-corrosion varnish.




| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 240 | 115570 | 0 | 10 | -  | 360 |
| 240 | 115575 | 5 | 3  | C5 | 390 |
| 300 | 115580 | 9 | 3  | -  | 535 |
| 300 | 115585 | 4 | 1  | C5 | 605 |





### Technibost pliers

- Exceptional resistance to torsion thanks to an axis riveted and flanged.
- Cross pliers with double rack for higher precision jaw clamping positions.
- Self-locking on tubes, jaw profile suited to nuts.
- 7 setting positions.
- High frequency tempering of the teeth: hardness 60-62 HRC.
- Ergonomic handle, PVC sleeve.
- Anti finger crushing stop.
- Shot-blasted steel and anti-corrosion varnish.



## DIAGONAL CUTTERS


NF E 73-105/ ISO 5749/ DIN ISO 5749



### Expert mechanics diagonal cutter

- Mechanics diagonal cutter for hard wires.
- Double induction treatment of cutting edges to cut hard materials: piano wire 200 kg/mm<sup>2</sup> max.
- Broad head: high resistance.
- Axis offset towards cutting edges for maximum cutting demultiplication.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 140 | 114130 | 7 | 6 | -  | 150 |
| 140 | 114136 | 9 | 3 | C2 | 170 |
| 160 | 114140 | 6 | 6 | -  | 200 |
| 160 | 114146 | 8 | 3 | C2 | 220 |
| 180 | 114150 | 5 | 6 | -  | 240 |
| 180 | 114156 | 7 | 3 | C2 | 260 |




### Expert electricians diagonal cutting

- Fine cutting edges sharpened to cut:
  - soft materials: copper wires even small diameter: 0,5 mm
  - semi-hard wires max. 160 kg/mm max.
- Fine and thin nose for access to confined spaces.
- Induction treatment of cutting edges: extended lifetime.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 140 | 114170 | 3 | 6 | -  | 150 |
| 140 | 114176 | 5 | 3 | C2 | 170 |
| 160 | 114180 | 2 | 6 | -  | 190 |
| 160 | 114186 | 4 | 3 | C2 | 210 |

## FRONT CUTTING PLIERS


NF E 73-104/ ISO 5748/ DIN ISO 5748



### Mechanics front cutter

- Double induction treatment of cutting edges to:
  - cuts hard materials: piano wire 200 kg/mm<sup>2</sup> max.
  - extended lifetime.
- Axis offset towards cutting edges for maximum cutting demultiplication.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114200 | 7 | 6 | -  | 210 |
| 160 | 114206 | 9 | 3 | C2 | 230 |




\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## FRONT CUTTING PLIERS

NF E 73-104/ ISO 5748/ DIN ISO 5748



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114230 | 4 | 6 | -  | 225 |
| 160 | 114236 | 6 | 3 | C2 | 245 |




### Electricians front cutters


- Double induction treatment of cutting edges to cut semi-hard wire: max 160 kg/mm<sup>2</sup>.
- Thin cutting edges cut and sharpened specifically for copper wire.

## EXPERT UNIVERSAL PLIERS

NF 73-103/ ISO 5746/ DIN ISO 5746




| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114010 | 2 | 6 | -  | 180 |
| 160 | 114016 | 4 | 3 | C2 | 200 |
| 160 | 114020 | 1 | 6 | -  | 215 |
| 180 | 114026 | 3 | 3 | C2 | 235 |
| 200 | 114030 | 0 | 6 | -  | 290 |
| 200 | 114036 | 2 | 3 | C3 | 310 |



- Double induction treatment of cutting edges to cut harder wires: piano wire 200 kg/mm<sup>2</sup> maximum.
- Flanged rivet: mastering of the operating clearance.
- Shot-blasted finish.
- Transparent varnish

## EXPERT RANGE FLAT PLIERS


NF 73-103/ ISO 5745-1/ DIN ISO 5745



### Flat pliers straight long nose

- Nose inner face ribbed for stronger grip
- Nose length: 46 mm

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114090 | 4 | 6 | -  | 160 |
| 160 | 114096 | 6 | 3 | C2 | 180 |




\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## EXPERT RANGE ROUND PLIERS

NF E 73-102/ ISO 5745/ DIN ISO 5745




- Inner face of the nose ribbed to reinforce grip.
- Nose length: 46 mm.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114120 | 8 | 1 | -  | 150 |
| 160 | 114126 | 0 | 3 | C2 | 170 |

## HALF ROUND PLIERS

NF E 73-102/ ISO 5745/ DIN ISO 5745



### Half round pliers straight long nose

- Double induction treatment of cutting edges to cut semi-hard wires: Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Half-round nose for greater access in confined spaces.
- Ribbed nose for solid grip on the part.
- Nose length: 75 mm.
- Shot-blasted finish - anticorrosion varnish

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 200 | 114250 | 2 | 3 | -  | 190 |
| 200 | 114256 | 4 | 1 | C2 | 210 |




### Half round pliers with straight short nose

- Double induction treatment of cutting edges to cut semi-hard wire: Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Ribbed nose for solid grip on the part.
- Nose length: 50mm
- Shot-blasted finish, anti corrosion varnish.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114270 | 0 | 6 | -  | 164 |
| 160 | 114276 | 2 | 3 | C2 | 184 |

## HALF ROUND PLIERS

NF E 73-102/ ISO 5745/ DIN ISO 5745




### Half round angled long nose pliers

- Double induction treatment of cutting edges to cut half-hard wires: Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Ribbed nose for solid grip on the part and angled at 45° for easy access in confined spaces.
- Nose length: 75 mm for 200 mm length models, and 50 mm for 160 mm long models.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 114290 | 8 | 6 | -  | 164 |
| 160 | 114296 | 0 | 3 | C2 | 184 |
| 200 | 114260 | 1 | 3 | -  | 190 |
| 200 | 114266 | 3 | 1 | C2 | 210 |


## EXPERT WIRE STRIPPERS / CABLE CUTTER

NF E 73-102/ ISO 5745/ DIN ISO 5745



- Stripping capacity: wires from 0.5 to 6 mm<sup>2</sup>.
- Built-in cable cutter.
- Adjustable stripping diameter.
- Stripping over a larger length without excessive distortion.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 190 | 114310 | 3 | 6 | -  | 160 |
| 190 | 114316 | 5 | 3 | C2 | 180 |



\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

### Case with 3 EXPERT pliers

- Composed of:
  - 1 240 mm Multibost with built-in wire cutter (80 kg/mm<sup>2</sup>).
  - 1 Universal 180 mm.
  - 1 Mechanics diagonal cutter 160 mm.

| Qté | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x3  | 114560 | 2 | 1 | CC | 865 |



### Case with 2 EXPERT pliers

- Composed of:
  - 1 240 mm Multibost with built-in wire cutter (80 kg/mm<sup>2</sup>).
  - 1 Mechanics diagonal cutter 160 mm.

| Qté | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x2  | 114540 | 4 | 1 | CC | 615 |



### Case with 2 EXPERT pliers


- Composed of:
  - 1 Universal 180 mm.
  - 1 Mechanics diagonal cutting 160 mm.

| Qté | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x2  | 114550 | 3 | 1 | CC | 480 |



## PRIMO RANGE MULTIGRIP PLIERS


NF E 73-108 / ISO 8976 / DIN ISO 8976



### Multibost


- Riveted rack joint.
- Flexible position change.
- Fitted with a wire cutter: max. 80 kg/mm<sup>2</sup>.
- Finger anti-crush stop.
- 7 setting positions.
- Self-clamping on tubes.
- Orange PVC sleeves with guard.

| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 240 | 117230 | 1 | 6  | -  | 350 |
| 240 | 117235 | 6 | 3  | C5 | 370 |
| 240 | 117400 | 8 | 80 | -  | 350 |



## PRIMO RANGE DIAGONAL CUTTING PLIERS


NF E 73105 / ISO 5749 / DIN ISO5749



### Mechanics diagonal cutting pliers

- Double induction treatment of cutting edges to cut hard materials: piano wire (200 kg/mm<sup>2</sup>).
- Axis offset to cutting edges for maximum cutting demultiplication
- Orange PVC sleeves with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117280 | 6 | 6 | -  | 172 |
| 160 | 117285 | 1 | 3 | C2 | 192 |
| 180 | 117290 | 5 | 6 | -  | 232 |
| 180 | 117295 | 0 | 3 | C2 | 252 |



### Electricians diagonal cutting pliers

- Double induction treatment of cutting edges to cut half-hard wires max 160 kg/mm<sup>2</sup>.
- Axis offset towards cutting edges for maximum cutting demultiplication.
- Orange PVC sleeves with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 140 | 117300 | 1 | 6 | -  | 162 |
| 140 | 117305 | 6 | 3 | C2 | 187 |
| 160 | 117310 | 0 | 6 | -  | 197 |
| 160 | 117315 | 5 | 3 | C3 | 219 |

## PRIMO RANGE FRONT CUTTING PLIERS

NF E 73104 / ISO 5748 / DIN ISO 5748

### mechanics front cutting pliers

- Double induction treatment of cutting edges to cut hard wires max 200 kg/mm<sup>2</sup>.
- Axis offset towards cutting edges for maximum cutting demultiplication.
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117320 | 9 | 3 | -  | 172 |
| 160 | 117325 | 4 | 1 | C2 | 192 |



### Front cutter


- Double induction treatment of cutting edges to cut hard wires max 200 kg/mm<sup>2</sup>.
- Axis offset towards cutting edges for maximum cutting demultiplication.
- Orange PVC sleeve.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 190 | 115345 | 4 | 1 | C3 | 420 |
| 220 | 115355 | 3 | 1 | C4 | 520 |



## PRIMO RANGE UNIVERSAL PLIERS

NF 73-103/ ISO 5746/ DIN ISO 5746



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117200 | 4 | 6 | -  | 172 |
| 160 | 117205 | 9 | 3 | C2 | 192 |
| 180 | 117210 | 3 | 6 | -  | 202 |
| 180 | 117215 | 8 | 3 | C3 | 222 |
| 200 | 117220 | 2 | 6 | -  | 277 |
| 200 | 117225 | 7 | 3 | C4 | 287 |

- Double induction treatment of cutting edges to cut the hardest wires.
- Piano wire 200 kg/mm<sup>2</sup>.
- Orange PVC sleeve with guards.


\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## PRIMO RANGE FLET PLIERS

NF E 73-102 / ISO 5745 / DIN ISO 5745



- Ribbed nose for better part gripping.
- Nose length: 46 mm.
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117250 | 9 | 3 | -  | 137 |
| 160 | 117255 | 4 | 1 | C2 | 157 |

## PRIMO RANGE ROUND PLIERS

NF E 73-102 / ISO 5745 / DIN ISO 5745




- Ribbed noses for better part gripping.
- Nose length: 41 mm.
- Nose diameter: 2 mm.
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 167 | 117270 | 7 | 3 | -  | 107 |
| 167 | 117275 | 2 | 1 | C2 | 127 |

## PRIMO RANGE HALF ROUND PLIERS


NF E 73-102 / ISO 5745 / DIN ISO 5745



### Long nose half round pliers

- Ribbed nose.
- Double induction treatment of cutting edges to cut semi-hard wires max 160 kg/mm<sup>2</sup>
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 200 | 117330 | 8 | 3 | -  | 165 |
| 200 | 117335 | 3 | 1 | C2 | 185 |




\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## PRIMO RANGE HALF ROUND PLIERS

NF E 73-102 / ISO 5745 / DIN ISO 5745



### Long elbow half round pliers

- Inner nose face ribbed for tighter grip.
- Double induction treatment of cutting edges for semi-hard wires max 1.6 to 160 kg/mm<sup>2</sup>.
- Orange PVC sleeve with guards.
- Nose angled at 45°.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 193 | 117340 | 7 | 3 | -  | 165 |
| 193 | 117345 | 2 | 1 | C2 | 185 |



### Short nose half round straight pliers

- Double induction treatment of cutting edges for semi-hard wires: Ø 1.6 to 160 kg/mm<sup>2</sup>.
- Ribbed nose for tight part gripping.
- Nose length: 50 mm.
- Shot-blasted finish, anticorrosion varnish.
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117350 | 6 | 3 | -  | 150 |
| 160 | 117355 | 1 | 1 | C2 | 170 |



### Angled short half round nose pliers

- Nose angled at 45°.
- Orange PVC sleeve with guards.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 117360 | 5 | 3 | -  | 150 |
| 160 | 117365 | 0 | 1 | C1 | 170 |

## PRIMO RANGE WIRE STRIPPERS

- Fitted with an opening return spring and a setting screw.
- Stripping capacity: wires from 0.5 to 6 mm<sup>2</sup>.
- Orange PVC sleeve with guards.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 150 | 117370 | 4 | 6 | -  | 180 |
| 150 | 117375 | 9 | 3 | C1 | 200 |

\* For a full EAN, add the following before the code: 303254

**Case with 3 pliers**

- Composed of:
  - 1 PVC Multibost with built-in wire cutter guards (80 kg/mm<sup>2</sup>).
  - 1 Universal (200 kg/mm<sup>2</sup>) in PVC with guards.
  - 1 mechanics diagonal cutter in PVC with guards (200 kg/mm<sup>2</sup>).
- Presentation in cardboard box.

| Qty | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x3  | 118030 | 6 | 1 | CC | 940 |

**Case with 2 pliers**

- Composed:
  - 1 PVC Multibost with built-in wire-cutter guards (80 kg/mm<sup>2</sup>).
  - 1 mechanics diagonal cutter in PVC with guards (200 kg/mm<sup>2</sup>).
- Presentation in cardboard box.


| Qty | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x2  | 118090 | 0 | 1 | CC | 645 |

**Case with 2 pliers**

- Composed:
  - 1 Universal (200 kg/mm<sup>2</sup>) in PVC with guards.
  - 1 mechanics diagonal cutter in PVC with guards (200 kg/mm<sup>2</sup>).
- Presentation in cardboard box.

| Qty | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| x2  | 118080 | 1 | 1 | CC | 555 |






| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 240 | 139080 | 4 | 6 | -  | 325 |
| 240 | 139085 | 9 | 3 | C5 | 352 |

## Multibost


- Riveted rack joint: high resistance to torsion and flexible change of positions.
- Fitted with a wire cutter (80 kg/mm<sup>2</sup>).
- Anti finger crushing stop and 7 setting positions.
- Self-clamping on tubes.
- Polished head, red lacquered handles and transparent anti-corrosion varnish.



| L1  | 1      | * | 0  | W | 7 g |
|-----|--------|---|----|---|-----|
| 240 | 139060 | 6 | 10 | - | 345 |

## Technibost plier

- Exceptional resistance to torsion thanks to its riveted axis.
- Double rack cross branches.
- Self-clamping on tubes.
- Anti-finger crushing stop.
- 7 setting positions.
- Epoxy lacquer.



## SECTOR MULTIGRIP PLIERS

NE E 73-108 / ISO 8976 / DIN ISO 8976





| L1  | 1      | * | 0 | W | 7 g  |
|-----|--------|---|---|---|------|
| 400 | 115480 | 2 | 1 | - | 1120 |

- 10 setting positions.
- Nose positioned by machined sectors authorising very high strength.
- Handles in red PVC, chrome-plated pliers, length: 400 mm.


## LACQUERED RANGE UNIVERSAL PLIERS

NF E 73-103 / ISO 5746 / DIN ISO 5746



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 180 | 139020 | 0 | 10 | -  | 200 |
| 180 | 139025 | 5 | 3  | C3 | 220 |
| 200 | 139030 | 9 | 10 | -  | 275 |

- Double induction treatment of cutting edges for hard wires: piano wire 200 kg/mm<sup>2</sup>.
- Polished heads, lacquered handles.
- Anti-corrosion transparent varnish.



\* For a full EAN, add the following before the code: 303254

**Bost**


Catalogue 2005



### Multibost


- Riveted rack joint.
- Wire cutter: 80 Kg/mm<sup>2</sup>.
- 7 setting positions.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 240 | 145030 | 0 | 1 | -  | 290 |
| 240 | 145035 | 5 | 1 | C4 | 310 |



### MECHANICS DIAGONAL NF EN 60900


### g CUTTING PLIERS



### Mechanics diagonal cutter

- Cutting edges designed and machined to cut hard wires (200 kg/mm<sup>2</sup>).


| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 187 | 145060 | 7 | 1 | - | 240 |




### Electricians diagonal pliers

- Thin sharpened cutting edges for copper and semi-hard wires (160 Kg/mm<sup>2</sup>).

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 143 | 145080 | 5 | 1 | -  | 150 |
| 163 | 145090 | 4 | 1 | -  | 170 |
| 163 | 145095 | 9 | 1 | C3 | 190 |









| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 158 | 145110 | 9 | 1 | -  | 200 |
| 158 | 145115 | 4 | 1 | C2 | 225 |

- Sharpened thin cutting edges for copper and semi-hard wires (160 Kg/mm<sup>2</sup>).

## INSULATED UNIVERSAL PLIERS


g

NF EN 60900



| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 180 | 145010 | 2 | 1 | - | 230 |


- Sharpened thin cutting edges for copper wire.
- Polished head with anti-corrosion transparent varnish.



### Long straight half round nose pliers

- Cutting edges: max. 160 kg/mm<sup>2</sup>.

| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 200 | 145120 | 8 | 1 | - | 210 |



### 45° angled long nose half round pliers

- Cutting edges: max. 160 kg/mm<sup>2</sup>.

| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 194 | 145130 | 7 | 1 | - | 210 |




| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 160 | 145140 | 6 | 1 | - | 135 |



### Straight short nose half round pliers


- Cutting edges: max. 160 kg/mm<sup>2</sup>.





- Copper and aluminium.
- Cutting capacity: Ø 14 mm (50 mm²).

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 210 | 145150 | 5 | 1 | -  | 325 |
| 210 | 145155 | 0 | 1 | C3 | 350 |



- Screw setting.
- With opening return spring.
- Capacity: 0.5 to 6 mm².

| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 160 | 145160 | 4 | 1 | - | 180 |
| 160 | 145165 | 9 | 1 | - | 205 |

## MINIBOST RANGE SECTOR MULTIGRIP PLIERS




- Ribbed nose.
- 4 setting positions.
- Blue grained PVC sleeves.

| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 125 | 111070 | 9 | 10 | -  | 70  |
| 125 | 111076 | 1 | 1  | B3 | 84  |

## MINIBOST RANGE DIAGONAL CUTTING PLIERS

### Diagonal cutters

- Cutting edges designed and machined to cut copper and soft steel wire.
- Max: Ø 1 mm to 110 kg/mm<sup>2</sup>.
- Polished head, anti-corrosion varnish.
- Opening return spring for flexible and easy operation.
- Blue PVC grained sleeve.
- Flush cutting of copper and soft steel wire.





| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 115 | 111010 | 5 | 10 | -  | 54  |
| 115 | 111016 | 7 | 1  | B3 | 88  |


## MINIBOST RANGE FRONT CUTTING PLIERS

- Normal cutting.
- Cutting edges designed and machined to cut copper and soft steel wire.
- Max: Ø 1.5 mm à 110kg/mm<sup>2</sup>.
- Blue grained PVC sleeve.

| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 115 | 111020 | 4 | 10 | -  | 70  |
| 115 | 111026 | 6 | 1  | B3 | 84  |




## MINIBOST RANGE UNIVERSAL PLIERS



- Cutting edges designed and machined to cut copper and soft steel wire.
- Blue grained PVC sleeve

| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 115 | 111000 | 6 | 10 | -  | 62  |
| 115 | 111006 | 8 | 1  | B3 | 76  |

## MINIBOST RANGE SHORT NOSE FLAT PLIERS




- Smooth nose.
- Nose length: 23 mm.
- Blue, grained, PVC sleeve.



| L1  | 1      | * | 0  | W | 7 g |
|-----|--------|---|----|---|-----|
| 115 | 111090 | 7 | 10 | - | 60  |


## MINIBOST RANGE HALF ROUND FLAT PLIERS



- Long ribbed long nose.
- Nose length: 44 mm.
- Wire cutter (copper and soft steel).
- Blue, grained PVC sleeves.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 138 | 111060 | 0 | 10 | -  | 74  |
| 138 | 111066 | 2 | 1  | B3 | 74  |



## MINIBOST RANGE LONG NOSE ROUND CLAMP

- Smooth nose.
- Nose length: 29.5 mm.
- Ø at tip 1.5 mm.
- Blue PVC grained sleeve.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 125 | 111106 | 5 | 1 | B3 | 79  |


## MINIBOST RANGE 1/2 ROUND PARTS

### Half round short nose

- Ribbed nose.
- Cutting edges designed and machined to cut copper and soft steel wire.
- Blue grained PVC sleeve.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 120 | 111030 | 3 | 10 | -  | 56  |
| 120 | 111036 | 5 | 1  | B3 | 70  |





### Half round long nose

- Ribbed nose.
- Wire cutter with stripping hole (max. Ø 2 mm).
- Blue grained PVC sleeves.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 138 | 111040 | 2 | 10 | -  | 65  |
| 138 | 111046 | 4 | 1  | B3 | 79  |





## Long elbow half round nose

- Cutting edges designed and machined to cut copper and soft steel wire.
- Blue grained PVC sleeve.
- Ribbed nose, with 30° angle.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 135 | 111050 | 1 | 10 | -  | 62  |
| 135 | 111056 | 3 | 1  | B3 | 76  |

# MINIBOST RANGE WIRE STRIPPERS

## Wire stripper

- High precision pliers.
- Strips wires between 0.1 and 2 mm².
- Grained blue PVC sleeves.




| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 125 | 111080 | 8 | 10 | -  | 62  |
| 125 | 111086 | 0 | 1  | B3 | 76  |

# SET OF MINIBOST PLIERS

## Set of pliers in plastic case

- Ref. 112000
  - 1 universal (ref : 111000).
  - 1 diagonal (ref : 111010).
  - 1 long half-round nose (ref : 111040).
- Ref. 112010
  - 1 universal (ref : 111000).
  - 1 diagonal (ref : 111010).

| Qty | 1      | * | 0 | W   | 7 g |
|-----|--------|---|---|-----|-----|
| x3  | 112000 | 5 | 1 | CP6 | 355 |
| x2  | 112010 | 4 | 1 | CP5 | 250 |



## FINE NOSE TWEEZERS

### Fine straight nose tweezer

- Straight ribbed nose.
- Fine polish stainless steel.
- Blue PVC sleeve.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 155 | 123106 | 0 | 1 | B3 | 39  |

### Fine nose angled tweezer

- Ribbed nose with 45° angle.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 150 | 123116 | 9 | 1 | B3 | 39  |

## LONG NOSE TWEEZERS

### Long straight nose tweezer

- Straight ribbed nose.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 123016 | 2 | 1 | B3 | 44  |

### Long angled nose tweezer

- Ribbed nose with 35° angle.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 155 | 123026 | 1 | 1 | B3 | 44  |

## SELF-TIGHTENING TWEEZER

- Straight ribbed nose.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 155 | 123046 | 9 | 1 | B3 | 44  |

## ANTIMAGNETIC TWEEZERS

- Slightly ribbed thin nose



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 110 | 123066 | 7 | 1 | B3 | 29  |

\* For a full EAN, add the following before the code: 303254

## LOCK GRIP PLIERS

- Tightening force set by adjustment screw.
- Teeth on entire depth and handy release lever.
- Jaws precision machined and tempered for longer lifetime.
- Chrome-plated finish.



| L1  | H  | 1      | * | 0 | W  | 7 g |
|-----|----|--------|---|---|----|-----|
| 135 | 30 | 133036 | 7 | 1 | B3 | 184 |
| 190 | 42 | 133040 | 4 | 1 | -  | 370 |
| 190 | 42 | 133046 | 6 | 1 | B7 | 415 |
| 235 | 63 | 133050 | 3 | 1 | -  | 600 |
| 235 | 63 | 133056 | 5 | 1 | B7 | 645 |



## HIGH CAPACITY LOCK GRIP PLIERS

- Rack with 4 setting positions.
- Chrome-plated finish.


| L1  | H   | 1      | * | 0 | W  | 7 g |
|-----|-----|--------|---|---|----|-----|
| 220 | 50  | 133000 | 8 | 1 | -  | 640 |
| 220 | 50  | 133006 | 0 | 1 | B7 | 685 |
| 250 | 100 | 133010 | 7 | 1 | -  | 750 |
| 250 | 100 | 133016 | 9 | 1 | B7 | 795 |



## HIGH CAPACITY LOCK GRIP PLIERS WITH SWIVEL JAWS

- Swivel jaws.
- Rack with 4 setting positions.
- Chrome-plated finish.

| L1  | H   | 1      | * | 0 | W  | 7 g |
|-----|-----|--------|---|---|----|-----|
| 250 | 100 | 133020 | 6 | 1 | -  | 750 |
| 250 | 100 | 133026 | 8 | 1 | B7 | 795 |



\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## EXTERNAL CIRCLIP PLIERS - STRAIGHT NOSE

NF - E 73-130 / DIN 5254 A B



| L1  | 1      | * | Ø<br>mm | DØ<br>mini - maxi mm | 0 | W  | 7 g |
|-----|--------|---|---------|----------------------|---|----|-----|
| 130 | 135000 | 6 | 0,9     | 3 - 10               | 3 | -  | 130 |
| 130 | 135005 | 1 | 0,9     | 3 - 10               | 1 | C1 | 142 |
| 140 | 135010 | 5 | 1,3     | 10 - 25              | 3 | -  | 130 |
| 140 | 135015 | 0 | 1,3     | 10 - 25              | 1 | C1 | 142 |
| 180 | 135020 | 4 | 1,8     | 19 - 60              | 3 | -  | 195 |
| 180 | 135025 | 9 | 1,8     | 19 - 60              | 1 | C2 | 207 |
| 230 | 135030 | 3 | 2,3     | 40 - 100             | 3 | -  | 275 |
| 230 | 135035 | 8 | 2,3     | 40 - 100             | 1 | C3 | 287 |

- Special shape nickel-plated nose guaranteeing the circlip is maintained on the pliers.
- Opening return spring, PVC sleeve on handles.
- Shot-blasted pliers, transparent anti-corrosion varnish.

## EXTERNAL CIRCLIP PLIERS - NOSE WITH 90° ANGLE

NF - E 73-130 / DIN 5254 A B



| L1  | 1      | * | Ø<br>mm | DØ<br>mini - maxi mm | 0 | W  | 7 g |
|-----|--------|---|---------|----------------------|---|----|-----|
| 130 | 135045 | 7 | 0,9     | 3 - 10               | 1 | C1 | 142 |
| 140 | 135050 | 1 | 1,3     | 10 - 25              | 3 | -  | 130 |
| 140 | 135055 | 6 | 1,3     | 10 - 25              | 1 | C1 | 142 |
| 180 | 135060 | 0 | 1,8     | 19 - 60              | 3 | -  | 195 |
| 180 | 135065 | 5 | 1,8     | 19 - 60              | 1 | C2 | 207 |


- Special shape of the nickel-plated nose guaranteeing the circlip is maintained on the pliers.
- Opening return spring, PVC sleeve handles.
- Shot-blasted pliers, transparent anti-corrosion varnish.

## INTERNAL CIRCLIP PLIERS - STRAIGHT NOSE

NF - E 73-130 / DIN 5256 C D

- Special shaped nickel-plated nose guaranteeing the circlip is maintained on the pliers.
- Opening return spring, handles with PVC sleeve.
- Shot-blasted pliers, transparent anti-corrosion varnish.

| L1  | 1      | * | Ø<br>mm | d Ø<br>mini - maxi mm | 0 | w  | 7 g |
|-----|--------|---|---------|-----------------------|---|----|-----|
| 130 | 135080 | 8 | 0,9     | 8 - 12                | 3 | -  | 120 |
| 140 | 135090 | 7 | 1,3     | 12 - 25               | 3 | -  | 120 |
| 140 | 135095 | 2 | 1,3     | 12 - 25               | 1 | C1 | 142 |
| 180 | 135100 | 3 | 1,8     | 19 - 60               | 3 | -  | 185 |
| 180 | 135105 | 8 | 1,8     | 19 - 60               | 1 | C2 | 197 |
| 230 | 135110 | 2 | 2,3     | 40 - 100              | 3 | -  | 265 |
| 230 | 135115 | 7 | 2,3     | 40 - 100              | 1 | C3 | 277 |



## INTERNAL CIRCLIP PLIERS - NOSE WITH 90° ANGLE

NF - E 73-130 / DIN 5256 C D

- Special shaped nickel-plated nose guaranteeing the circlip is maintained on the plier.
- Opening return spring, handles with PVC sleeve.
- Shot-blasted pliers, transparent anti-corrosion varnish.

| L1  | 1      | * | Ø<br>mm | d Ø<br>mini - maxi mm | 0 | w  | 7 g |
|-----|--------|---|---------|-----------------------|---|----|-----|
| 130 | 135125 | 6 | 0,9     | 8 - 12                | 1 | C1 | 142 |
| 140 | 135130 | 0 | 1,3     | 12 - 25               | 3 | -  | 120 |
| 140 | 135135 | 5 | 1,3     | 12 - 25               | 1 | C1 | 142 |
| 180 | 135140 | 9 | 1,8     | 19 - 60               | 3 | -  | 185 |
| 180 | 135145 | 4 | 1,8     | 19 - 60               | 1 | C4 | 197 |



## REVERSIBLE CIRCLIP PLIERS

NF - E 73-130 / DIN 5256 C D

- Straight nose.
- Used for fitting and removing external or internal circlips.
- Burnished - PVC

| L1  | 1      | * | D Ø<br>mini - maxi | d Ø<br>mini - maxi | 0 | w  | 7 g |
|-----|--------|---|--------------------|--------------------|---|----|-----|
| 130 | 135195 | 9 | 10 - 25            | 10 - 25            | 1 | C1 | 82  |



\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

## SPECIAL PLASTIC PLIERS



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 163 | 115290 | 7 | 1 | -  | 180 |
| 163 | 115295 | 2 | 1 | C3 | 200 |

- Flush cutting.
- Screw adjusted stop.
- Opening return spring.
- Max capacity Ø 6 mm on plastic.

## SIDE CUTTING PLIERS



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 156 | 115300 | 3 | 3 | -  | 130 |
| 156 | 115305 | 8 | 1 | C3 | 150 |

- Flush cutting.
- Fine cutting edges tilted by 35°.
- Max Ø 0.9 to 80 kg/mm².

## REVOLVER PUNCH PLIERS

- For diameters: 3 - 3.2 - 3.5 - 4 - 4.5 - 5.
- Presentation: chrome-plated.
- For leather, fabric, rubber ...



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 220 | 138866 | 5 | 1 | B7 | 220 |



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 260 | 138006 | 5 | 1 | B7 | 600 |



- 4 nozzles for rivets diameter 2.4 - 3.2 - 4 - 4.8.
- Supplied with nozzle key.
- Opening return spring.

## GAS PLIERS



| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 230 | 138870 | 2 | 5 | - | 390 |


- Used to tighten tubes of different diameter.
- Polished head, lacquered handles.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 190 | 137100 | 1 | 20 | -  | 200 |
| 190 | 137105 | 6 | 5  | C1 | 227 |
| 220 | 137110 | 0 | 20 | -  | 295 |
| 220 | 137115 | 5 | 5  | C4 | 322 |
| 250 | 137120 | 9 | 20 | -  | 380 |
| 250 | 137125 | 4 | 5  | C4 | 407 |
| 280 | 137130 | 8 | 20 | -  | 455 |
| 280 | 137133 | 9 | 5  | -  | 455 |

## Burnished

- High precision designed and machined cutting edge for clear cutting of the wire to bind.
- Double induction tempering.
- Polished head, matt burnishing.



| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 220 | 137150 | 6 | 20 | -  | 295 |
| 220 | 137155 | 1 | 5  | C4 | 320 |
| 250 | 137160 | 5 | 20 | -  | 380 |
| 250 | 137165 | 0 | 5  | C4 | 400 |
| 280 | 137170 | 4 | 20 | -  | 455 |

## Lacquered


- High precision designed and machined cutting edges for clear cut of the wire to bind.
- Double induction tempering.
- Red lacquer.



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 220 | 137185 | 8 | 5 | C5 | 310 |
| 250 | 137195 | 7 | 5 | C5 | 400 |


## With sleeves

- High precision designed and machined cutting edges for clear cut of the wire to bind.
- Double induction tempering.
- Matt burnishing, PVC handles.



## JOINERS NIPPERS

NF - E 73-114 / ISO 9243 / DIN 5241



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 200 | 137020 | 2 | 6 | -  | 360 |
| 200 | 137026 | 4 | 1 | B7 | 380 |
| 230 | 137030 | 1 | 6 | -  | 520 |
| 230 | 137036 | 3 | 1 | B7 | 540 |
| 250 | 137040 | 0 | 6 | -  | 560 |

- Polished head, red lacquered body.
- Long lever handles.

## FRONT CUTTING: GREEK MODEL

NF - E 73-114 / ISO 9243 / DIN 5241

- Clear cutting of the wire to bind.
- Burnished pliers, polished head.

| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 160 | 139200 | 6 | 3 | - | 180 |
| 180 | 139210 | 5 | 3 | - | 250 |



## "COMTE" CUTTING PLIERS

NF - E 73107 / ISO 5748 / DIN 5243



| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 160 | 137230 | 5 | 6 | -  | 240 |
| 160 | 137235 | 0 | 1 | C2 | 260 |
| 190 | 137240 | 4 | 6 | -  | 400 |
| 190 | 137245 | 9 | 1 | C3 | 420 |

- Cutting edges designed and machined to cut soft steel wires (Max 80 kg/mm<sup>2</sup>).
- Spatula shaped handles for good grip.
- Lacquered.


\* For a full EAN, add the following before the code: 303254

**Bost**

Catalogue 2005

# 140 Kg/mm<sup>2</sup> BOLT CROPPER

NF ISO 8976 / ISO 8976 / DIN ISO 8976





| N° | L1   | 1      | * | 0 | A | B | 50<br>kg/mm<br>Ø | 140<br>kg/mm<br>Ø | 7 Kg |
|----|------|--------|---|---|---|---|------------------|-------------------|------|
| 00 | 350  | 138504 | 6 | 1 | • |   | 7                | 4                 | 1    |
| 0  | 450  | 138514 | 5 | 1 | • |   | 8                | 6                 | 1,7  |
| 1  | 600  | 138524 | 4 | 1 | • |   | 10               | 7                 | 2,8  |
| 2  | 750  | 138534 | 3 | 1 | • |   | 13               | 8                 | 4,2  |
| 3  | 900  | 138544 | 2 | 1 | • |   | 16               | 9                 | 6,15 |
| 4  | 1050 | 138554 | 1 | 1 | • |   | 19               | 10                | 8,6  |

- Forged head and body.
- Tube arm.
- Adjustable by 2 excentric screws on the head.
- Very fine adjustment.
- Spare head supplied complete with hardware.



| N° | L1   | 1      | * | 0 | A | B | 50<br>kg/mm<br>Ø | 140<br>kg/mm<br>Ø | 7 Kg  |
|----|------|--------|---|---|---|---|------------------|-------------------|-------|
| 00 | 350  | 138604 | 3 | 1 | • |   | 7                | 4                 | 0,450 |
| 0  | 450  | 138614 | 2 | 1 | • |   | 8                | 6                 | 0,650 |
| 1  | 600  | 138624 | 1 | 1 | • |   | 10               | 7                 | 1,1   |
| 2  | 750  | 138634 | 0 | 1 | • |   | 13               | 8                 | 1,7   |
| 3  | 900  | 138644 | 9 | 1 | • |   | 16               | 9                 | 2,450 |
| 4  | 1050 | 138654 | 8 | 1 | • |   | 19               | 10                | 3,250 |

- Spare head for bolt cropper.



\* For a full EAN, add the following  
before the code: 303254


**Bost**

Catalogue 2005

**Jointed diagonal cutters**

- Demultiplication system for easy cutting of steel wires Ø 2.5 mm.
- $R = 200 \text{ Kg/mm}^2$ .
- Fitted with an opening spring with closed position locking system and strap.
- Bronze plated blades - lacquered handles.

| L1  | 1      | * | 0  | W  | 7 g |
|-----|--------|---|----|----|-----|
| 210 | 138800 | 9 | 10 | -  | 275 |
| 210 | 138805 | 4 | 1  | C2 | 295 |

**Jointed front cutter**

- Specifications identical to diagonal cutting.


| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 210 | 138835 | 1 | 1 | C2 | 305 |

## CABLE CUTTER



- To cut copper and aluminium cables.
- Stainless steel.
- Fitted with an opening return spring and a locking system.
- Ergonomic handle.

| L1  | 1      | * | 0 | Ø <sub>max</sub> | mm | W  | 7 g |
|-----|--------|---|---|------------------|----|----|-----|
| 170 | 121005 | 8 | 1 | 10               | 24 | C2 | 147 |



## CABLE CUTTER

### Cable cutter with sleeve

- Fitted with a closed position locking system.
- Opening return spring.
- Blue PVC handles.
- Chrome-plated body.



| L1  | 1      | * | 0 | Ø<br>max | mm <sup>2</sup> | W   | 7 g |
|-----|--------|---|---|----------|-----------------|-----|-----|
| 160 | 121015 | 7 | 1 | 12       | 50              | C2  | 187 |
| 210 | 121020 | 1 | 3 | 14       | 50              | -   | 290 |
| 210 | 121025 | 6 | 1 | 14       | 50              | C11 | 317 |
| 240 | 121035 | 5 | 1 | 18       | 60              | C14 | 377 |

### Chrome-plated cable cutter

- Fitted with a closed position locking system.
- Opening return spring.
- Blue PVC handles.
- Chrome-plated body.



| L1  | 1      | * | 0 | Ø<br>max | mm <sup>2</sup> | W  | 7 g |
|-----|--------|---|---|----------|-----------------|----|-----|
| 170 | 121045 | 4 | 1 | 10       | 50              | C2 | 267 |

## CRIMPING PLIERS

- Tip wire-cutter.
- Pre-insulated lugs 0.5 - 6 mm<sup>2</sup>.
- Non insulated lugs 0.5 - 6 mm<sup>2</sup>.
- Stripping capacity: 0.75 - 6 mm<sup>2</sup>.
- Threaded rod cutters: M = 2.6 - 3 - 3.5 - 4 - 5.



| L1  | 1      | * | 0 | W | 7 g |
|-----|--------|---|---|---|-----|
| 230 | 127010 | 6 | 5 | - | 215 |
| 230 | 127015 | 1 | 3 | C | 242 |

## AUTOMATIC WIRE STRIPPER

- Strips and ejects in a single operation.
- 6 stripping sizes: 0.5 - 0.75 - 1 - 1.5 - 2.5 - 4 mm<sup>2</sup>.
- PVC branches.

| L1  | 1      | * | 0 | W  | 7 g |
|-----|--------|---|---|----|-----|
| 175 | 125036 | 8 | 1 | B7 | 405 |

